

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930700

Luminaire Tested: DFN2DS-PN4F0-070DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-070DS935-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5117.0 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930700

CATALOG NUMBER: DFN2DS-PN4F0-070DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930700

CATALOG NUMBER: DFN2DS-PN4F0-070DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1816	1816	1816
5°	1823	1793	1803
10°	1809	1764	1749
15°	1788	1712	1663
20°	1760	1637	1555
25°	1730	1552	1451
30°	1689	1465	1317
35°	1649	1371	1200
40°	1609	1272	1064
45°	1562	1162	941
50°	1514	1051	821
55°	1464	931	705
60°	1407	805	585
65°	1342	677	533
70°	1264	557	490
75°	1168	508	457
80°	1032	454	417
85°	811	358	358

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1562 cd/sqm

TEST NUMBER: P930700

CATALOG NUMBER: DFN2DS-PN4F0-070DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.2	4.6
10°-20°	640.1	12.5
20°-30°	898.7	17.6
30°-40°	979.7	19.1
40°-50°	900.4	17.6
50°-60°	707.1	13.8
60°-70°	460.3	9.0
70°-80°	236.9	4.6
80°-90°	60.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1772.1	34.6
0°-40°	2751.7	53.8
0°-60°	4359.3	85.2
0°-90°	5117.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5117.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2488	2488	2488	2488	2488	
5°	2488	2477	2448	2468	2461	236
15°	2366	2342	2265	2222	2200	667
25°	2148	2076	1927	1835	1801	988
35°	1851	1736	1538	1396	1346	1158
45°	1513	1362	1126	966	912	1169
55°	1150	975	732	597	554	1028
65°	777	594	392	315	308	770
75°	414	256	180	164	162	438
85°	97	49	43	43	43	116
90°	0	0	0	0	0	

TEST NUMBER: P930700

CATALOG NUMBER: DFN2DS-PN4F0-070DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2488.1	2488.1	2488.1	2488.1	2488.1
2.5°	2499.2	2488.1	2463.2	2485.9	2481.4
5°	2488.1	2476.8	2447.5	2467.8	2461.1
7.5°	2467.8	2454.4	2422.9	2431.6	2420.5
10°	2440.8	2425.0	2380.0	2373.2	2359.8
12.5°	2407.1	2386.8	2325.9	2312.5	2287.6
15°	2366.5	2341.6	2265.2	2222.4	2200.0
17.5°	2319.2	2283.1	2188.5	2139.0	2103.0
20°	2265.2	2220.0	2107.5	2051.4	2001.6
22.5°	2206.7	2154.8	2024.1	1947.6	1914.0
25°	2148.1	2076.0	1927.3	1835.2	1801.3
27.5°	2078.4	2001.6	1837.3	1731.5	1679.7
30°	2004.1	1918.3	1738.1	1623.5	1562.6
32.5°	1931.9	1828.3	1643.8	1508.6	1452.2
35°	1850.9	1736.0	1538.0	1396.1	1346.4
37.5°	1772.1	1648.1	1438.9	1283.3	1227.2
40°	1688.7	1553.8	1335.2	1175.4	1116.8
42.5°	1603.2	1459.2	1231.7	1064.9	1008.9
45°	1513.2	1362.2	1125.9	965.9	911.9
47.5°	1427.6	1267.8	1024.6	864.6	815.1
50°	1333.0	1173.2	925.4	770.0	722.9
52.5°	1240.6	1071.6	830.8	682.2	639.5
55°	1150.5	974.9	731.7	596.8	554.0
57.5°	1058.3	878.1	644.1	517.9	481.9
60°	963.7	783.5	551.6	437.0	400.8
62.5°	871.4	691.4	472.7	364.8	346.8
65°	776.8	594.3	391.8	315.4	308.4
67.5°	686.8	504.3	315.4	276.8	270.2
70°	592.2	416.6	261.1	238.6	229.5
72.5°	502.2	335.4	218.4	200.5	195.9
75°	414.3	256.5	180.1	164.3	162.2
77.5°	326.5	182.2	141.9	132.8	128.3
80°	245.4	130.6	108.0	99.2	99.2
82.5°	171.1	87.9	74.3	69.7	69.7
85°	96.8	49.4	42.7	42.7	42.7
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930700

CATALOG NUMBER: DFN2DS-PN4F0-070DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.31	14.83	13.67	15.14	15.46	9.27	10.79	9.63	11.10	11.42
	3H	15.07	16.44	15.45	16.77	17.13	10.53	11.90	10.91	12.23	12.59
	4H	15.74	17.02	16.14	17.37	17.75	11.04	12.32	11.43	12.66	13.04
	6H	16.23	17.41	16.64	17.78	18.17	11.42	12.60	11.83	12.97	13.36
	8H	16.39	17.52	16.82	17.91	18.31	11.54	12.67	11.97	13.06	13.46
	12H	16.50	17.58	16.93	17.96	18.39	11.62	12.70	12.05	13.08	13.51
4H	2H	13.41	14.69	13.81	15.04	15.42	9.96	11.24	10.36	11.59	11.97
	3H	15.35	16.41	15.76	16.81	17.21	11.41	12.47	11.82	12.87	13.27
	4H	16.09	17.05	16.53	17.47	17.91	12.01	12.96	12.44	13.38	13.82
	6H	16.69	17.52	17.14	17.96	18.42	12.49	13.33	12.95	13.77	14.23
	8H	16.90	17.68	17.36	18.12	18.59	12.66	13.43	13.12	13.88	14.35
	12H	17.05	17.75	17.54	18.23	18.70	12.77	13.47	13.26	13.95	14.42
8H	4H	16.12	16.90	16.58	17.34	17.81	12.36	13.14	12.82	13.58	14.05
	6H	16.76	17.40	17.25	17.89	18.37	12.95	13.59	13.44	14.08	14.56
	8H	17.01	17.58	17.52	18.09	18.58	13.17	13.74	13.68	14.25	14.74
	12H	17.21	17.72	17.72	18.21	18.78	13.35	13.86	13.86	14.35	14.91
12H	4H	16.10	16.80	16.59	17.28	17.75	12.40	13.10	12.89	13.58	14.05
	6H	16.74	17.31	17.25	17.82	18.31	13.01	13.59	13.52	14.10	14.59
	8H	17.02	17.53	17.53	18.02	18.59	13.28	13.79	13.79	14.29	14.85