

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930327

Luminaire Tested: DFN2DS-HX4F0-080DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-080DS830-FLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7460.7 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930327

CATALOG NUMBER: DFN2DS-HX4F0-080DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930327

CATALOG NUMBER: DFN2DS-HX4F0-080DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2180	2180	2180
5°	2189	2157	2170
10°	2176	2135	2146
15°	2149	2108	2106
20°	2111	2066	2064
25°	2073	2015	2015
30°	2024	1968	1951
35°	1978	1912	1884
40°	1921	1856	1820
45°	1865	1800	1755
50°	1804	1742	1680
55°	1740	1674	1612
60°	1669	1593	1535
65°	1593	1513	1444
70°	1496	1416	1349
75°	1360	1304	1272
80°	1208	1171	1110
85°	985	939	842

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1865 cd/sqm

TEST NUMBER: P930327

CATALOG NUMBER: DFN2DS-HX4F0-080DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.0	3.7
10°-20°	776.5	10.4
20°-30°	1141.2	15.3
30°-40°	1325.4	17.8
40°-50°	1323.8	17.7
50°-60°	1154.3	15.5
60°-70°	853.3	11.4
70°-80°	482.8	6.5
80°-90°	127.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2193.7	29.4
0°-40°	3519.1	47.2
0°-60°	5997.2	80.4
0°-90°	7460.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7460.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2932	2932	2932	2932	2932	
5°	2932	2921	2890	2913	2907	278
15°	2791	2775	2738	2749	2735	786
25°	2526	2504	2456	2461	2456	1163
35°	2180	2152	2106	2089	2075	1361
45°	1774	1754	1711	1681	1669	1369
55°	1342	1325	1292	1258	1244	1200
65°	905	888	860	835	821	895
75°	474	468	454	437	443	505
85°	116	113	110	102	99	136
90°	0	0	0	0	0	

TEST NUMBER: P930327

CATALOG NUMBER: DFN2DS-HX4F0-080DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2932.3	2932.3	2932.3	2932.3	2932.3
2.5°	2949.3	2935.3	2904.2	2932.3	2926.9
5°	2932.3	2921.2	2890.2	2912.6	2907.2
7.5°	2912.6	2895.8	2864.7	2887.4	2881.8
10°	2881.8	2862.0	2828.2	2850.6	2842.3
12.5°	2839.3	2822.5	2788.7	2802.7	2797.1
15°	2791.4	2774.7	2737.8	2749.2	2735.2
17.5°	2732.2	2715.4	2678.6	2692.7	2678.6
20°	2667.3	2650.5	2611.0	2619.4	2608.3
22.5°	2602.7	2577.2	2540.4	2540.4	2534.7
25°	2526.3	2503.9	2456.1	2461.4	2456.1
27.5°	2441.7	2422.0	2385.4	2377.0	2363.0
30°	2357.4	2334.6	2292.5	2284.1	2272.7
32.5°	2267.0	2250.2	2205.0	2188.0	2176.7
35°	2179.6	2151.5	2106.3	2089.3	2075.2
37.5°	2080.9	2055.4	2010.3	1990.5	1976.5
40°	1979.5	1956.7	1911.6	1886.4	1875.1
42.5°	1880.8	1858.0	1813.2	1784.7	1768.0
45°	1773.7	1753.9	1711.4	1680.6	1669.3
47.5°	1669.3	1649.5	1604.3	1573.2	1556.5
50°	1559.2	1545.2	1505.6	1466.1	1452.1
52.5°	1452.1	1432.3	1395.9	1364.8	1345.0
55°	1342.3	1325.2	1291.5	1257.7	1243.5
57.5°	1232.2	1218.2	1181.4	1147.5	1136.1
60°	1122.1	1111.1	1071.5	1040.4	1032.1
62.5°	1015.0	995.3	967.2	939.1	927.7
65°	905.3	888.2	860.0	834.6	820.6
67.5°	792.4	778.1	752.9	733.3	721.9
70°	688.0	676.6	651.3	631.5	620.4
72.5°	580.9	569.6	555.5	535.8	527.4
75°	473.5	468.2	453.9	437.1	442.7
77.5°	377.8	366.4	360.8	352.4	344.0
80°	282.1	279.1	273.5	265.1	259.3
82.5°	191.8	191.8	189.1	177.7	177.7
85°	115.5	112.8	110.1	101.5	98.7
87.5°	50.9	45.2	39.5	31.1	28.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930327

CATALOG NUMBER: DFN2DS-HX4F0-080DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.99	15.60	14.36	15.92	16.23	13.55	15.16	13.91	15.47	15.79
	3H	15.74	17.20	16.12	17.52	17.88	15.25	16.70	15.63	17.03	17.39
	4H	16.39	17.76	16.79	18.10	18.48	15.89	17.26	16.29	17.61	17.99
	6H	16.86	18.12	17.27	18.49	18.88	16.35	17.62	16.77	17.99	18.38
	8H	17.00	18.21	17.42	18.60	19.00	16.50	17.71	16.92	18.10	18.50
	12H	17.09	18.25	17.52	18.63	19.06	16.58	17.74	17.01	18.12	18.55
4H	2H	14.55	15.92	14.95	16.27	16.64	14.20	15.57	14.60	15.91	16.29
	3H	16.53	17.67	16.94	18.07	18.47	16.12	17.27	16.53	17.66	18.06
	4H	17.30	18.34	17.73	18.75	19.19	16.88	17.91	17.31	18.33	18.76
	6H	17.90	18.80	18.35	19.24	19.70	17.47	18.37	17.92	18.81	19.27
	8H	18.09	18.94	18.55	19.38	19.84	17.65	18.50	18.11	18.94	19.41
	12H	18.22	18.98	18.70	19.46	19.93	17.77	18.53	18.25	19.00	19.47
8H	4H	17.58	18.42	18.04	18.87	19.33	17.20	18.05	17.66	18.49	18.96
	6H	18.29	18.99	18.78	19.48	19.96	17.91	18.61	18.40	19.10	19.58
	8H	18.55	19.18	19.06	19.69	20.17	18.16	18.79	18.67	19.30	19.78
	12H	18.75	19.31	19.26	19.80	20.36	18.34	18.89	18.84	19.38	19.95
12H	4H	17.60	18.36	18.08	18.84	19.31	17.24	18.00	17.72	18.47	18.94
	6H	18.34	18.97	18.85	19.47	19.96	17.97	18.60	18.48	19.11	19.59
	8H	18.65	19.21	19.16	19.70	20.26	18.27	18.83	18.78	19.32	19.88