

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930754

Luminaire Tested: DFN2DS-PN4F0-100DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-100DS935-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7310.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 105.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930754

CATALOG NUMBER: DFN2DS-PN4F0-100DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930754

CATALOG NUMBER: DFN2DS-PN4F0-100DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2595	2595	2595
5°	2604	2562	2576
10°	2584	2520	2499
15°	2555	2445	2375
20°	2514	2339	2221
25°	2472	2218	2073
30°	2413	2093	1882
35°	2356	1958	1714
40°	2299	1818	1520
45°	2231	1660	1345
50°	2163	1501	1173
55°	2092	1330	1007
60°	2010	1150	836
65°	1917	967	761
70°	1806	796	700
75°	1669	726	653
80°	1473	649	595
85°	1157	512	512

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2231 cd/sqm

TEST NUMBER: P930754

CATALOG NUMBER: DFN2DS-PN4F0-100DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.1	4.6
10°-20°	914.5	12.5
20°-30°	1283.9	17.6
30°-40°	1399.5	19.1
40°-50°	1286.3	17.6
50°-60°	1010.2	13.8
60°-70°	657.6	9.0
70°-80°	338.5	4.6
80°-90°	86.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2531.5	34.6
0°-40°	3931.0	53.8
0°-60°	6227.6	85.2
0°-90°	7310.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7310.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3554	3554	3554	3554	3554	
5°	3554	3538	3496	3525	3516	337
15°	3381	3345	3236	3175	3143	953
25°	3069	2966	2753	2622	2573	1411
35°	2644	2480	2197	1994	1923	1655
45°	2162	1946	1608	1380	1303	1669
55°	1644	1393	1045	852	791	1469
65°	1110	849	560	450	441	1100
75°	592	366	257	235	232	626
85°	138	71	61	61	61	166
90°	0	0	0	0	0	

TEST NUMBER: P930754

CATALOG NUMBER: DFN2DS-PN4F0-100DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3554.4	3554.4	3554.4	3554.4	3554.4
2.5°	3570.4	3554.4	3518.9	3551.3	3544.8
5°	3554.4	3538.3	3496.3	3525.4	3515.8
7.5°	3525.4	3506.2	3461.2	3473.8	3457.8
10°	3486.8	3464.3	3400.1	3390.2	3371.1
12.5°	3438.7	3409.6	3322.6	3303.5	3268.0
15°	3380.7	3345.1	3235.9	3174.9	3142.8
17.5°	3313.1	3261.5	3126.4	3055.8	3004.2
20°	3235.9	3171.4	3010.7	2930.5	2859.5
22.5°	3152.3	3078.3	2891.6	2782.4	2734.3
25°	3068.7	2965.7	2753.4	2621.6	2573.2
27.5°	2969.1	2859.5	2624.7	2473.5	2399.5
30°	2862.9	2740.4	2483.1	2319.3	2232.3
32.5°	2759.9	2611.7	2348.3	2155.2	2074.6
35°	2644.2	2480.1	2197.1	1994.4	1923.4
37.5°	2531.6	2354.4	2055.5	1833.3	1753.1
40°	2412.5	2219.7	1907.4	1679.1	1595.5
42.5°	2290.3	2084.5	1759.6	1521.4	1441.2
45°	2161.6	1945.9	1608.5	1379.8	1302.6
47.5°	2039.5	1811.2	1463.7	1235.0	1164.4
50°	1904.3	1676.0	1322.1	1099.9	1032.7
52.5°	1772.2	1531.0	1187.0	974.6	913.6
55°	1643.5	1392.8	1045.3	852.5	791.4
57.5°	1511.9	1254.5	920.1	739.9	688.3
60°	1376.7	1119.4	788.0	624.2	572.7
62.5°	1244.9	987.6	675.4	521.2	495.5
65°	1109.8	849.1	559.7	450.5	440.6
67.5°	981.2	720.4	450.5	395.5	386.0
70°	846.0	595.2	373.0	340.9	328.0
72.5°	717.3	479.1	311.9	286.3	279.8
75°	591.8	366.5	257.3	234.8	231.7
77.5°	466.6	260.4	202.7	189.7	183.3
80°	350.4	186.7	154.3	141.6	141.6
82.5°	244.3	125.6	106.1	99.7	99.7
85°	138.2	70.6	61.1	61.1	61.1
87.5°	51.5	25.6	25.6	22.5	22.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930754

CATALOG NUMBER: DFN2DS-PN4F0-100DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.55	16.07	14.91	16.38	16.70	10.51	12.03	10.87	12.34	12.66
	3H	16.31	17.68	16.69	18.01	18.37	11.77	13.14	12.15	13.47	13.83
	4H	16.98	18.26	17.38	18.61	18.99	12.27	13.56	12.67	13.90	14.28
	6H	17.47	18.65	17.88	19.02	19.41	12.66	13.84	13.07	14.20	14.60
	8H	17.63	18.76	18.06	19.15	19.55	12.78	13.91	13.21	14.30	14.70
	12H	17.74	18.81	18.17	19.20	19.63	12.86	13.94	13.29	14.32	14.75
4H	2H	14.65	15.93	15.05	16.28	16.66	11.20	12.48	11.60	12.83	13.21
	3H	16.58	17.65	17.00	18.05	18.45	12.65	13.71	13.06	14.11	14.51
	4H	17.33	18.29	17.77	18.71	19.14	13.25	14.20	13.68	14.62	15.06
	6H	17.93	18.76	18.38	19.20	19.66	13.73	14.57	14.19	15.01	15.47
	8H	18.14	18.92	18.60	19.36	19.83	13.90	14.67	14.36	15.12	15.58
	12H	18.29	18.99	18.78	19.47	19.94	14.01	14.71	14.50	15.19	15.66
8H	4H	17.36	18.14	17.82	18.58	19.05	13.60	14.38	14.06	14.82	15.29
	6H	18.00	18.64	18.49	19.13	19.61	14.19	14.83	14.68	15.32	15.80
	8H	18.25	18.82	18.76	19.33	19.82	14.41	14.98	14.92	15.49	15.98
	12H	18.45	18.96	18.96	19.45	20.02	14.59	15.10	15.10	15.59	16.15
12H	4H	17.34	18.04	17.82	18.52	18.99	13.64	14.34	14.12	14.82	15.29
	6H	17.98	18.55	18.49	19.06	19.55	14.25	14.83	14.76	15.34	15.82
	8H	18.26	18.77	18.77	19.26	19.83	14.52	15.03	15.03	15.52	16.09