

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930276

Luminaire Tested: DFN2DS-HX4F0-050DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-050DS835-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4250.0 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 48.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930276

CATALOG NUMBER: DFN2DS-HX4F0-050DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930276

CATALOG NUMBER: DFN2DS-HX4F0-050DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1537	1537	1537
5°	1542	1517	1526
10°	1531	1493	1480
15°	1513	1448	1407
20°	1489	1385	1316
25°	1464	1313	1227
30°	1429	1240	1114
35°	1395	1160	1015
40°	1361	1076	900
45°	1322	983	796
50°	1281	889	695
55°	1239	788	596
60°	1190	681	495
65°	1135	573	451
70°	1069	472	415
75°	989	430	387
80°	873	384	352
85°	686	303	303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1322 cd/sqm

TEST NUMBER: P930276

CATALOG NUMBER: DFN2DS-HX4F0-050DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	4.6
10°-20°	531.7	12.5
20°-30°	746.5	17.6
30°-40°	813.7	19.1
40°-50°	747.9	17.6
50°-60°	587.3	13.8
60°-70°	382.3	9.0
70°-80°	196.8	4.6
80°-90°	50.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.8	34.6
0°-40°	2285.5	53.8
0°-60°	3620.7	85.2
0°-90°	4250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4250.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	96
90°	0	0	0	0	0	

TEST NUMBER: P930276

CATALOG NUMBER: DFN2DS-HX4F0-050DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930276

CATALOG NUMBER: DFN2DS-HX4F0-050DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.73	14.25	13.09	14.56	14.88	8.69	10.21	9.05	10.52	10.84
	3H	14.49	15.86	14.87	16.19	16.55	9.95	11.32	10.33	11.65	12.01
	4H	15.16	16.44	15.56	16.79	17.17	10.45	11.74	10.85	12.08	12.46
	6H	15.65	16.83	16.06	17.20	17.59	10.84	12.02	11.25	12.38	12.78
	8H	15.81	16.94	16.24	17.33	17.73	10.96	12.09	11.39	12.48	12.88
	12H	15.92	16.99	16.35	17.38	17.81	11.04	12.12	11.47	12.50	12.93
4H	2H	12.83	14.11	13.23	14.46	14.84	9.38	10.66	9.78	11.01	11.39
	3H	14.76	15.83	15.18	16.23	16.63	10.83	11.89	11.24	12.29	12.69
	4H	15.51	16.47	15.95	16.89	17.32	11.43	12.38	11.86	12.80	13.24
	6H	16.11	16.94	16.56	17.38	17.84	11.91	12.75	12.37	13.19	13.65
	8H	16.32	17.10	16.78	17.54	18.01	12.08	12.85	12.54	13.30	13.76
	12H	16.47	17.17	16.96	17.65	18.12	12.19	12.89	12.67	13.37	13.84
8H	4H	15.54	16.32	16.00	16.76	17.23	11.78	12.56	12.24	13.00	13.47
	6H	16.18	16.82	16.67	17.31	17.79	12.37	13.01	12.86	13.50	13.98
	8H	16.43	17.00	16.94	17.51	18.00	12.59	13.16	13.10	13.67	14.16
	12H	16.63	17.14	17.14	17.63	18.20	12.77	13.28	13.28	13.77	14.33
12H	4H	15.52	16.22	16.00	16.70	17.17	11.82	12.52	12.31	13.00	13.47
	6H	16.16	16.73	16.67	17.24	17.73	12.43	13.01	12.94	13.52	14.00
	8H	16.44	16.95	16.95	17.44	18.01	12.70	13.21	13.21	13.70	14.27