

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930347

Luminaire Tested: DFN2DS-HX4F0-090DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-090DS835-FLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8910.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 93.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930347

CATALOG NUMBER: DFN2DS-HX4F0-090DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930347

CATALOG NUMBER: DFN2DS-HX4F0-090DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2604	2604	2604
5°	2614	2576	2591
10°	2599	2550	2563
15°	2566	2517	2515
20°	2521	2467	2465
25°	2475	2406	2406
30°	2417	2351	2330
35°	2363	2283	2250
40°	2295	2216	2174
45°	2227	2149	2096
50°	2154	2080	2006
55°	2078	1999	1925
60°	1993	1903	1833
65°	1902	1807	1724
70°	1786	1691	1611
75°	1625	1557	1519
80°	1443	1398	1327
85°	1176	1122	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2227 cd/sqm

TEST NUMBER: P930347

CATALOG NUMBER: DFN2DS-HX4F0-090DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	3.7
10°-20°	927.4	10.4
20°-30°	1362.9	15.3
30°-40°	1582.9	17.8
40°-50°	1580.9	17.7
50°-60°	1378.5	15.5
60°-70°	1019.0	11.4
70°-80°	576.6	6.5
80°-90°	152.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2619.9	29.4
0°-40°	4202.8	47.2
0°-60°	7162.3	80.4
0°-90°	8910.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8910.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	162
90°	0	0	0	0	0	

TEST NUMBER: P930347

CATALOG NUMBER: DFN2DS-HX4F0-090DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930347

CATALOG NUMBER: DFN2DS-HX4F0-090DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.61	16.22	14.97	16.53	16.85	14.16	15.77	14.53	16.09	16.40
	3H	16.36	17.81	16.73	18.14	18.50	15.87	17.32	16.24	17.65	18.01
	4H	17.00	18.37	17.40	18.72	19.10	16.51	17.88	16.91	18.23	18.60
	6H	17.47	18.74	17.88	19.11	19.50	16.97	18.24	17.38	18.61	19.00
	8H	17.62	18.83	18.04	19.22	19.62	17.11	18.32	17.54	18.71	19.11
	12H	17.71	18.87	18.14	19.25	19.68	17.19	18.35	17.62	18.74	19.16
4H	2H	15.17	16.54	15.57	16.88	17.26	14.82	16.18	15.21	16.53	16.91
	3H	17.14	18.29	17.55	18.69	19.09	16.74	17.88	17.15	18.28	18.68
	4H	17.92	18.96	18.35	19.37	19.81	17.50	18.53	17.93	18.95	19.38
	6H	18.52	19.42	18.97	19.86	20.32	18.08	18.99	18.54	19.43	19.89
	8H	18.71	19.55	19.17	19.99	20.46	18.27	19.11	18.73	19.56	20.02
	12H	18.84	19.60	19.32	20.07	20.54	18.39	19.15	18.87	19.62	20.09
8H	4H	18.19	19.04	18.65	19.48	19.95	17.82	18.67	18.28	19.11	19.57
	6H	18.91	19.61	19.40	20.10	20.57	18.53	19.23	19.02	19.72	20.19
	8H	19.17	19.80	19.68	20.30	20.79	18.77	19.41	19.28	19.91	20.40
	12H	19.37	19.92	19.87	20.41	20.98	18.95	19.51	19.46	20.00	20.56
12H	4H	18.22	18.98	18.70	19.45	19.92	17.85	18.61	18.33	19.09	19.56
	6H	18.95	19.58	19.46	20.09	20.58	18.58	19.22	19.09	19.72	20.21
	8H	19.27	19.82	19.77	20.31	20.88	18.89	19.45	19.40	19.94	20.50