

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930703

Luminaire Tested: DFN2DS-PN4F0-070DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-070DS950-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6548.9 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930703

CATALOG NUMBER: DFN2DS-PN4F0-070DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930703

CATALOG NUMBER: DFN2DS-PN4F0-070DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1879	1879	1879
5°	1886	1859	1870
10°	1875	1840	1849
15°	1852	1816	1814
20°	1819	1780	1778
25°	1786	1736	1736
30°	1744	1696	1681
35°	1705	1648	1623
40°	1656	1599	1568
45°	1607	1551	1513
50°	1554	1501	1447
55°	1499	1443	1389
60°	1438	1373	1323
65°	1373	1304	1244
70°	1289	1220	1162
75°	1172	1123	1096
80°	1041	1009	957
85°	849	810	726

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1607 cd/sqm

TEST NUMBER: P930703

CATALOG NUMBER: DFN2DS-PN4F0-070DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.3	3.7
10°-20°	681.6	10.4
20°-30°	1001.7	15.3
30°-40°	1163.4	17.8
40°-50°	1162.0	17.7
50°-60°	1013.2	15.5
60°-70°	749.0	11.4
70°-80°	423.8	6.5
80°-90°	111.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1925.6	29.4
0°-40°	3089.0	47.2
0°-60°	5264.2	80.4
0°-90°	6548.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6548.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2574	2574	2574	2574	2574	
5°	2574	2564	2537	2557	2552	244
15°	2450	2436	2403	2413	2401	690
25°	2218	2198	2156	2161	2156	1020
35°	1913	1889	1849	1834	1822	1195
45°	1557	1540	1502	1475	1465	1202
55°	1178	1163	1134	1104	1092	1053
65°	795	780	755	733	720	786
75°	416	411	398	384	389	444
85°	101	99	97	89	87	119
90°	0	0	0	0	0	

TEST NUMBER: P930703

CATALOG NUMBER: DFN2DS-PN4F0-070DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2573.9	2573.9	2573.9	2573.9	2573.9
2.5°	2588.9	2576.5	2549.2	2573.9	2569.2
5°	2573.9	2564.3	2536.9	2556.6	2551.9
7.5°	2556.6	2541.9	2514.6	2534.6	2529.6
10°	2529.6	2512.2	2482.5	2502.3	2494.9
12.5°	2492.2	2477.6	2447.9	2460.2	2455.2
15°	2450.3	2435.5	2403.2	2413.2	2400.9
17.5°	2398.2	2383.6	2351.3	2363.6	2351.3
20°	2341.2	2326.6	2291.9	2299.3	2289.5
22.5°	2284.5	2262.2	2229.9	2229.9	2224.9
25°	2217.6	2197.9	2155.9	2160.6	2155.9
27.5°	2143.3	2126.0	2093.9	2086.6	2074.2
30°	2069.3	2049.2	2012.3	2004.9	1994.9
32.5°	1989.9	1975.2	1935.5	1920.6	1910.6
35°	1913.2	1888.6	1848.9	1834.0	1821.6
37.5°	1826.6	1804.3	1764.6	1747.3	1734.9
40°	1737.6	1717.6	1677.9	1655.9	1645.9
42.5°	1650.9	1631.0	1591.6	1566.6	1551.9
45°	1556.9	1539.6	1502.3	1475.2	1465.2
47.5°	1465.2	1447.9	1408.2	1380.9	1366.3
50°	1368.6	1356.3	1321.6	1287.0	1274.6
52.5°	1274.6	1257.3	1225.3	1198.0	1180.6
55°	1178.2	1163.3	1133.6	1103.9	1091.6
57.5°	1081.6	1069.3	1036.9	1007.3	997.4
60°	985.0	975.2	940.7	913.3	906.0
62.5°	890.9	873.7	849.0	824.3	814.3
65°	794.7	779.6	755.0	732.7	720.3
67.5°	695.6	683.0	660.9	643.6	633.6
70°	603.9	594.0	571.6	554.3	544.6
72.5°	509.9	500.0	487.6	470.3	463.0
75°	415.7	411.0	398.3	383.7	388.7
77.5°	331.7	321.7	316.7	309.3	302.0
80°	247.6	245.0	240.0	232.7	227.7
82.5°	168.3	168.3	165.9	156.0	156.0
85°	101.4	99.0	96.7	89.0	86.7
87.5°	44.6	39.7	34.7	27.3	24.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930703

CATALOG NUMBER: DFN2DS-PN4F0-070DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.47	15.08	13.84	15.40	15.71	13.03	14.64	13.39	14.95	15.27
	3H	15.22	16.68	15.60	17.00	17.37	14.73	16.19	15.11	16.51	16.87
	4H	15.87	17.24	16.27	17.59	17.96	15.38	16.74	15.77	17.09	17.47
	6H	16.34	17.61	16.75	17.97	18.36	15.84	17.11	16.25	17.47	17.86
	8H	16.48	17.69	16.91	18.08	18.48	15.98	17.19	16.40	17.58	17.98
	12H	16.57	17.73	17.00	18.11	18.54	16.06	17.22	16.49	17.60	18.03
4H	2H	14.03	15.40	14.43	15.75	16.13	13.68	15.05	14.08	15.40	15.77
	3H	16.01	17.16	16.42	17.55	17.95	15.60	16.75	16.01	17.15	17.55
	4H	16.79	17.82	17.22	18.24	18.67	16.36	17.40	16.79	17.81	18.25
	6H	17.38	18.29	17.84	18.73	19.18	16.95	17.85	17.40	18.30	18.75
	8H	17.57	18.42	18.03	18.86	19.33	17.13	17.98	17.59	18.42	18.89
	12H	17.70	18.46	18.18	18.94	19.41	17.25	18.01	17.73	18.49	18.96
8H	4H	17.06	17.91	17.52	18.35	18.81	16.69	17.53	17.15	17.97	18.44
	6H	17.77	18.48	18.27	18.96	19.44	17.39	18.10	17.89	18.58	19.06
	8H	18.03	18.66	18.54	19.17	19.66	17.64	18.27	18.15	18.78	19.26
	12H	18.23	18.79	18.74	19.28	19.84	17.82	18.38	18.33	18.87	19.43
12H	4H	17.09	17.85	17.57	18.32	18.79	16.72	17.48	17.20	17.96	18.43
	6H	17.82	18.45	18.33	18.96	19.44	17.45	18.08	17.96	18.59	19.08
	8H	18.13	18.69	18.64	19.18	19.74	17.75	18.31	18.26	18.80	19.36