

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930313

Luminaire Tested: DFN2DS-HX4F0-070DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-070DS840-FLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6936.9 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 71.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930313

CATALOG NUMBER: DFN2DS-HX4F0-070DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930313

CATALOG NUMBER: DFN2DS-HX4F0-070DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2027	2027	2027
5°	2035	2006	2018
10°	2023	1985	1995
15°	1998	1960	1958
20°	1962	1921	1919
25°	1927	1874	1874
30°	1882	1830	1814
35°	1840	1778	1751
40°	1786	1725	1692
45°	1734	1673	1632
50°	1677	1619	1562
55°	1618	1557	1499
60°	1552	1482	1427
65°	1481	1407	1342
70°	1391	1316	1254
75°	1265	1212	1183
80°	1123	1089	1032
85°	916	874	783

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1734 cd/sqm

TEST NUMBER: P930313

CATALOG NUMBER: DFN2DS-HX4F0-070DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.6	3.7
10°-20°	722.0	10.4
20°-30°	1061.1	15.3
30°-40°	1232.4	17.8
40°-50°	1230.8	17.7
50°-60°	1073.3	15.5
60°-70°	793.4	11.4
70°-80°	448.9	6.5
80°-90°	118.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2039.7	29.4
0°-40°	3272.1	47.2
0°-60°	5576.2	80.4
0°-90°	6936.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6936.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2726	2726	2726	2726	2726	
5°	2726	2716	2687	2708	2703	259
15°	2596	2580	2546	2556	2543	731
25°	2349	2328	2284	2289	2284	1081
35°	2027	2000	1958	1943	1930	1266
45°	1649	1631	1591	1563	1552	1273
55°	1248	1232	1201	1169	1156	1116
65°	842	826	800	776	763	832
75°	440	435	422	406	412	470
85°	107	105	102	94	92	126
90°	0	0	0	0	0	

TEST NUMBER: P930313

CATALOG NUMBER: DFN2DS-HX4F0-070DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.4	2726.4	2726.4	2726.4	2726.4
2.5°	2742.3	2729.2	2700.3	2726.4	2721.4
5°	2726.4	2716.2	2687.3	2708.1	2703.1
7.5°	2708.1	2692.5	2663.6	2684.8	2679.5
10°	2679.5	2661.1	2629.6	2650.5	2642.7
12.5°	2639.9	2624.4	2593.0	2606.0	2600.7
15°	2595.5	2579.9	2545.6	2556.3	2543.1
17.5°	2540.3	2524.8	2490.6	2503.7	2490.6
20°	2480.0	2464.5	2427.7	2435.5	2425.2
22.5°	2419.9	2396.3	2362.1	2362.1	2356.8
25°	2349.0	2328.1	2283.7	2288.7	2283.7
27.5°	2270.3	2251.9	2218.0	2210.2	2197.1
30°	2191.9	2170.7	2131.5	2123.7	2113.1
32.5°	2107.8	2092.3	2050.2	2034.4	2023.8
35°	2026.6	2000.5	1958.5	1942.6	1929.5
37.5°	1934.8	1911.2	1869.2	1850.8	1837.7
40°	1840.5	1819.4	1777.4	1754.1	1743.4
42.5°	1748.7	1727.6	1685.9	1659.5	1643.8
45°	1649.1	1630.8	1591.3	1562.7	1552.1
47.5°	1552.1	1533.7	1491.7	1462.8	1447.2
50°	1449.7	1436.6	1399.9	1363.3	1350.1
52.5°	1350.1	1331.8	1297.9	1269.0	1250.5
55°	1248.0	1232.2	1200.8	1169.4	1156.3
57.5°	1145.7	1132.6	1098.4	1067.0	1056.5
60°	1043.3	1033.0	996.4	967.5	959.7
62.5°	943.7	925.4	899.3	873.2	862.6
65°	841.7	825.8	799.7	776.1	763.0
67.5°	736.8	723.5	700.1	681.8	671.2
70°	639.7	629.2	605.5	587.2	576.9
72.5°	540.1	529.6	516.5	498.2	490.4
75°	440.3	435.3	421.9	406.4	411.7
77.5°	351.4	340.7	335.4	327.6	319.9
80°	262.3	259.6	254.3	246.4	241.1
82.5°	178.3	178.3	175.8	165.3	165.3
85°	107.4	104.9	102.4	94.3	91.8
87.5°	47.2	42.0	36.7	28.9	26.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930313

CATALOG NUMBER: DFN2DS-HX4F0-070DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.74	15.35	14.10	15.66	15.98	13.29	14.90	13.66	15.22	15.53
	3H	15.49	16.94	15.86	17.27	17.63	15.00	16.45	15.37	16.78	17.14
	4H	16.13	17.50	16.53	17.85	18.23	15.64	17.01	16.04	17.36	17.73
	6H	16.60	17.87	17.01	18.24	18.63	16.10	17.37	16.51	17.74	18.13
	8H	16.75	17.96	17.17	18.35	18.75	16.24	17.45	16.67	17.84	18.24
	12H	16.84	18.00	17.27	18.38	18.81	16.32	17.48	16.75	17.87	18.30
4H	2H	14.30	15.67	14.70	16.02	16.39	13.95	15.31	14.34	15.66	16.04
	3H	16.27	17.42	16.68	17.82	18.22	15.87	17.01	16.28	17.41	17.81
	4H	17.05	18.09	17.48	18.50	18.94	16.63	17.66	17.06	18.08	18.51
	6H	17.65	18.55	18.10	18.99	19.45	17.21	18.12	17.67	18.56	19.02
	8H	17.84	18.68	18.30	19.12	19.59	17.40	18.24	17.86	18.69	19.15
	12H	17.97	18.73	18.45	19.20	19.67	17.52	18.28	18.00	18.75	19.22
8H	4H	17.32	18.17	17.78	18.61	19.08	16.95	17.80	17.41	18.24	18.70
	6H	18.04	18.74	18.53	19.23	19.70	17.66	18.36	18.15	18.85	19.32
	8H	18.30	18.93	18.81	19.43	19.92	17.91	18.54	18.42	19.04	19.53
	12H	18.50	19.05	19.00	19.55	20.11	18.08	18.64	18.59	19.13	19.69
12H	4H	17.35	18.11	17.83	18.58	19.05	16.98	17.74	17.46	18.22	18.69
	6H	18.08	18.71	18.59	19.22	19.71	17.71	18.35	18.22	18.85	19.34
	8H	18.40	18.95	18.90	19.45	20.01	18.02	18.58	18.53	19.07	19.63