

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930831

Luminaire Tested: DFN2DS-SQ2F0-050DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-050DS830-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4662.9 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 47.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930831

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930831

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4030	4030	4030
5°	4045	3987	4011
10°	4022	3947	3966
15°	3972	3895	3891
20°	3901	3819	3815
25°	3831	3724	3724
30°	3741	3638	3606
35°	3657	3534	3482
40°	3551	3429	3364
45°	3447	3326	3244
50°	3334	3219	3104
55°	3216	3094	2980
60°	3084	2946	2837
65°	2944	2797	2668
70°	2765	2617	2493
75°	2515	2409	2352
80°	2232	2164	2053
85°	1822	1736	1557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3447 cd/sqm

TEST NUMBER: P930831

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.5	3.7
10°-20°	485.3	10.4
20°-30°	713.2	15.3
30°-40°	828.4	17.8
40°-50°	827.4	17.7
50°-60°	721.4	15.5
60°-70°	533.3	11.4
70°-80°	301.7	6.5
80°-90°	79.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.1	29.4
0°-40°	2199.4	47.2
0°-60°	3748.2	80.4
0°-90°	4662.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4662.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1826	1806	1820	1817	174
15°	1745	1734	1711	1718	1709	491
25°	1579	1565	1535	1538	1535	727
35°	1362	1345	1316	1306	1297	851
45°	1108	1096	1070	1050	1043	856
55°	839	828	807	786	777	750
65°	566	555	538	522	513	559
75°	296	293	284	273	277	316
85°	72	70	69	63	62	85
90°	0	0	0	0	0	

TEST NUMBER: P930831

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.7	1832.7	1832.7	1832.7	1832.7
2.5°	1843.3	1834.5	1815.1	1832.7	1829.4
5°	1832.7	1825.8	1806.3	1820.3	1817.0
7.5°	1820.3	1809.9	1790.5	1804.7	1801.1
10°	1801.1	1788.8	1767.7	1781.6	1776.4
12.5°	1774.5	1764.1	1743.0	1751.7	1748.2
15°	1744.6	1734.1	1711.1	1718.3	1709.4
17.5°	1707.6	1697.1	1674.1	1682.9	1674.1
20°	1667.1	1656.6	1631.9	1637.1	1630.2
22.5°	1626.6	1610.7	1587.7	1587.7	1584.2
25°	1579.0	1564.9	1535.0	1538.4	1535.0
27.5°	1526.0	1513.7	1490.9	1485.6	1476.9
30°	1473.3	1459.2	1432.8	1427.5	1420.4
32.5°	1416.9	1406.4	1378.1	1367.5	1360.4
35°	1362.2	1344.7	1316.4	1305.8	1297.0
37.5°	1300.5	1284.7	1256.4	1244.1	1235.3
40°	1237.2	1223.0	1194.7	1179.0	1171.9
42.5°	1175.5	1161.3	1133.2	1115.4	1105.0
45°	1108.5	1096.2	1069.6	1050.4	1043.3
47.5°	1043.3	1030.9	1002.8	983.3	972.8
50°	974.5	965.7	941.1	916.4	907.5
52.5°	907.5	895.2	872.4	853.0	840.6
55°	838.9	828.3	807.1	786.0	777.2
57.5°	770.1	761.3	738.3	717.2	710.1
60°	701.3	694.4	669.8	650.3	645.1
62.5°	634.4	622.1	604.5	586.9	579.8
65°	565.8	555.1	537.5	521.7	512.8
67.5°	495.3	486.4	470.6	458.3	451.1
70°	430.0	423.0	407.0	394.7	387.8
72.5°	363.1	356.0	347.2	334.9	329.6
75°	296.0	292.6	283.6	273.2	276.8
77.5°	236.2	229.0	225.5	220.2	215.1
80°	176.3	174.5	170.9	165.7	162.1
82.5°	119.8	119.8	118.1	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.7	28.3	24.7	19.4	17.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930831

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.12	17.74	16.49	18.05	18.36	15.68	17.29	16.05	17.61	17.92
	3H	17.88	19.33	18.25	19.66	20.02	17.38	18.84	17.76	19.16	19.53
	4H	18.52	19.89	18.92	20.24	20.61	18.03	19.40	18.42	19.74	20.12
	6H	18.99	20.26	19.40	20.62	21.01	18.49	19.76	18.90	20.12	20.51
	8H	19.13	20.34	19.56	20.73	21.13	18.63	19.84	19.06	20.23	20.63
	12H	19.22	20.38	19.65	20.77	21.19	18.71	19.87	19.14	20.25	20.68
4H	2H	16.68	18.05	17.08	18.40	18.78	16.33	17.70	16.73	18.05	18.43
	3H	18.66	19.81	19.07	20.20	20.60	18.25	19.40	18.66	19.80	20.20
	4H	19.44	20.47	19.87	20.89	21.32	19.01	20.05	19.44	20.46	20.90
	6H	20.03	20.94	20.49	21.38	21.84	19.60	20.51	20.06	20.95	21.40
	8H	20.22	21.07	20.68	21.51	21.98	19.79	20.63	20.25	21.07	21.54
	12H	20.35	21.11	20.84	21.59	22.06	19.90	20.66	20.38	21.14	21.61
8H	4H	19.71	20.56	20.17	21.00	21.46	19.34	20.18	19.80	20.63	21.09
	6H	20.42	21.13	20.92	21.62	22.09	20.04	20.75	20.54	21.23	21.71
	8H	20.68	21.31	21.19	21.82	22.31	20.29	20.92	20.80	21.43	21.92
	12H	20.88	21.44	21.39	21.93	22.49	20.47	21.03	20.98	21.52	22.08
12H	4H	19.74	20.50	20.22	20.97	21.44	19.37	20.13	19.85	20.61	21.08
	6H	20.47	21.10	20.98	21.61	22.09	20.10	20.73	20.61	21.24	21.73
	8H	20.78	21.34	21.29	21.83	22.39	20.41	20.96	20.91	21.45	22.02