

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930832

Luminaire Tested: DFN2DS-SQ2F0-050DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-050DS830-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4003.5 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 47.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930832

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930832

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4280	4280	4280
5°	4297	4227	4250
10°	4264	4158	4122
15°	4215	4035	3918
20°	4147	3858	3665
25°	4077	3659	3419
30°	3981	3453	3104
35°	3887	3230	2828
40°	3792	2998	2508
45°	3682	2739	2218
50°	3568	2477	1935
55°	3451	2195	1662
60°	3316	1898	1379
65°	3162	1595	1255
70°	2979	1313	1155
75°	2754	1197	1078
80°	2431	1070	981
85°	1910	843	843

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3682 cd/sqm

TEST NUMBER: P930832

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.4	4.6
10°-20°	500.8	12.5
20°-30°	703.2	17.6
30°-40°	766.5	19.1
40°-50°	704.5	17.6
50°-60°	553.3	13.8
60°-70°	360.1	9.0
70°-80°	185.4	4.6
80°-90°	47.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1386.4	34.6
0°-40°	2152.9	53.8
0°-60°	3410.7	85.2
0°-90°	4003.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4003.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1938	1915	1931	1926	185
15°	1852	1832	1772	1739	1721	522
25°	1681	1624	1508	1436	1409	773
35°	1448	1358	1203	1092	1053	906
45°	1184	1066	881	756	713	914
55°	900	763	572	467	433	804
65°	608	465	306	247	241	603
75°	324	201	141	129	127	343
85°	76	39	33	33	33	91
90°	0	0	0	0	0	

TEST NUMBER: P930832

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1946.6	1946.6	1946.6	1946.6	1946.6
2.5°	1955.4	1946.6	1927.2	1944.9	1941.4
5°	1946.6	1937.9	1914.9	1930.7	1925.5
7.5°	1930.7	1920.3	1895.6	1902.6	1893.7
10°	1909.6	1897.3	1862.1	1856.8	1846.2
12.5°	1883.2	1867.4	1819.8	1809.3	1789.8
15°	1851.5	1832.1	1772.3	1738.8	1721.2
17.5°	1814.5	1786.3	1712.3	1673.6	1645.3
20°	1772.3	1737.0	1648.9	1605.0	1566.1
22.5°	1726.5	1685.9	1583.7	1523.9	1497.5
25°	1680.6	1624.2	1508.0	1435.8	1409.2
27.5°	1626.1	1566.1	1437.5	1354.7	1314.2
30°	1568.0	1500.9	1360.0	1270.2	1222.5
32.5°	1511.5	1430.4	1286.1	1180.3	1136.2
35°	1448.1	1358.3	1203.3	1092.2	1053.4
37.5°	1386.4	1289.5	1125.8	1004.1	960.2
40°	1321.2	1215.7	1044.6	919.6	873.8
42.5°	1254.4	1141.6	963.7	833.2	789.3
45°	1183.9	1065.8	880.9	755.7	713.4
47.5°	1116.9	991.9	801.6	676.5	637.7
50°	1043.0	917.9	724.1	602.4	565.6
52.5°	970.6	838.5	650.1	533.8	500.4
55°	900.2	762.7	572.5	466.9	433.4
57.5°	828.0	687.1	503.9	405.2	377.0
60°	754.0	613.1	431.5	341.9	313.6
62.5°	681.8	540.9	369.9	285.4	271.4
65°	607.8	465.1	306.5	246.7	241.3
67.5°	537.3	394.6	246.7	216.7	211.4
70°	463.4	325.9	204.3	186.7	179.6
72.5°	392.9	262.4	170.9	156.8	153.3
75°	324.1	200.7	140.9	128.6	126.9
77.5°	255.5	142.6	111.1	103.9	100.3
80°	192.0	102.2	84.5	77.5	77.5
82.5°	133.9	68.8	58.1	54.5	54.5
85°	75.7	38.7	33.4	33.4	33.4
87.5°	28.3	14.0	14.0	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930832

CATALOG NUMBER: DFN2DS-SQ2F0-050DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.29	17.81	16.65	18.12	18.44	12.25	13.77	12.61	14.08	14.40
	3H	18.05	19.42	18.43	19.74	20.11	13.51	14.88	13.89	15.21	15.57
	4H	18.72	20.00	19.12	20.35	20.73	14.01	15.29	14.41	15.64	16.02
	6H	19.21	20.39	19.62	20.76	21.15	14.39	15.58	14.81	15.94	16.34
	8H	19.37	20.50	19.80	20.89	21.29	14.52	15.65	14.95	16.03	16.44
	12H	19.48	20.55	19.91	20.94	21.37	14.60	15.68	15.03	16.06	16.49
4H	2H	16.39	17.67	16.79	18.02	18.40	12.94	14.22	13.34	14.57	14.95
	3H	18.32	19.39	18.73	19.79	20.19	14.39	15.45	14.80	15.85	16.25
	4H	19.07	20.03	19.51	20.45	20.88	14.99	15.94	15.42	16.36	16.80
	6H	19.67	20.50	20.12	20.94	21.40	15.47	16.30	15.93	16.75	17.21
	8H	19.88	20.66	20.34	21.10	21.57	15.63	16.41	16.10	16.86	17.32
	12H	20.03	20.73	20.52	21.21	21.68	15.75	16.45	16.23	16.92	17.40
8H	4H	19.10	19.87	19.56	20.32	20.79	15.34	16.12	15.80	16.56	17.03
	6H	19.74	20.38	20.23	20.87	21.35	15.93	16.57	16.42	17.06	17.54
	8H	19.99	20.56	20.50	21.07	21.56	16.15	16.72	16.66	17.23	17.72
	12H	20.19	20.70	20.70	21.19	21.76	16.32	16.83	16.83	17.33	17.89
12H	4H	19.08	19.78	19.56	20.25	20.73	15.38	16.08	15.86	16.56	17.03
	6H	19.72	20.29	20.23	20.80	21.29	15.99	16.57	16.50	17.08	17.56
	8H	20.00	20.51	20.51	21.00	21.57	16.26	16.77	16.77	17.26	17.83

END OF REPORT