

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930261

Luminaire Tested: DFN2DS-HX4F0-040DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-040DS850-FLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4391.7 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930261

CATALOG NUMBER: DFN2DS-HX4F0-040DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930261

CATALOG NUMBER: DFN2DS-HX4F0-040DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84		
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	71		
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	60		
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51		
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	45		
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	39		
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	35		
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31		
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28		
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1283	1283	1283
5°	1288	1270	1277
10°	1281	1257	1263
15°	1265	1241	1239
20°	1242	1216	1215
25°	1220	1186	1186
30°	1191	1159	1149
35°	1165	1125	1109
40°	1131	1092	1071
45°	1098	1059	1033
50°	1062	1025	989
55°	1024	985	949
60°	982	938	903
65°	938	891	850
70°	880	834	794
75°	801	768	749
80°	711	689	654
85°	580	553	496

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1098 cd/sqm

TEST NUMBER: P930261

CATALOG NUMBER: DFN2DS-HX4F0-040DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	3.7
10°-20°	457.1	10.4
20°-30°	671.7	15.3
30°-40°	780.2	17.8
40°-50°	779.2	17.7
50°-60°	679.5	15.5
60°-70°	502.3	11.4
70°-80°	284.2	6.5
80°-90°	75.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.3	29.4
0°-40°	2071.5	47.2
0°-60°	3530.2	80.4
0°-90°	4391.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4391.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P930261

CATALOG NUMBER: DFN2DS-HX4F0-040DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930261

CATALOG NUMBER: DFN2DS-HX4F0-040DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.15	13.76	12.51	14.07	14.39	11.71	13.32	12.07	13.63	13.94
	3H	13.90	15.35	14.28	15.68	16.04	13.41	14.86	13.79	15.19	15.55
	4H	14.55	15.92	14.94	16.26	16.64	14.05	15.42	14.45	15.77	16.14
	6H	15.02	16.28	15.43	16.65	17.04	14.51	15.78	14.92	16.15	16.54
	8H	15.16	16.37	15.58	16.76	17.16	14.66	15.87	15.08	16.26	16.65
	12H	15.25	16.41	15.68	16.79	17.22	14.74	15.90	15.17	16.28	16.71
4H	2H	12.71	14.08	13.11	14.43	14.80	12.36	13.73	12.76	14.07	14.45
	3H	14.69	15.83	15.10	16.23	16.63	14.28	15.42	14.69	15.82	16.22
	4H	15.46	16.50	15.89	16.91	17.35	15.04	16.07	15.47	16.49	16.92
	6H	16.06	16.96	16.51	17.40	17.86	15.63	16.53	16.08	16.97	17.43
	8H	16.25	17.09	16.71	17.54	18.00	15.81	16.66	16.27	17.10	17.56
	12H	16.38	17.14	16.86	17.62	18.08	15.93	16.69	16.41	17.16	17.63
8H	4H	15.74	16.58	16.20	17.02	17.49	15.36	16.21	15.82	16.65	17.12
	6H	16.45	17.15	16.94	17.64	18.12	16.07	16.77	16.56	17.26	17.73
	8H	16.71	17.34	17.22	17.85	18.33	16.32	16.95	16.83	17.45	17.94
	12H	16.91	17.47	17.42	17.96	18.52	16.50	17.05	17.00	17.54	18.10
12H	4H	15.76	16.52	16.24	17.00	17.47	15.40	16.16	15.88	16.63	17.10
	6H	16.49	17.13	17.00	17.63	18.12	16.13	16.76	16.64	17.26	17.75
	8H	16.81	17.37	17.32	17.86	18.42	16.43	16.99	16.94	17.48	18.04