

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930867

Luminaire Tested: DFN2DS-SQ2F0-070DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-070DS830-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6528.1 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930867

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930867

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5663	5582	5615
10°	5630	5525	5553
15°	5560	5453	5448
20°	5461	5346	5341
25°	5363	5214	5214
30°	5237	5093	5049
35°	5120	4947	4874
40°	4972	4801	4710
45°	4826	4657	4542
50°	4667	4507	4347
55°	4503	4332	4171
60°	4318	4124	3972
65°	4121	3916	3736
70°	3870	3663	3490
75°	3521	3374	3291
80°	3125	3030	2873
85°	2551	2432	2180

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4826 cd/sqm

TEST NUMBER: P930867

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.5	3.7
10°-20°	679.5	10.4
20°-30°	998.5	15.3
30°-40°	1159.7	17.8
40°-50°	1158.3	17.7
50°-60°	1010.0	15.5
60°-70°	746.6	11.4
70°-80°	422.4	6.5
80°-90°	111.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1919.5	29.4
0°-40°	3079.2	47.2
0°-60°	5247.5	80.4
0°-90°	6528.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6528.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2566	2566	2566	2566	2566	
5°	2566	2556	2529	2548	2544	244
15°	2442	2428	2396	2406	2393	688
25°	2211	2191	2149	2154	2149	1017
35°	1907	1883	1843	1828	1816	1191
45°	1552	1535	1498	1471	1461	1198
55°	1174	1160	1130	1100	1088	1050
65°	792	777	753	730	718	783
75°	414	410	397	382	387	442
85°	101	99	96	89	86	119
90°	0	0	0	0	0	

TEST NUMBER: P930867

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2565.7	2565.7	2565.7	2565.7	2565.7
2.5°	2580.7	2568.4	2541.1	2565.7	2561.0
5°	2565.7	2556.1	2528.9	2548.5	2543.8
7.5°	2548.5	2533.8	2506.6	2526.5	2521.5
10°	2521.5	2504.2	2474.6	2494.3	2487.0
12.5°	2484.3	2469.7	2440.2	2452.4	2447.4
15°	2442.5	2427.8	2395.6	2405.6	2393.2
17.5°	2390.6	2376.0	2343.8	2356.1	2343.8
20°	2333.8	2319.2	2284.6	2292.0	2282.3
22.5°	2277.3	2255.1	2222.8	2222.8	2217.8
25°	2210.6	2190.9	2149.1	2153.8	2149.1
27.5°	2136.5	2119.2	2087.3	2079.9	2067.6
30°	2062.7	2042.7	2005.9	1998.5	1988.6
32.5°	1983.6	1969.0	1929.4	1914.5	1904.5
35°	1907.2	1882.6	1843.0	1828.1	1815.8
37.5°	1820.8	1798.6	1759.0	1741.8	1729.4
40°	1732.1	1712.2	1672.6	1650.7	1640.7
42.5°	1645.7	1625.8	1586.5	1561.6	1547.0
45°	1551.9	1534.7	1497.5	1470.6	1460.6
47.5°	1460.6	1443.3	1403.8	1376.5	1361.9
50°	1364.3	1352.0	1317.4	1282.9	1270.6
52.5°	1270.6	1253.3	1221.4	1194.2	1176.8
55°	1174.5	1159.6	1130.0	1100.4	1088.1
57.5°	1078.2	1065.9	1033.7	1004.1	994.2
60°	981.8	972.1	937.7	910.4	903.1
62.5°	888.1	870.9	846.3	821.7	811.7
65°	792.1	777.2	752.6	730.3	718.0
67.5°	693.4	680.9	658.8	641.6	631.6
70°	602.0	592.1	569.8	552.6	542.9
72.5°	508.3	498.4	486.1	468.8	461.5
75°	414.4	409.7	397.1	382.5	387.4
77.5°	330.6	320.7	315.7	308.3	301.1
80°	246.8	244.3	239.3	231.9	226.9
82.5°	167.8	167.8	165.4	155.5	155.5
85°	101.1	98.7	96.4	88.7	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930867

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.29	18.90	17.66	19.22	19.53	16.85	18.46	17.21	18.77	19.09
	3H	19.04	20.50	19.42	20.83	21.19	18.55	20.01	18.93	20.33	20.69
	4H	19.69	21.06	20.09	21.41	21.78	19.20	20.56	19.59	20.91	21.29
	6H	20.16	21.43	20.57	21.79	22.18	19.66	20.93	20.07	21.29	21.68
	8H	20.30	21.51	20.73	21.90	22.30	19.80	21.01	20.22	21.40	21.80
	12H	20.39	21.55	20.82	21.93	22.36	19.88	21.04	20.31	21.42	21.85
4H	2H	17.85	19.22	18.25	19.57	19.95	17.50	18.87	17.90	19.22	19.59
	3H	19.83	20.98	20.24	21.37	21.77	19.42	20.57	19.83	20.97	21.37
	4H	20.61	21.64	21.04	22.06	22.49	20.18	21.22	20.61	21.63	22.07
	6H	21.20	22.11	21.66	22.55	23.00	20.77	21.67	21.22	22.12	22.57
	8H	21.39	22.24	21.85	22.68	23.15	20.95	21.80	21.41	22.24	22.71
	12H	21.52	22.28	22.00	22.76	23.23	21.07	21.83	21.55	22.31	22.78
8H	4H	20.88	21.73	21.34	22.17	22.63	20.51	21.35	20.97	21.79	22.26
	6H	21.59	22.30	22.09	22.79	23.26	21.21	21.92	21.71	22.40	22.88
	8H	21.85	22.48	22.36	22.99	23.48	21.46	22.09	21.97	22.60	23.08
	12H	22.05	22.61	22.56	23.10	23.66	21.64	22.20	22.15	22.69	23.25
12H	4H	20.91	21.67	21.39	22.14	22.61	20.54	21.30	21.02	21.78	22.25
	6H	21.64	22.27	22.15	22.78	23.26	21.27	21.90	21.78	22.41	22.90
	8H	21.95	22.51	22.46	23.00	23.56	21.58	22.13	22.08	22.62	23.18