

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930887

Luminaire Tested: DFN2DS-SQ2F0-080DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-080DS835-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930887

CATALOG NUMBER: DFN2DS-SQ2F0-080DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930887

CATALOG NUMBER: DFN2DS-SQ2F0-080DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6845	6845	6845
5°	6871	6772	6812
10°	6831	6704	6737
15°	6746	6616	6610
20°	6626	6486	6479
25°	6507	6326	6326
30°	6354	6179	6126
35°	6211	6002	5914
40°	6032	5825	5714
45°	5855	5650	5511
50°	5662	5468	5273
55°	5463	5256	5061
60°	5239	5002	4818
65°	5000	4750	4532
70°	4696	4445	4234
75°	4271	4093	3993
80°	3793	3676	3486
85°	3093	2949	2644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5855 cd/sqm

TEST NUMBER: P930887

CATALOG NUMBER: DFN2DS-SQ2F0-080DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	3.7
10°-20°	824.3	10.4
20°-30°	1211.5	15.3
30°-40°	1407.0	17.8
40°-50°	1405.3	17.7
50°-60°	1225.4	15.5
60°-70°	905.8	11.4
70°-80°	512.5	6.5
80°-90°	135.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2328.8	29.4
0°-40°	3735.8	47.2
0°-60°	6366.4	80.4
0°-90°	7920.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	144
90°	0	0	0	0	0	

TEST NUMBER: P930887

CATALOG NUMBER: DFN2DS-SQ2F0-080DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930887

CATALOG NUMBER: DFN2DS-SQ2F0-080DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.97	19.58	18.33	19.89	20.20	17.52	19.13	17.89	19.45	19.76
	3H	19.72	21.17	20.09	21.50	21.86	19.22	20.68	19.60	21.01	21.37
	4H	20.36	21.73	20.76	22.08	22.45	19.87	21.24	20.27	21.58	21.96
	6H	20.83	22.10	21.24	22.46	22.86	20.33	21.60	20.74	21.96	22.35
	8H	20.97	22.18	21.40	22.57	22.97	20.47	21.68	20.90	22.07	22.47
	12H	21.06	22.22	21.49	22.61	23.03	20.55	21.71	20.98	22.09	22.52
4H	2H	18.53	19.90	18.92	20.24	20.62	18.17	19.54	18.57	19.89	20.27
	3H	20.50	21.65	20.91	22.05	22.45	20.09	21.24	20.50	21.64	22.04
	4H	21.28	22.31	21.71	22.73	23.16	20.85	21.89	21.29	22.30	22.74
	6H	21.87	22.78	22.33	23.22	23.68	21.44	22.35	21.90	22.79	23.24
	8H	22.06	22.91	22.52	23.35	23.82	21.63	22.47	22.09	22.91	23.38
	12H	22.20	22.96	22.68	23.43	23.90	21.74	22.50	22.22	22.98	23.45
8H	4H	21.55	22.40	22.01	22.84	23.31	21.18	22.02	21.64	22.47	22.93
	6H	22.27	22.97	22.76	23.46	23.93	21.88	22.59	22.38	23.08	23.55
	8H	22.52	23.16	23.03	23.66	24.15	22.13	22.76	22.64	23.27	23.76
	12H	22.72	23.28	23.23	23.77	24.33	22.31	22.87	22.82	23.36	23.92
12H	4H	21.58	22.34	22.06	22.81	23.28	21.21	21.97	21.69	22.45	22.92
	6H	22.31	22.94	22.82	23.45	23.94	21.94	22.57	22.45	23.08	23.57
	8H	22.62	23.18	23.13	23.67	24.23	22.25	22.80	22.75	23.29	23.86