

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930336

Luminaire Tested: DFN2DS-HX4F0-080DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-080DS927-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5385.6 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930336

CATALOG NUMBER: DFN2DS-HX4F0-080DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930336

CATALOG NUMBER: DFN2DS-HX4F0-080DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1947	1947	1947
5°	1955	1923	1933
10°	1940	1891	1875
15°	1917	1835	1782
20°	1887	1755	1667
25°	1855	1664	1555
30°	1811	1571	1412
35°	1768	1469	1286
40°	1725	1364	1141
45°	1675	1246	1009
50°	1623	1127	880
55°	1570	998	756
60°	1508	863	627
65°	1439	725	571
70°	1355	597	525
75°	1253	545	491
80°	1106	487	447
85°	869	384	384

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1675 cd/sqm

TEST NUMBER: P930336

CATALOG NUMBER: DFN2DS-HX4F0-080DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.4	4.6
10°-20°	673.7	12.5
20°-30°	945.9	17.6
30°-40°	1031.1	19.1
40°-50°	947.7	17.6
50°-60°	744.3	13.8
60°-70°	484.4	9.0
70°-80°	249.4	4.6
80°-90°	63.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1865.1	34.6
0°-40°	2896.2	53.8
0°-60°	4588.1	85.2
0°-90°	5385.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5385.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2619	2607	2576	2597	2590	248
15°	2491	2464	2384	2339	2315	702
25°	2261	2185	2028	1932	1896	1040
35°	1948	1827	1619	1469	1417	1219
45°	1593	1434	1185	1016	960	1230
55°	1211	1026	770	628	583	1082
65°	818	626	412	332	325	811
75°	436	270	190	173	171	461
85°	102	52	45	45	45	122
90°	0	0	0	0	0	

TEST NUMBER: P930336

CATALOG NUMBER: DFN2DS-HX4F0-080DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2618.7	2618.7	2618.7	2618.7	2618.7
2.5°	2630.5	2618.7	2592.5	2616.4	2611.6
5°	2618.7	2606.9	2575.9	2597.3	2590.2
7.5°	2597.3	2583.2	2550.0	2559.3	2547.5
10°	2568.9	2552.3	2505.0	2497.7	2483.6
12.5°	2533.4	2512.1	2447.9	2433.8	2407.7
15°	2490.7	2464.5	2384.1	2339.1	2315.4
17.5°	2440.9	2402.9	2303.4	2251.3	2213.3
20°	2384.1	2336.6	2218.2	2159.1	2106.7
22.5°	2322.5	2267.9	2130.4	2049.9	2014.5
25°	2260.8	2185.0	2028.5	1931.5	1895.8
27.5°	2187.4	2106.7	1933.7	1822.4	1767.8
30°	2109.3	2019.0	1829.4	1708.7	1644.6
32.5°	2033.3	1924.2	1730.1	1587.8	1528.5
35°	1948.1	1827.1	1618.7	1469.4	1417.0
37.5°	1865.1	1734.6	1514.4	1350.7	1291.6
40°	1777.4	1635.3	1405.2	1237.0	1175.4
42.5°	1687.4	1535.8	1296.3	1120.9	1061.8
45°	1592.6	1433.7	1185.0	1016.5	959.7
47.5°	1502.6	1334.4	1078.4	909.9	857.9
50°	1402.9	1234.8	974.1	810.4	760.8
52.5°	1305.7	1127.9	874.4	718.1	673.1
55°	1210.9	1026.1	770.1	628.1	583.1
57.5°	1113.9	924.3	677.9	545.1	507.1
60°	1014.2	824.7	580.5	459.8	421.9
62.5°	917.2	727.6	497.6	384.0	365.1
65°	817.7	625.5	412.3	331.9	324.6
67.5°	722.9	530.8	331.9	291.4	284.4
70°	623.3	438.5	274.8	251.1	241.6
72.5°	528.5	353.0	229.8	211.0	206.2
75°	436.0	270.1	189.6	173.0	170.8
77.5°	343.7	191.8	149.4	139.8	135.0
80°	258.2	137.6	113.7	104.3	104.3
82.5°	180.0	92.5	78.2	73.4	73.4
85°	101.9	52.0	45.0	45.0	45.0
87.5°	37.9	18.8	18.8	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930336

CATALOG NUMBER: DFN2DS-HX4F0-080DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.55	15.07	13.92	15.39	15.70	9.51	11.03	9.88	11.35	11.66
	3H	15.32	16.68	15.69	17.01	17.37	10.78	12.14	11.15	12.47	12.83
	4H	15.98	17.26	16.38	17.61	17.99	11.28	12.56	11.68	12.91	13.29
	6H	16.47	17.65	16.88	18.02	18.41	11.66	12.84	12.07	13.21	13.60
	8H	16.64	17.76	17.06	18.15	18.55	11.78	12.91	12.21	13.30	13.70
	12H	16.74	17.82	17.17	18.20	18.63	11.86	12.94	12.29	13.32	13.75
4H	2H	13.65	14.93	14.05	15.28	15.66	10.21	11.49	10.61	11.84	12.21
	3H	15.59	16.65	16.00	17.05	17.45	11.65	12.71	12.06	13.11	13.51
	4H	16.34	17.29	16.77	17.71	18.15	12.25	13.20	12.68	13.62	14.06
	6H	16.93	17.76	17.39	18.20	18.66	12.74	13.57	13.19	14.01	14.47
	8H	17.14	17.92	17.61	18.36	18.83	12.90	13.68	13.36	14.12	14.59
	12H	17.30	17.99	17.78	18.47	18.94	13.02	13.71	13.50	14.19	14.66
8H	4H	16.36	17.14	16.82	17.58	18.05	12.60	13.38	13.07	13.82	14.29
	6H	17.00	17.64	17.50	18.13	18.61	13.19	13.83	13.69	14.32	14.80
	8H	17.25	17.83	17.76	18.34	18.82	13.41	13.99	13.92	14.50	14.98
	12H	17.45	17.96	17.96	18.45	19.02	13.59	14.10	14.10	14.59	15.16
12H	4H	16.35	17.04	16.83	17.52	17.99	12.65	13.34	13.13	13.82	14.29
	6H	16.98	17.56	17.49	18.07	18.55	13.25	13.83	13.77	14.34	14.83
	8H	17.26	17.77	17.77	18.27	18.83	13.53	14.04	14.03	14.53	15.09