

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930889

Luminaire Tested: DFN2DS-SQ2F0-080DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-080DS840-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7927.9 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930889

CATALOG NUMBER: DFN2DS-SQ2F0-080DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930889

CATALOG NUMBER: DFN2DS-SQ2F0-080DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6852	6852	6852
5°	6878	6779	6819
10°	6838	6710	6744
15°	6753	6623	6617
20°	6632	6493	6486
25°	6513	6332	6332
30°	6360	6185	6132
35°	6217	6008	5920
40°	6038	5831	5719
45°	5861	5655	5516
50°	5668	5473	5278
55°	5468	5261	5066
60°	5244	5007	4823
65°	5005	4755	4537
70°	4700	4450	4239
75°	4275	4098	3997
80°	3796	3680	3490
85°	3096	2952	2647

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5861 cd/sqm

TEST NUMBER: P930889

CATALOG NUMBER: DFN2DS-SQ2F0-080DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.3	3.7
10°-20°	825.2	10.4
20°-30°	1212.7	15.3
30°-40°	1408.4	17.8
40°-50°	1406.7	17.7
50°-60°	1226.6	15.5
60°-70°	906.7	11.4
70°-80°	513.0	6.5
80°-90°	135.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2331.1	29.4
0°-40°	3739.5	47.2
0°-60°	6372.8	80.4
0°-90°	7927.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7927.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3104	3071	3095	3089	296
15°	2966	2948	2909	2921	2906	835
25°	2685	2661	2610	2616	2610	1235
35°	2316	2286	2238	2220	2205	1446
45°	1885	1864	1819	1786	1774	1455
55°	1426	1408	1372	1336	1321	1275
65°	962	944	914	887	872	951
75°	503	498	482	464	470	537
85°	123	120	117	108	105	144
90°	0	0	0	0	0	

TEST NUMBER: P930889

CATALOG NUMBER: DFN2DS-SQ2F0-080DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3115.9	3115.9	3115.9	3115.9	3115.9
2.5°	3134.0	3119.1	3086.1	3115.9	3110.2
5°	3115.9	3104.2	3071.2	3095.0	3089.3
7.5°	3095.0	3077.2	3044.1	3068.3	3062.3
10°	3062.3	3041.2	3005.3	3029.1	3020.3
12.5°	3017.1	2999.3	2963.4	2978.3	2972.3
15°	2966.3	2948.4	2909.3	2921.4	2906.5
17.5°	2903.3	2885.5	2846.3	2861.4	2846.3
20°	2834.3	2816.5	2774.6	2783.5	2771.7
22.5°	2765.7	2738.6	2699.5	2699.5	2693.5
25°	2684.6	2660.8	2609.9	2615.6	2609.9
27.5°	2594.6	2573.7	2534.8	2525.9	2511.0
30°	2505.0	2480.8	2436.0	2427.1	2415.0
32.5°	2409.0	2391.2	2343.1	2325.0	2313.0
35°	2316.1	2286.3	2238.2	2220.1	2205.2
37.5°	2211.2	2184.2	2136.2	2115.2	2100.3
40°	2103.5	2079.3	2031.3	2004.6	1992.5
42.5°	1998.6	1974.4	1926.7	1896.5	1878.8
45°	1884.8	1863.8	1818.6	1785.9	1773.9
47.5°	1773.9	1752.9	1704.8	1671.8	1654.0
50°	1656.9	1641.9	1599.9	1558.0	1543.0
52.5°	1543.0	1522.0	1483.3	1450.2	1429.2
55°	1426.3	1408.2	1372.4	1336.4	1321.4
57.5°	1309.4	1294.5	1255.4	1219.4	1207.3
60°	1192.4	1180.7	1138.6	1105.6	1096.7
62.5°	1078.6	1057.7	1027.7	997.9	985.8
65°	962.0	943.8	913.9	886.9	872.0
67.5°	842.0	826.8	800.1	779.2	767.1
70°	731.1	719.0	692.1	671.1	659.3
72.5°	617.3	605.3	590.3	569.4	560.5
75°	503.2	497.5	482.3	464.5	470.5
77.5°	401.5	389.4	383.4	374.5	365.6
80°	299.8	296.6	290.6	281.7	275.6
82.5°	203.8	203.8	200.9	188.8	188.8
85°	122.7	119.8	117.0	107.8	104.9
87.5°	54.1	48.0	41.9	33.0	29.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930889

CATALOG NUMBER: DFN2DS-SQ2F0-080DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.97	19.58	18.33	19.89	20.21	17.52	19.14	17.89	19.45	19.76
	3H	19.72	21.17	20.10	21.50	21.86	19.23	20.68	19.60	21.01	21.37
	4H	20.37	21.73	20.76	22.08	22.46	19.87	21.24	20.27	21.59	21.96
	6H	20.83	22.10	21.25	22.47	22.86	20.33	21.60	20.74	21.97	22.36
	8H	20.98	22.19	21.40	22.58	22.98	20.47	21.69	20.90	22.07	22.47
	12H	21.07	22.23	21.50	22.61	23.04	20.56	21.72	20.99	22.10	22.53
4H	2H	18.53	19.90	18.93	20.25	20.62	18.18	19.55	18.57	19.89	20.27
	3H	20.50	21.65	20.91	22.05	22.45	20.10	21.24	20.51	21.64	22.04
	4H	21.28	22.32	21.71	22.73	23.17	20.86	21.89	21.29	22.31	22.74
	6H	21.88	22.78	22.33	23.22	23.68	21.45	22.35	21.90	22.79	23.25
	8H	22.07	22.91	22.53	23.36	23.82	21.63	22.48	22.09	22.92	23.38
	12H	22.20	22.96	22.68	23.43	23.90	21.75	22.51	22.23	22.98	23.45
8H	4H	21.55	22.40	22.01	22.84	23.31	21.18	22.03	21.64	22.47	22.93
	6H	22.27	22.97	22.76	23.46	23.94	21.89	22.59	22.38	23.08	23.55
	8H	22.53	23.16	23.04	23.67	24.15	22.14	22.77	22.65	23.27	23.76
	12H	22.73	23.29	23.23	23.78	24.34	22.31	22.87	22.82	23.36	23.92
12H	4H	21.58	22.34	22.06	22.82	23.29	21.22	21.98	21.70	22.45	22.92
	6H	22.31	22.95	22.82	23.45	23.94	21.95	22.58	22.46	23.08	23.57
	8H	22.63	23.19	23.13	23.68	24.24	22.25	22.81	22.76	23.30	23.86