

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930266

Luminaire Tested: DFN2DS-HX4F0-040DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-040DS930-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2771.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930266

CATALOG NUMBER: DFN2DS-HX4F0-040DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930266

CATALOG NUMBER: DFN2DS-HX4F0-040DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1002	1002	1002
5°	1006	989	995
10°	998	973	965
15°	986	944	917
20°	971	903	858
25°	954	856	800
30°	932	808	727
35°	910	756	662
40°	888	702	587
45°	862	641	519
50°	835	580	453
55°	808	514	389
60°	776	444	323
65°	740	373	294
70°	697	307	270
75°	644	280	253
80°	569	250	230
85°	447	197	197

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 862 cd/sqm

TEST NUMBER: P930266

CATALOG NUMBER: DFN2DS-HX4F0-040DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	4.6
10°-20°	346.7	12.5
20°-30°	486.7	17.6
30°-40°	530.5	19.1
40°-50°	487.6	17.6
50°-60°	382.9	13.8
60°-70°	249.3	9.0
70°-80°	128.3	4.6
80°-90°	32.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.6	34.6
0°-40°	1490.1	53.8
0°-60°	2360.7	85.2
0°-90°	2771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1347	1341	1325	1336	1333	128
15°	1282	1268	1227	1204	1191	361
25°	1163	1124	1044	994	975	535
35°	1002	940	833	756	729	627
45°	819	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	63
90°	0	0	0	0	0	

TEST NUMBER: P930266

CATALOG NUMBER: DFN2DS-HX4F0-040DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.4	1347.4	1347.4	1347.4	1347.4
2.5°	1353.5	1347.4	1333.9	1346.2	1343.7
5°	1347.4	1341.2	1325.4	1336.4	1332.8
7.5°	1336.4	1329.1	1312.1	1316.8	1310.8
10°	1321.8	1313.2	1288.8	1285.1	1277.9
12.5°	1303.5	1292.5	1259.5	1252.2	1238.8
15°	1281.5	1268.1	1226.7	1203.5	1191.4
17.5°	1255.9	1236.4	1185.1	1158.4	1138.8
20°	1226.7	1202.2	1141.2	1110.8	1083.9
22.5°	1195.0	1166.9	1096.1	1054.7	1036.5
25°	1163.2	1124.2	1043.7	993.8	975.4
27.5°	1125.5	1083.9	995.0	937.7	909.5
30°	1085.3	1038.8	941.2	879.1	846.2
32.5°	1046.2	990.1	890.1	817.0	786.4
35°	1002.4	940.1	832.8	756.0	729.1
37.5°	959.7	892.5	779.1	695.0	664.6
40°	914.5	841.4	723.1	636.5	604.8
42.5°	868.1	790.1	667.0	576.7	546.3
45°	819.4	737.7	609.7	523.1	493.8
47.5°	773.1	686.6	554.9	468.2	441.4
50°	721.8	635.3	501.1	417.0	391.4
52.5°	671.8	580.4	450.0	369.4	346.3
55°	623.1	528.0	396.3	323.1	300.0
57.5°	573.1	475.6	348.7	280.4	261.0
60°	521.8	424.3	298.7	236.6	217.1
62.5°	472.0	374.4	256.0	197.6	187.9
65°	420.7	321.8	212.1	170.7	167.0
67.5°	372.0	273.1	170.7	150.0	146.3
70°	320.7	225.6	141.4	129.3	124.3
72.5°	272.0	181.7	118.3	108.6	106.1
75°	224.3	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.4
80°	132.8	70.7	58.4	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.1	23.1	23.1
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930266

CATALOG NUMBER: DFN2DS-HX4F0-040DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.24	12.76	11.61	13.08	13.39	7.20	8.72	7.57	9.04	9.35
	3H	13.01	14.37	13.38	14.70	15.06	8.47	9.83	8.84	10.16	10.52
	4H	13.67	14.95	14.07	15.30	15.68	8.97	10.25	9.37	10.60	10.98
	6H	14.16	15.35	14.57	15.71	16.10	9.35	10.53	9.76	10.90	11.29
	8H	14.33	15.45	14.75	15.84	16.24	9.47	10.60	9.90	10.99	11.39
	12H	14.43	15.51	14.86	15.89	16.32	9.55	10.63	9.98	11.01	11.44
4H	2H	11.35	12.63	11.75	12.97	13.35	7.90	9.18	8.30	9.53	9.90
	3H	13.28	14.34	13.69	14.74	15.14	9.34	10.40	9.75	10.80	11.20
	4H	14.03	14.98	14.46	15.40	15.84	9.94	10.90	10.37	11.31	11.75
	6H	14.62	15.45	15.08	15.89	16.35	10.43	11.26	10.89	11.70	12.16
	8H	14.83	15.61	15.30	16.06	16.52	10.59	11.37	11.05	11.81	12.28
	12H	14.99	15.68	15.47	16.16	16.63	10.71	11.40	11.19	11.88	12.35
8H	4H	14.05	14.83	14.52	15.27	15.74	10.29	11.07	10.76	11.52	11.98
	6H	14.69	15.33	15.19	15.82	16.30	10.88	11.52	11.38	12.01	12.49
	8H	14.94	15.52	15.45	16.03	16.51	11.10	11.68	11.61	12.19	12.68
	12H	15.14	15.65	15.65	16.15	16.71	11.28	11.79	11.79	12.28	12.85
12H	4H	14.04	14.73	14.52	15.21	15.68	10.34	11.03	10.82	11.51	11.98
	6H	14.67	15.25	15.18	15.76	16.25	10.94	11.52	11.46	12.03	12.52
	8H	14.96	15.46	15.46	15.96	16.52	11.22	11.73	11.73	12.22	12.78