

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930838

Luminaire Tested: DFN2DS-SQ2F0-050DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-050DS850-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4713.3 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 47.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930838

CATALOG NUMBER: DFN2DS-SQ2F0-050DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930838

CATALOG NUMBER: DFN2DS-SQ2F0-050DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5039	5039	5039
5°	5058	4976	5004
10°	5020	4895	4853
15°	4962	4750	4613
20°	4882	4542	4314
25°	4800	4307	4025
30°	4687	4065	3654
35°	4577	3803	3329
40°	4465	3530	2953
45°	4334	3225	2612
50°	4200	2916	2278
55°	4063	2583	1956
60°	3903	2234	1624
65°	3723	1878	1478
70°	3507	1546	1360
75°	3242	1409	1269
80°	2862	1260	1156
85°	2250	994	994

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4334 cd/sqm

TEST NUMBER: P930838

CATALOG NUMBER: DFN2DS-SQ2F0-050DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	4.6
10°-20°	589.6	12.5
20°-30°	827.8	17.6
30°-40°	902.4	19.1
40°-50°	829.4	17.6
50°-60°	651.3	13.8
60°-70°	424.0	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1632.2	34.6
0°-40°	2534.6	53.8
0°-60°	4015.3	85.2
0°-90°	4713.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4713.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P930838

CATALOG NUMBER: DFN2DS-SQ2F0-050DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930838

CATALOG NUMBER: DFN2DS-SQ2F0-050DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.85	18.38	17.22	18.69	19.00	12.81	14.34	13.18	14.65	14.96
	3H	18.62	19.98	19.00	20.31	20.67	14.08	15.45	14.46	15.77	16.13
	4H	19.29	20.57	19.69	20.91	21.29	14.58	15.86	14.98	16.21	16.59
	6H	19.77	20.96	20.19	21.32	21.72	14.96	16.15	15.37	16.51	16.90
	8H	19.94	21.07	20.37	21.46	21.86	15.09	16.21	15.51	16.60	17.00
	12H	20.04	21.12	20.47	21.50	21.93	15.17	16.25	15.60	16.63	17.06
4H	2H	16.96	18.24	17.36	18.59	18.97	13.51	14.79	13.91	15.14	15.52
	3H	18.89	19.95	19.30	20.35	20.75	14.95	16.02	15.36	16.42	16.82
	4H	19.64	20.60	20.07	21.01	21.45	15.55	16.51	15.99	16.92	17.36
	6H	20.23	21.06	20.69	21.51	21.97	16.04	16.87	16.50	17.32	17.77
	8H	20.45	21.22	20.91	21.67	22.14	16.20	16.98	16.67	17.42	17.89
	12H	20.60	21.30	21.08	21.77	22.24	16.32	17.01	16.80	17.49	17.96
8H	4H	19.66	20.44	20.13	20.89	21.35	15.91	16.68	16.37	17.13	17.60
	6H	20.30	20.94	20.80	21.44	21.91	16.49	17.14	16.99	17.63	18.10
	8H	20.55	21.13	21.07	21.64	22.13	16.71	17.29	17.23	17.80	18.29
	12H	20.76	21.27	21.27	21.76	22.32	16.89	17.40	17.40	17.89	18.46
12H	4H	19.65	20.34	20.13	20.82	21.29	15.95	16.64	16.43	17.12	17.59
	6H	20.28	20.86	20.80	21.37	21.86	16.56	17.13	17.07	17.64	18.13
	8H	20.57	21.08	21.08	21.57	22.13	16.83	17.34	17.34	17.83	18.40