

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930806

Luminaire Tested: DFN2DS-SQ2F0-030DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-030DS930-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2078.2 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930806

CATALOG NUMBER: DFN2DS-SQ2F0-030DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930806

CATALOG NUMBER: DFN2DS-SQ2F0-030DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2222	2222	2222
5°	2230	2194	2206
10°	2213	2158	2140
15°	2188	2094	2034
20°	2153	2003	1902
25°	2117	1899	1775
30°	2067	1793	1611
35°	2018	1677	1468
40°	1969	1557	1302
45°	1911	1422	1152
50°	1852	1286	1004
55°	1791	1139	863
60°	1721	985	716
65°	1642	828	652
70°	1546	681	599
75°	1429	622	560
80°	1262	555	510
85°	992	439	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1911 cd/sqm

TEST NUMBER: P930806

CATALOG NUMBER: DFN2DS-SQ2F0-030DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	4.6
10°-20°	260.0	12.5
20°-30°	365.0	17.6
30°-40°	397.9	19.1
40°-50°	365.7	17.6
50°-60°	287.2	13.8
60°-70°	186.9	9.0
70°-80°	96.2	4.6
80°-90°	24.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	719.7	34.6
0°-40°	1117.6	53.8
0°-60°	1770.5	85.2
0°-90°	2078.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2078.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1010	1010	1010	1010	1010	
5°	1010	1006	994	1002	1000	96
15°	961	951	920	903	894	271
25°	872	843	783	745	732	401
35°	752	705	625	567	547	471
45°	615	553	457	392	370	475
55°	467	396	297	242	225	418
65°	316	241	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	47
90°	0	0	0	0	0	

TEST NUMBER: P930806

CATALOG NUMBER: DFN2DS-SQ2F0-030DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.5	1010.5	1010.5	1010.5	1010.5
2.5°	1015.1	1010.5	1000.4	1009.6	1007.8
5°	1010.5	1006.0	994.1	1002.3	999.5
7.5°	1002.3	996.8	984.0	987.6	983.1
10°	991.3	984.9	966.7	963.8	958.4
12.5°	977.6	969.4	944.7	939.2	929.1
15°	961.1	951.0	920.0	902.6	893.5
17.5°	941.9	927.3	888.8	868.8	854.1
20°	920.0	901.6	855.9	833.2	813.0
22.5°	896.3	875.1	822.1	791.0	777.3
25°	872.5	843.1	782.8	745.3	731.5
27.5°	844.1	813.0	746.2	703.3	682.2
30°	813.9	779.1	706.0	659.4	634.6
32.5°	784.6	742.5	667.6	612.7	589.8
35°	751.8	705.1	624.6	567.0	546.9
37.5°	719.7	669.4	584.4	521.2	498.5
40°	685.9	631.1	542.3	477.3	453.6
42.5°	651.1	592.7	500.2	432.5	409.7
45°	614.6	553.2	457.3	392.3	370.3
47.5°	579.8	514.9	416.1	351.1	331.1
50°	541.4	476.4	375.9	312.7	293.6
52.5°	503.8	435.3	337.5	277.1	259.7
55°	467.2	395.9	297.1	242.4	225.0
57.5°	429.8	356.6	261.6	210.4	195.7
60°	391.4	318.3	224.0	177.4	162.8
62.5°	354.0	280.8	192.0	148.2	140.9
65°	315.5	241.4	159.1	128.0	125.3
67.5°	279.0	204.8	128.0	112.5	109.7
70°	240.5	169.2	106.0	96.9	93.2
72.5°	203.9	136.2	88.7	81.4	79.5
75°	168.2	104.2	73.2	66.7	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.8	40.3	40.3
82.5°	69.4	35.7	30.2	28.4	28.4
85°	39.3	20.0	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930806

CATALOG NUMBER: DFN2DS-SQ2F0-030DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.01	15.53	14.37	15.84	16.16	9.97	11.49	10.34	11.81	12.12
	3H	15.77	17.14	16.15	17.47	17.83	11.23	12.60	11.61	12.93	13.29
	4H	16.44	17.72	16.84	18.07	18.45	11.74	13.02	12.14	13.37	13.74
	6H	16.93	18.11	17.34	18.48	18.87	12.12	13.30	12.53	13.67	14.06
	8H	17.09	18.22	17.52	18.61	19.01	12.24	13.37	12.67	13.76	14.16
	12H	17.20	18.28	17.63	18.66	19.09	12.32	13.40	12.75	13.78	14.21
4H	2H	14.11	15.39	14.51	15.74	16.12	10.67	11.95	11.07	12.29	12.67
	3H	16.05	17.11	16.46	17.51	17.91	12.11	13.17	12.52	13.57	13.97
	4H	16.79	17.75	17.23	18.17	18.61	12.71	13.66	13.14	14.08	14.52
	6H	17.39	18.22	17.84	18.66	19.12	13.20	14.03	13.65	14.47	14.93
	8H	17.60	18.38	18.06	18.82	19.29	13.36	14.14	13.82	14.58	15.05
	12H	17.75	18.45	18.24	18.93	19.40	13.48	14.17	13.96	14.65	15.12
8H	4H	16.82	17.60	17.28	18.04	18.51	13.06	13.84	13.52	14.28	14.75
	6H	17.46	18.10	17.95	18.59	19.07	13.65	14.29	14.14	14.78	15.26
	8H	17.71	18.28	18.22	18.79	19.28	13.87	14.45	14.38	14.96	15.44
	12H	17.91	18.42	18.42	18.91	19.48	14.05	14.56	14.56	15.05	15.62
12H	4H	16.80	17.50	17.29	17.98	18.45	13.10	13.80	13.59	14.28	14.75
	6H	17.44	18.02	17.95	18.52	19.01	13.71	14.29	14.23	14.80	15.29
	8H	17.72	18.23	18.23	18.72	19.29	13.99	14.50	14.50	14.99	15.55