

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930359

Luminaire Tested: DFN2DS-HX4F0-090DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-090DS940-FLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7947.7 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 93.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930359

CATALOG NUMBER: DFN2DS-HX4F0-090DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930359

CATALOG NUMBER: DFN2DS-HX4F0-090DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2323	2323	2323
5°	2332	2298	2312
10°	2318	2275	2286
15°	2289	2245	2243
20°	2248	2201	2199
25°	2208	2147	2147
30°	2156	2097	2079
35°	2108	2037	2007
40°	2047	1977	1939
45°	1987	1917	1870
50°	1921	1855	1789
55°	1854	1783	1717
60°	1778	1698	1635
65°	1697	1612	1538
70°	1594	1508	1437
75°	1449	1389	1355
80°	1287	1247	1183
85°	1049	1001	898

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1987 cd/sqm

TEST NUMBER: P930359

CATALOG NUMBER: DFN2DS-HX4F0-090DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.0	3.7
10°-20°	827.2	10.4
20°-30°	1215.7	15.3
30°-40°	1412.0	17.8
40°-50°	1410.2	17.7
50°-60°	1229.7	15.5
60°-70°	909.0	11.4
70°-80°	514.3	6.5
80°-90°	135.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2336.9	29.4
0°-40°	3748.9	47.2
0°-60°	6388.7	80.4
0°-90°	7947.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7947.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3124	3124	3124	3124	3124	
5°	3124	3112	3079	3103	3097	297
15°	2974	2956	2917	2929	2914	837
25°	2691	2667	2616	2622	2616	1238
35°	2322	2292	2244	2226	2211	1450
45°	1889	1868	1823	1790	1778	1458
55°	1430	1412	1376	1340	1325	1278
65°	964	946	916	889	874	953
75°	504	499	484	466	472	539
85°	123	120	117	108	105	145
90°	0	0	0	0	0	

TEST NUMBER: P930359

CATALOG NUMBER: DFN2DS-HX4F0-090DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3123.7	3123.7	3123.7	3123.7	3123.7
2.5°	3141.9	3126.9	3093.8	3123.7	3118.0
5°	3123.7	3111.9	3078.8	3102.7	3096.9
7.5°	3102.7	3084.9	3051.7	3076.0	3069.9
10°	3069.9	3048.9	3012.8	3036.7	3027.8
12.5°	3024.6	3006.8	2970.8	2985.7	2979.7
15°	2973.7	2955.8	2916.6	2928.7	2913.7
17.5°	2910.5	2892.7	2853.5	2868.5	2853.5
20°	2841.4	2823.5	2781.4	2790.4	2778.6
22.5°	2772.5	2745.5	2706.2	2706.2	2700.2
25°	2691.3	2667.3	2616.4	2622.1	2616.4
27.5°	2601.1	2580.0	2541.2	2532.3	2517.3
30°	2511.2	2487.0	2442.0	2433.1	2421.1
32.5°	2415.0	2397.2	2349.0	2330.9	2318.8
35°	2322.0	2292.0	2243.8	2225.7	2210.7
37.5°	2216.8	2189.7	2141.5	2120.6	2105.6
40°	2108.7	2084.5	2036.3	2009.6	1997.5
42.5°	2003.5	1979.3	1931.5	1901.3	1883.5
45°	1889.4	1868.5	1823.2	1790.3	1778.3
47.5°	1778.3	1757.2	1709.1	1676.0	1658.1
50°	1661.0	1646.0	1603.9	1561.9	1546.9
52.5°	1546.9	1525.9	1487.0	1453.9	1432.8
55°	1430.0	1411.8	1375.7	1339.8	1324.8
57.5°	1312.7	1297.7	1258.5	1222.5	1210.4
60°	1195.4	1183.6	1141.5	1108.4	1099.5
62.5°	1081.3	1060.2	1030.3	1000.4	988.2
65°	964.3	946.1	916.2	889.1	874.2
67.5°	844.2	828.9	802.1	781.1	769.0
70°	733.0	720.8	693.8	672.7	661.0
72.5°	618.9	606.7	591.8	570.8	561.9
75°	504.5	498.7	483.5	465.6	471.7
77.5°	402.5	390.4	384.4	375.4	366.5
80°	300.5	297.3	291.2	282.3	276.3
82.5°	204.3	204.3	201.4	189.3	189.3
85°	123.0	120.2	117.3	108.0	105.2
87.5°	54.1	48.1	42.1	33.2	30.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930359

CATALOG NUMBER: DFN2DS-HX4F0-090DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.21	15.82	14.58	16.14	16.45	13.77	15.38	14.13	15.69	16.01
	3H	15.96	17.42	16.34	17.74	18.10	15.47	16.92	15.85	17.25	17.61
	4H	16.61	17.98	17.01	18.32	18.70	16.11	17.48	16.51	17.83	18.21
	6H	17.08	18.34	17.49	18.71	19.10	16.57	17.84	16.99	18.21	18.60
	8H	17.22	18.43	17.64	18.82	19.22	16.72	17.93	17.14	18.32	18.72
	12H	17.31	18.47	17.74	18.85	19.28	16.80	17.96	17.23	18.34	18.77
4H	2H	14.77	16.14	15.17	16.49	16.86	14.42	15.79	14.82	16.14	16.51
	3H	16.75	17.89	17.16	18.29	18.69	16.34	17.49	16.75	17.88	18.28
	4H	17.52	18.56	17.95	18.97	19.41	17.10	18.13	17.53	18.55	18.98
	6H	18.12	19.02	18.57	19.46	19.92	17.69	18.59	18.14	19.03	19.49
	8H	18.31	19.15	18.77	19.60	20.06	17.87	18.72	18.33	19.16	19.62
	12H	18.44	19.20	18.92	19.68	20.15	17.99	18.75	18.47	19.22	19.69
8H	4H	17.80	18.64	18.26	19.08	19.55	17.42	18.27	17.88	18.71	19.18
	6H	18.51	19.21	19.00	19.70	20.18	18.13	18.83	18.62	19.32	19.80
	8H	18.77	19.40	19.28	19.91	20.39	18.38	19.01	18.89	19.52	20.00
	12H	18.97	19.53	19.48	20.02	20.58	18.56	19.11	19.06	19.60	20.17
12H	4H	17.82	18.58	18.30	19.06	19.53	17.46	18.22	17.94	18.69	19.16
	6H	18.56	19.19	19.07	19.69	20.18	18.19	18.82	18.70	19.33	19.81
	8H	18.87	19.43	19.38	19.92	20.48	18.49	19.05	19.00	19.54	20.10