

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930862

Luminaire Tested: DFN2DS-SQ2F0-060DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-060DS935-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4386.0 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 58.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930862

CATALOG NUMBER: DFN2DS-SQ2F0-060DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930862

CATALOG NUMBER: DFN2DS-SQ2F0-060DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4689	4689	4689
5°	4707	4630	4656
10°	4671	4555	4516
15°	4618	4420	4292
20°	4543	4227	4015
25°	4467	4008	3746
30°	4362	3783	3401
35°	4259	3539	3098
40°	4155	3285	2748
45°	4033	3001	2431
50°	3909	2714	2120
55°	3781	2404	1820
60°	3633	2079	1511
65°	3465	1747	1376
70°	3263	1439	1265
75°	3017	1312	1182
80°	2663	1171	1076
85°	2092	923	923

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4033 cd/sqm

TEST NUMBER: P930862

CATALOG NUMBER: DFN2DS-SQ2F0-060DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	4.6
10°-20°	548.7	12.5
20°-30°	770.3	17.6
30°-40°	839.7	19.1
40°-50°	771.8	17.6
50°-60°	606.1	13.8
60°-70°	394.5	9.0
70°-80°	203.1	4.6
80°-90°	51.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.9	34.6
0°-40°	2358.6	53.8
0°-60°	3736.5	85.2
0°-90°	4386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2133	2133	2133	2133	2133	
5°	2133	2123	2098	2115	2110	202
15°	2028	2007	1942	1905	1886	572
25°	1841	1779	1652	1573	1544	847
35°	1586	1488	1318	1197	1154	993
45°	1297	1168	965	828	782	1002
55°	986	836	627	512	475	881
65°	666	510	336	270	264	660
75°	355	220	154	141	139	376
85°	83	42	37	37	37	99
90°	0	0	0	0	0	

TEST NUMBER: P930862

CATALOG NUMBER: DFN2DS-SQ2F0-060DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2132.6	2132.6	2132.6	2132.6	2132.6
2.5°	2142.3	2132.6	2111.3	2130.7	2126.9
5°	2132.6	2123.0	2097.8	2115.3	2109.5
7.5°	2115.3	2103.7	2076.7	2084.3	2074.7
10°	2092.0	2078.5	2040.1	2034.2	2022.6
12.5°	2063.2	2045.8	1993.6	1982.1	1960.8
15°	2028.4	2007.1	1941.5	1904.9	1885.6
17.5°	1987.9	1956.9	1875.8	1833.4	1802.6
20°	1941.5	1902.8	1806.4	1758.3	1715.7
22.5°	1891.4	1846.9	1735.0	1669.4	1640.5
25°	1841.3	1779.4	1652.1	1573.0	1544.0
27.5°	1781.5	1715.7	1574.8	1484.1	1439.7
30°	1717.8	1644.2	1489.9	1391.6	1339.4
32.5°	1655.9	1567.1	1409.0	1293.1	1244.8
35°	1586.5	1488.1	1318.3	1196.6	1154.0
37.5°	1518.9	1412.6	1233.3	1100.0	1051.9
40°	1447.5	1331.8	1144.4	1007.4	957.3
42.5°	1374.2	1250.7	1055.7	912.8	864.7
45°	1297.0	1167.5	965.1	827.8	781.6
47.5°	1223.7	1086.7	878.2	741.1	698.7
50°	1142.6	1005.6	793.3	660.0	619.6
52.5°	1063.3	918.6	712.2	584.8	548.2
55°	986.2	835.7	627.2	511.5	474.8
57.5°	907.1	752.7	552.0	443.9	413.0
60°	826.0	671.7	472.8	374.5	343.6
62.5°	747.0	592.6	405.2	312.7	297.3
65°	665.9	509.5	335.8	270.3	264.4
67.5°	588.7	432.2	270.3	237.4	231.6
70°	507.6	357.1	223.8	204.6	196.8
72.5°	430.4	287.5	187.1	171.8	167.9
75°	355.1	219.9	154.4	140.9	139.1
77.5°	279.9	156.3	121.6	113.9	110.0
80°	210.3	112.0	92.5	85.0	85.0
82.5°	146.6	75.3	63.6	59.8	59.8
85°	82.9	42.4	36.6	36.6	36.6
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930862

CATALOG NUMBER: DFN2DS-SQ2F0-060DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.60	18.13	16.97	18.44	18.75	12.56	14.09	12.93	14.40	14.71
	3H	18.37	19.73	18.75	20.06	20.42	13.83	15.19	14.21	15.52	15.88
	4H	19.04	20.32	19.43	20.66	21.04	14.33	15.61	14.73	15.96	16.34
	6H	19.52	20.71	19.94	21.07	21.47	14.71	15.90	15.12	16.26	16.65
	8H	19.69	20.82	20.12	21.21	21.61	14.84	15.96	15.26	16.35	16.75
	12H	19.79	20.87	20.22	21.25	21.68	14.92	16.00	15.35	16.38	16.81
4H	2H	16.71	17.99	17.11	18.34	18.72	13.26	14.54	13.66	14.89	15.27
	3H	18.64	19.70	19.05	20.10	20.50	14.70	15.77	15.11	16.17	16.57
	4H	19.39	20.35	19.82	20.76	21.20	15.30	16.26	15.74	16.67	17.11
	6H	19.98	20.81	20.44	21.26	21.72	15.79	16.62	16.25	17.07	17.53
	8H	20.20	20.97	20.66	21.42	21.89	15.95	16.73	16.42	17.17	17.64
	12H	20.35	21.04	20.83	21.52	21.99	16.07	16.76	16.55	17.24	17.71
8H	4H	19.41	20.19	19.88	20.64	21.10	15.66	16.43	16.12	16.88	17.35
	6H	20.05	20.69	20.55	21.19	21.66	16.24	16.89	16.74	17.38	17.85
	8H	20.30	20.88	20.82	21.39	21.88	16.46	17.04	16.98	17.55	18.04
	12H	20.51	21.02	21.02	21.51	22.07	16.64	17.15	17.15	17.65	18.21
12H	4H	19.40	20.09	19.88	20.57	21.04	15.70	16.39	16.18	16.87	17.34
	6H	20.03	20.61	20.55	21.12	21.61	16.31	16.88	16.82	17.39	17.88
	8H	20.32	20.83	20.83	21.32	21.88	16.58	17.09	17.09	17.58	18.15