

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930879

Luminaire Tested: DFN2DS-SQ2F0-070DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-070DS935-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5959.8 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930879

CATALOG NUMBER: DFN2DS-SQ2F0-070DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930879

CATALOG NUMBER: DFN2DS-SQ2F0-070DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5151	5151	5151
5°	5170	5096	5126
10°	5140	5044	5070
15°	5076	4979	4974
20°	4986	4881	4876
25°	4897	4760	4760
30°	4781	4650	4610
35°	4674	4517	4450
40°	4539	4383	4300
45°	4406	4251	4146
50°	4261	4114	3968
55°	4110	3955	3808
60°	3942	3765	3626
65°	3763	3575	3411
70°	3533	3344	3186
75°	3214	3080	3005
80°	2853	2766	2624
85°	2329	2220	1991

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4406 cd/sqm

TEST NUMBER: P930879

CATALOG NUMBER: DFN2DS-SQ2F0-070DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.5	3.7
10°-20°	620.3	10.4
20°-30°	911.6	15.3
30°-40°	1058.8	17.8
40°-50°	1057.5	17.7
50°-60°	922.1	15.5
60°-70°	681.6	11.4
70°-80°	385.7	6.5
80°-90°	101.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1752.4	29.4
0°-40°	2811.2	47.2
0°-60°	4790.7	80.4
0°-90°	5959.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5959.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2342	2342	2342	2342	2342	
5°	2342	2334	2309	2327	2322	222
15°	2230	2216	2187	2196	2185	628
25°	2018	2000	1962	1966	1962	929
35°	1741	1719	1683	1669	1658	1087
45°	1417	1401	1367	1342	1333	1093
55°	1072	1059	1032	1005	993	959
65°	723	710	687	667	656	715
75°	378	374	362	349	354	404
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P930879

CATALOG NUMBER: DFN2DS-SQ2F0-070DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2342.4	2342.4	2342.4	2342.4	2342.4
2.5°	2356.1	2344.8	2319.9	2342.4	2338.1
5°	2342.4	2333.6	2308.8	2326.6	2322.3
7.5°	2326.6	2313.2	2288.4	2306.6	2302.0
10°	2302.0	2286.2	2259.2	2277.2	2270.5
12.5°	2268.1	2254.7	2227.7	2238.9	2234.4
15°	2229.9	2216.5	2187.1	2196.2	2184.9
17.5°	2182.5	2169.2	2139.8	2151.0	2139.8
20°	2130.6	2117.3	2085.8	2092.5	2083.6
22.5°	2079.0	2058.8	2029.3	2029.3	2024.8
25°	2018.2	2000.2	1962.0	1966.3	1962.0
27.5°	1950.5	1934.7	1905.6	1898.9	1887.6
30°	1883.1	1864.9	1831.3	1824.6	1815.5
32.5°	1810.9	1797.6	1761.5	1747.9	1738.7
35°	1741.2	1718.7	1682.6	1669.0	1657.7
37.5°	1662.3	1642.0	1605.9	1590.1	1578.9
40°	1581.3	1563.1	1527.0	1507.0	1497.9
42.5°	1502.4	1484.3	1448.4	1425.7	1412.3
45°	1416.8	1401.1	1367.1	1342.5	1333.4
47.5°	1333.4	1317.7	1281.6	1256.7	1243.4
50°	1245.5	1234.3	1202.7	1171.2	1160.0
52.5°	1160.0	1144.2	1115.1	1090.2	1074.4
55°	1072.2	1058.7	1031.7	1004.7	993.4
57.5°	984.4	973.1	943.7	916.7	907.6
60°	896.4	887.5	856.0	831.2	824.5
62.5°	810.8	795.1	772.6	750.2	741.1
65°	723.2	709.5	687.1	666.8	655.5
67.5°	633.0	621.6	601.5	585.7	576.6
70°	549.6	540.6	520.2	504.5	495.6
72.5°	464.1	455.0	443.8	428.0	421.3
75°	378.3	374.0	362.5	349.2	353.7
77.5°	301.9	292.7	288.2	281.5	274.9
80°	225.3	223.0	218.4	211.7	207.2
82.5°	153.2	153.2	151.0	142.0	142.0
85°	92.3	90.1	88.0	81.0	78.9
87.5°	40.6	36.1	31.6	24.9	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930879

CATALOG NUMBER: DFN2DS-SQ2F0-070DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.98	18.59	17.34	18.90	19.22	16.53	18.14	16.90	18.46	18.77
	3H	18.73	20.18	19.10	20.51	20.87	18.24	19.69	18.61	20.02	20.38
	4H	19.37	20.74	19.77	21.09	21.47	18.88	20.25	19.28	20.60	20.97
	6H	19.84	21.11	20.25	21.48	21.87	19.34	20.61	19.75	20.97	21.37
	8H	19.99	21.20	20.41	21.59	21.99	19.48	20.69	19.91	21.08	21.48
	12H	20.08	21.24	20.51	21.62	22.05	19.56	20.72	19.99	21.11	21.53
4H	2H	17.54	18.91	17.94	19.25	19.63	17.19	18.55	17.58	18.90	19.28
	3H	19.51	20.66	19.92	21.06	21.46	19.11	20.25	19.52	20.65	21.05
	4H	20.29	21.33	20.72	21.74	22.18	19.87	20.90	20.30	21.32	21.75
	6H	20.89	21.79	21.34	22.23	22.69	20.45	21.36	20.91	21.80	22.26
	8H	21.08	21.92	21.54	22.36	22.83	20.64	21.48	21.10	21.93	22.39
	12H	21.21	21.97	21.69	22.44	22.91	20.76	21.52	21.24	21.99	22.46
8H	4H	20.56	21.41	21.02	21.85	22.32	20.19	21.04	20.65	21.48	21.94
	6H	21.28	21.98	21.77	22.47	22.94	20.90	21.60	21.39	22.09	22.56
	8H	21.54	22.17	22.05	22.67	23.16	21.14	21.78	21.65	22.28	22.77
	12H	21.74	22.29	22.24	22.78	23.35	21.32	21.88	21.83	22.37	22.93
12H	4H	20.59	21.35	21.07	21.82	22.29	20.22	20.98	20.70	21.46	21.93
	6H	21.32	21.95	21.83	22.46	22.95	20.95	21.59	21.46	22.09	22.58
	8H	21.64	22.19	22.14	22.68	23.25	21.26	21.82	21.77	22.31	22.87