

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930326

Luminaire Tested: DFN2DS-HX4F0-070DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-070DS950-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5622.7 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 71.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930326

CATALOG NUMBER: DFN2DS-HX4F0-070DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930326

CATALOG NUMBER: DFN2DS-HX4F0-070DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2033	2033	2033
5°	2041	2007	2019
10°	2025	1975	1958
15°	2002	1916	1861
20°	1970	1832	1740
25°	1937	1738	1624
30°	1891	1640	1474
35°	1846	1534	1343
40°	1801	1424	1191
45°	1748	1301	1054
50°	1694	1176	919
55°	1639	1042	789
60°	1575	901	655
65°	1502	757	596
70°	1415	624	548
75°	1308	569	512
80°	1154	508	467
85°	907	401	401

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1748 cd/sqm

TEST NUMBER: P930326

CATALOG NUMBER: DFN2DS-HX4F0-070DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.2	4.6
10°-20°	703.4	12.5
20°-30°	987.6	17.6
30°-40°	1076.5	19.1
40°-50°	989.4	17.6
50°-60°	777.0	13.8
60°-70°	505.8	9.0
70°-80°	260.3	4.6
80°-90°	66.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1947.2	34.6
0°-40°	3023.7	53.8
0°-60°	4790.2	85.2
0°-90°	5622.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5622.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2734	2734	2734	2734	2734	
5°	2734	2722	2689	2712	2704	259
15°	2600	2573	2489	2442	2417	733
25°	2360	2281	2118	2016	1979	1086
35°	2034	1908	1690	1534	1480	1273
45°	1663	1497	1237	1061	1002	1284
55°	1264	1071	804	656	609	1130
65°	854	653	430	346	339	846
75°	455	282	198	181	178	481
85°	106	54	47	47	47	127
90°	0	0	0	0	0	

TEST NUMBER: P930326

CATALOG NUMBER: DFN2DS-HX4F0-070DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2734.0	2734.0	2734.0	2734.0	2734.0
2.5°	2746.3	2734.0	2706.7	2731.6	2726.6
5°	2734.0	2721.6	2689.4	2711.7	2704.3
7.5°	2711.7	2696.9	2662.3	2672.0	2659.7
10°	2682.0	2664.7	2615.3	2607.7	2593.0
12.5°	2645.0	2622.7	2555.8	2541.0	2513.7
15°	2600.4	2573.0	2489.0	2442.1	2417.4
17.5°	2548.4	2508.8	2404.8	2350.4	2310.8
20°	2489.0	2439.4	2315.8	2254.1	2199.5
22.5°	2424.8	2367.8	2224.2	2140.1	2103.2
25°	2360.4	2281.1	2117.8	2016.5	1979.3
27.5°	2283.8	2199.5	2018.9	1902.7	1845.7
30°	2202.1	2107.9	1909.9	1784.0	1717.1
32.5°	2122.8	2009.0	1806.3	1657.7	1595.7
35°	2033.8	1907.6	1690.0	1534.1	1479.5
37.5°	1947.3	1811.0	1581.1	1410.1	1348.5
40°	1855.6	1707.3	1467.1	1291.5	1227.2
42.5°	1761.7	1603.4	1353.4	1170.2	1108.6
45°	1662.7	1496.8	1237.2	1061.3	1002.0
47.5°	1568.7	1393.1	1125.9	950.0	895.7
50°	1464.8	1289.2	1016.9	846.1	794.4
52.5°	1363.2	1177.6	913.0	749.7	702.7
55°	1264.2	1071.3	804.0	655.7	608.8
57.5°	1162.9	964.9	707.7	569.1	529.5
60°	1059.0	861.0	606.1	480.2	440.5
62.5°	957.6	759.7	519.5	400.9	381.1
65°	853.6	653.1	430.5	346.5	338.9
67.5°	754.7	554.1	346.5	304.2	296.9
70°	650.7	457.8	286.9	262.2	252.2
72.5°	551.8	368.5	239.9	220.3	215.3
75°	455.2	281.9	197.9	180.6	178.2
77.5°	358.8	200.2	155.9	145.9	141.0
80°	269.6	143.5	118.7	109.0	109.0
82.5°	188.0	96.6	81.6	76.6	76.6
85°	106.3	54.3	47.0	47.0	47.0
87.5°	39.6	19.7	19.7	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930326

CATALOG NUMBER: DFN2DS-HX4F0-070DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.70	15.22	14.06	15.53	15.85	9.66	11.18	10.03	11.50	11.81
	3H	15.46	16.83	15.84	17.16	17.52	10.93	12.29	11.30	12.62	12.98
	4H	16.13	17.41	16.53	17.76	18.14	11.43	12.71	11.83	13.06	13.43
	6H	16.62	17.80	17.03	18.17	18.56	11.81	12.99	12.22	13.36	13.75
	8H	16.79	17.91	17.21	18.30	18.70	11.93	13.06	12.36	13.45	13.85
	12H	16.89	17.97	17.32	18.35	18.78	12.01	13.09	12.44	13.47	13.90
4H	2H	13.80	15.08	14.20	15.43	15.81	10.36	11.64	10.76	11.99	12.36
	3H	15.74	16.80	16.15	17.20	17.60	11.80	12.86	12.21	13.26	13.66
	4H	16.49	17.44	16.92	17.86	18.30	12.40	13.35	12.83	13.77	14.21
	6H	17.08	17.91	17.53	18.35	18.81	12.89	13.72	13.34	14.16	14.62
	8H	17.29	18.07	17.76	18.51	18.98	13.05	13.83	13.51	14.27	14.74
	12H	17.45	18.14	17.93	18.62	19.09	13.17	13.86	13.65	14.34	14.81
8H	4H	16.51	17.29	16.97	17.73	18.20	12.75	13.53	13.22	13.97	14.44
	6H	17.15	17.79	17.64	18.28	18.76	13.34	13.98	13.84	14.47	14.95
	8H	17.40	17.97	17.91	18.48	18.97	13.56	14.14	14.07	14.65	15.13
	12H	17.60	18.11	18.11	18.60	19.17	13.74	14.25	14.25	14.74	15.31
12H	4H	16.49	17.19	16.98	17.67	18.14	12.80	13.49	13.28	13.97	14.44
	6H	17.13	17.71	17.64	18.22	18.70	13.40	13.98	13.92	14.49	14.98
	8H	17.41	17.92	17.92	18.41	18.98	13.68	14.18	14.18	14.68	15.24