

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930897

Luminaire Tested: DFN2DS-SQ2F0-080DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-080DS935-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6811.2 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930897

CATALOG NUMBER: DFN2DS-SQ2F0-080DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930897

CATALOG NUMBER: DFN2DS-SQ2F0-080DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5886	5886	5886
5°	5909	5824	5858
10°	5874	5765	5794
15°	5801	5690	5685
20°	5698	5578	5572
25°	5596	5440	5440
30°	5465	5314	5268
35°	5342	5162	5086
40°	5187	5010	4914
45°	5036	4859	4739
50°	4870	4702	4535
55°	4698	4520	4352
60°	4505	4302	4144
65°	4300	4085	3898
70°	4038	3823	3641
75°	3673	3520	3434
80°	3262	3162	2999
85°	2659	2536	2273

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5036 cd/sqm

TEST NUMBER: P930897

CATALOG NUMBER: DFN2DS-SQ2F0-080DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.0	3.7
10°-20°	708.9	10.4
20°-30°	1041.8	15.3
30°-40°	1210.0	17.8
40°-50°	1208.5	17.7
50°-60°	1053.8	15.5
60°-70°	779.0	11.4
70°-80°	440.7	6.5
80°-90°	116.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2002.7	29.4
0°-40°	3212.8	47.2
0°-60°	5475.1	80.4
0°-90°	6811.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6811.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2677	2677	2677	2677	2677	
5°	2677	2667	2639	2659	2654	254
15°	2548	2533	2500	2510	2497	718
25°	2306	2286	2242	2247	2242	1061
35°	1990	1964	1923	1907	1895	1243
45°	1619	1601	1562	1534	1524	1250
55°	1225	1210	1179	1148	1135	1096
65°	826	811	785	762	749	817
75°	432	427	414	399	404	462
85°	105	103	100	93	90	124
90°	0	0	0	0	0	

TEST NUMBER: P930897

CATALOG NUMBER: DFN2DS-SQ2F0-080DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2677.0	2677.0	2677.0	2677.0	2677.0
2.5°	2692.6	2679.8	2651.4	2677.0	2672.1
5°	2677.0	2666.9	2638.6	2659.0	2654.1
7.5°	2659.0	2643.7	2615.3	2636.1	2630.9
10°	2630.9	2612.9	2582.0	2602.4	2594.9
12.5°	2592.1	2576.8	2545.9	2558.8	2553.6
15°	2548.4	2533.1	2499.5	2509.9	2497.1
17.5°	2494.3	2479.0	2445.4	2458.3	2445.4
20°	2435.1	2419.8	2383.7	2391.4	2381.3
22.5°	2376.1	2352.9	2319.2	2319.2	2314.1
25°	2306.4	2286.0	2242.3	2247.2	2242.3
27.5°	2229.1	2211.1	2177.8	2170.1	2157.3
30°	2152.2	2131.3	2092.9	2085.2	2074.8
32.5°	2069.7	2054.4	2013.1	1997.5	1987.2
35°	1989.9	1964.2	1923.0	1907.4	1894.6
37.5°	1899.7	1876.5	1835.3	1817.3	1804.5
40°	1807.2	1786.4	1745.2	1722.2	1711.8
42.5°	1717.1	1696.3	1655.3	1629.4	1614.1
45°	1619.3	1601.2	1562.4	1534.3	1524.0
47.5°	1524.0	1505.9	1464.7	1436.3	1421.0
50°	1423.5	1410.7	1374.5	1338.5	1325.7
52.5°	1325.7	1307.6	1274.3	1246.0	1227.9
55°	1225.4	1209.8	1179.1	1148.2	1135.3
57.5°	1125.0	1112.2	1078.5	1047.7	1037.2
60°	1024.4	1014.4	978.2	949.9	942.2
62.5°	926.6	908.7	883.0	857.3	846.9
65°	826.5	810.9	785.2	762.0	749.1
67.5°	723.4	710.4	687.4	669.4	659.0
70°	628.1	617.7	594.6	576.5	566.4
72.5°	530.4	520.0	507.1	489.2	481.5
75°	432.3	427.4	414.3	399.0	404.2
77.5°	344.9	334.5	329.4	321.7	314.1
80°	257.6	254.8	249.7	242.0	236.8
82.5°	175.1	175.1	172.6	162.2	162.2
85°	105.4	102.9	100.5	92.6	90.1
87.5°	46.4	41.3	36.0	28.4	25.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930897

CATALOG NUMBER: DFN2DS-SQ2F0-080DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.44	19.05	17.81	19.37	19.68	17.00	18.61	17.36	18.92	19.24
	3H	19.19	20.65	19.57	20.97	21.33	18.70	20.15	19.08	20.48	20.84
	4H	19.84	21.21	20.24	21.55	21.93	19.34	20.71	19.74	21.06	21.44
	6H	20.31	21.58	20.72	21.94	22.33	19.81	21.07	20.22	21.44	21.83
	8H	20.45	21.66	20.87	22.05	22.45	19.95	21.16	20.37	21.55	21.95
	12H	20.54	21.70	20.97	22.08	22.51	20.03	21.19	20.46	21.57	22.00
4H	2H	18.00	19.37	18.40	19.72	20.10	17.65	19.02	18.05	19.37	19.74
	3H	19.98	21.12	20.39	21.52	21.92	19.57	20.72	19.98	21.11	21.51
	4H	20.75	21.79	21.18	22.20	22.64	20.33	21.37	20.76	21.78	22.22
	6H	21.35	22.25	21.80	22.70	23.15	20.92	21.82	21.37	22.26	22.72
	8H	21.54	22.39	22.00	22.83	23.29	21.10	21.95	21.56	22.39	22.86
	12H	21.67	22.43	22.15	22.91	23.38	21.22	21.98	21.70	22.45	22.92
8H	4H	21.03	21.87	21.49	22.32	22.78	20.65	21.50	21.11	21.94	22.41
	6H	21.74	22.44	22.23	22.93	23.41	21.36	22.06	21.85	22.55	23.03
	8H	22.00	22.63	22.51	23.14	23.62	21.61	22.24	22.12	22.75	23.23
	12H	22.20	22.76	22.71	23.25	23.81	21.79	22.34	22.29	22.84	23.40
12H	4H	21.05	21.81	21.53	22.29	22.76	20.69	21.45	21.17	21.92	22.39
	6H	21.79	22.42	22.30	22.93	23.41	21.42	22.05	21.93	22.56	23.04
	8H	22.10	22.66	22.61	23.15	23.71	21.72	22.28	22.23	22.77	23.33