

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930845

Luminaire Tested: DFN2DS-SQ2F0-050DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-050DS940-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4415.4 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 47.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930845

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930845

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3816	3816	3816
5°	3831	3775	3798
10°	3808	3737	3756
15°	3761	3689	3685
20°	3694	3616	3612
25°	3628	3526	3526
30°	3542	3445	3415
35°	3463	3346	3297
40°	3363	3247	3185
45°	3264	3150	3072
50°	3157	3048	2940
55°	3045	2930	2822
60°	2921	2789	2686
65°	2787	2648	2527
70°	2618	2478	2361
75°	2381	2282	2227
80°	2115	2049	1944
85°	1723	1642	1473

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3264 cd/sqm

TEST NUMBER: P930845

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	3.7
10°-20°	459.6	10.4
20°-30°	675.4	15.3
30°-40°	784.4	17.8
40°-50°	783.4	17.7
50°-60°	683.1	15.5
60°-70°	505.0	11.4
70°-80°	285.7	6.5
80°-90°	75.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.3	29.4
0°-40°	2082.7	47.2
0°-60°	3549.3	80.4
0°-90°	4415.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4415.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1729	1710	1724	1721	165
15°	1652	1642	1620	1627	1619	465
25°	1495	1482	1454	1457	1454	688
35°	1290	1273	1247	1236	1228	806
45°	1050	1038	1013	995	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	486	530
75°	280	277	269	259	262	299
85°	68	67	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P930845

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1735.4	1735.4	1735.4	1735.4	1735.4
2.5°	1745.5	1737.2	1718.8	1735.4	1732.3
5°	1735.4	1728.9	1710.4	1723.7	1720.6
7.5°	1723.7	1713.8	1695.4	1708.9	1705.5
10°	1705.5	1693.8	1673.8	1687.0	1682.1
12.5°	1680.3	1670.4	1650.5	1658.8	1655.4
15°	1652.0	1642.1	1620.3	1627.1	1618.7
17.5°	1616.9	1607.0	1585.3	1593.6	1585.3
20°	1578.6	1568.7	1545.3	1550.2	1543.7
22.5°	1540.3	1525.2	1503.5	1503.5	1500.1
25°	1495.2	1481.9	1453.5	1456.7	1453.5
27.5°	1445.0	1433.4	1411.8	1406.8	1398.5
30°	1395.1	1381.7	1356.7	1351.7	1345.0
32.5°	1341.7	1331.8	1305.0	1294.9	1288.2
35°	1289.9	1273.3	1246.6	1236.5	1228.2
37.5°	1231.5	1216.5	1189.7	1178.1	1169.8
40°	1171.6	1158.1	1131.3	1116.4	1109.7
42.5°	1113.1	1099.7	1073.1	1056.2	1046.3
45°	1049.7	1038.0	1012.9	994.7	987.9
47.5°	987.9	976.2	949.5	931.1	921.2
50°	922.8	914.5	891.1	867.7	859.4
52.5°	859.4	847.7	826.1	807.7	796.0
55°	794.4	784.3	764.3	744.3	736.0
57.5°	729.2	720.9	699.1	679.2	672.4
60°	664.1	657.6	634.2	615.7	610.8
62.5°	600.8	589.1	572.4	555.7	549.0
65°	535.7	525.7	509.0	494.0	485.6
67.5°	469.0	460.5	445.6	434.0	427.2
70°	407.2	400.5	385.4	373.7	367.2
72.5°	343.9	337.1	328.8	317.1	312.1
75°	280.3	277.1	268.6	258.7	262.1
77.5°	223.6	216.8	213.5	208.5	203.6
80°	167.0	165.2	161.8	156.9	153.5
82.5°	113.5	113.5	111.9	105.2	105.2
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930845

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.94	17.55	16.30	17.86	18.17	15.49	17.10	15.86	17.42	17.73
	3H	17.69	19.14	18.06	19.47	19.83	17.19	18.65	17.57	18.98	19.34
	4H	18.33	19.70	18.73	20.05	20.42	17.84	19.21	18.24	19.55	19.93
	6H	18.80	20.07	19.21	20.43	20.83	18.30	19.57	18.71	19.93	20.32
	8H	18.94	20.15	19.37	20.54	20.94	18.44	19.65	18.87	20.04	20.44
	12H	19.03	20.19	19.46	20.58	21.00	18.52	19.68	18.95	20.06	20.49
4H	2H	16.50	17.86	16.89	18.21	18.59	16.14	17.51	16.54	17.86	18.24
	3H	18.47	19.62	18.88	20.01	20.41	18.06	19.21	18.47	19.61	20.01
	4H	19.25	20.28	19.68	20.70	21.13	18.82	19.86	19.26	20.27	20.71
	6H	19.84	20.75	20.30	21.19	21.65	19.41	20.32	19.87	20.76	21.21
	8H	20.03	20.88	20.49	21.32	21.79	19.60	20.44	20.06	20.88	21.35
	12H	20.17	20.93	20.65	21.40	21.87	19.71	20.47	20.19	20.95	21.42
8H	4H	19.52	20.37	19.98	20.81	21.28	19.15	19.99	19.61	20.44	20.90
	6H	20.24	20.94	20.73	21.43	21.90	19.85	20.56	20.35	21.05	21.52
	8H	20.49	21.13	21.00	21.63	22.12	20.10	20.73	20.61	21.24	21.73
	12H	20.69	21.25	21.20	21.74	22.30	20.28	20.84	20.79	21.33	21.89
12H	4H	19.55	20.31	20.03	20.78	21.25	19.18	19.94	19.66	20.42	20.89
	6H	20.28	20.91	20.79	21.42	21.91	19.91	20.54	20.42	21.05	21.54
	8H	20.59	21.15	21.10	21.64	22.20	20.22	20.77	20.72	21.27	21.83