

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930472

Luminaire Tested: DFN2DS-PN2F0-050DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-050DS830-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4003.5 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930472

CATALOG NUMBER: DFN2DS-PN2F0-050DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930472

CATALOG NUMBER: DFN2DS-PN2F0-050DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4216	4216	4216
5°	4232	4163	4186
10°	4200	4095	4060
15°	4152	3974	3859
20°	4085	3801	3610
25°	4016	3604	3368
30°	3921	3401	3057
35°	3829	3182	2785
40°	3735	2953	2471
45°	3626	2698	2185
50°	3514	2440	1906
55°	3399	2162	1637
60°	3266	1869	1358
65°	3115	1571	1237
70°	2935	1294	1137
75°	2712	1179	1062
80°	2395	1054	967
85°	1881	830	830

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3626 cd/sqm

TEST NUMBER: P930472

CATALOG NUMBER: DFN2DS-PN2F0-050DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.4	4.6
10°-20°	500.8	12.5
20°-30°	703.2	17.6
30°-40°	766.5	19.1
40°-50°	704.5	17.6
50°-60°	553.3	13.8
60°-70°	360.1	9.0
70°-80°	185.4	4.6
80°-90°	47.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1386.4	34.6
0°-40°	2152.9	53.8
0°-60°	3410.7	85.2
0°-90°	4003.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4003.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1938	1915	1931	1926	185
15°	1852	1832	1772	1739	1721	522
25°	1681	1624	1508	1436	1409	773
35°	1448	1358	1203	1092	1053	906
45°	1184	1066	881	756	713	914
55°	900	763	572	467	433	804
65°	608	465	306	247	241	603
75°	324	201	141	129	127	343
85°	76	39	33	33	33	91
90°	0	0	0	0	0	

TEST NUMBER: P930472

CATALOG NUMBER: DFN2DS-PN2F0-050DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1946.6	1946.6	1946.6	1946.6	1946.6
2.5°	1955.4	1946.6	1927.2	1944.9	1941.4
5°	1946.6	1937.9	1914.9	1930.7	1925.5
7.5°	1930.7	1920.3	1895.6	1902.6	1893.7
10°	1909.6	1897.3	1862.1	1856.8	1846.2
12.5°	1883.2	1867.4	1819.8	1809.3	1789.8
15°	1851.5	1832.1	1772.3	1738.8	1721.2
17.5°	1814.5	1786.3	1712.3	1673.6	1645.3
20°	1772.3	1737.0	1648.9	1605.0	1566.1
22.5°	1726.5	1685.9	1583.7	1523.9	1497.5
25°	1680.6	1624.2	1508.0	1435.8	1409.2
27.5°	1626.1	1566.1	1437.5	1354.7	1314.2
30°	1568.0	1500.9	1360.0	1270.2	1222.5
32.5°	1511.5	1430.4	1286.1	1180.3	1136.2
35°	1448.1	1358.3	1203.3	1092.2	1053.4
37.5°	1386.4	1289.5	1125.8	1004.1	960.2
40°	1321.2	1215.7	1044.6	919.6	873.8
42.5°	1254.4	1141.6	963.7	833.2	789.3
45°	1183.9	1065.8	880.9	755.7	713.4
47.5°	1116.9	991.9	801.6	676.5	637.7
50°	1043.0	917.9	724.1	602.4	565.6
52.5°	970.6	838.5	650.1	533.8	500.4
55°	900.2	762.7	572.5	466.9	433.4
57.5°	828.0	687.1	503.9	405.2	377.0
60°	754.0	613.1	431.5	341.9	313.6
62.5°	681.8	540.9	369.9	285.4	271.4
65°	607.8	465.1	306.5	246.7	241.3
67.5°	537.3	394.6	246.7	216.7	211.4
70°	463.4	325.9	204.3	186.7	179.6
72.5°	392.9	262.4	170.9	156.8	153.3
75°	324.1	200.7	140.9	128.6	126.9
77.5°	255.5	142.6	111.1	103.9	100.3
80°	192.0	102.2	84.5	77.5	77.5
82.5°	133.9	68.8	58.1	54.5	54.5
85°	75.7	38.7	33.4	33.4	33.4
87.5°	28.3	14.0	14.0	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930472

CATALOG NUMBER: DFN2DS-PN2F0-050DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.23	17.76	16.60	18.07	18.38	12.19	13.72	12.56	14.03	14.34
	3H	18.00	19.36	18.38	19.69	20.05	13.46	14.83	13.84	15.15	15.51
	4H	18.67	19.95	19.07	20.30	20.67	13.96	15.24	14.36	15.59	15.97
	6H	19.15	20.34	19.57	20.70	21.10	14.34	15.52	14.75	15.89	16.28
	8H	19.32	20.45	19.75	20.84	21.24	14.47	15.59	14.89	15.98	16.38
	12H	19.42	20.50	19.85	20.88	21.31	14.55	15.63	14.98	16.01	16.44
4H	2H	16.34	17.62	16.74	17.97	18.35	12.89	14.17	13.29	14.52	14.90
	3H	18.27	19.33	18.68	19.73	20.14	14.33	15.40	14.74	15.80	16.20
	4H	19.02	19.98	19.45	20.39	20.83	14.93	15.89	15.37	16.30	16.74
	6H	19.61	20.44	20.07	20.89	21.35	15.42	16.25	15.88	16.69	17.15
	8H	19.83	20.60	20.29	21.05	21.52	15.58	16.36	16.05	16.80	17.27
	12H	19.98	20.68	20.46	21.15	21.62	15.70	16.39	16.18	16.87	17.34
8H	4H	19.04	19.82	19.51	20.27	20.73	15.29	16.06	15.75	16.51	16.98
	6H	19.68	20.32	20.18	20.82	21.29	15.87	16.51	16.37	17.01	17.48
	8H	19.93	20.51	20.45	21.02	21.51	16.09	16.67	16.61	17.18	17.67
	12H	20.14	20.65	20.65	21.14	21.70	16.27	16.78	16.78	17.27	17.84
12H	4H	19.03	19.72	19.51	20.20	20.67	15.33	16.02	15.81	16.50	16.97
	6H	19.66	20.24	20.18	20.75	21.24	15.94	16.51	16.45	17.02	17.51
	8H	19.95	20.46	20.46	20.95	21.51	16.21	16.72	16.72	17.21	17.77