

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930846

Luminaire Tested: DFN2DS-SQ2F0-050DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-050DS940-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3791.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 47.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930846

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930846

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4053	4053	4053
5°	4069	4002	4025
10°	4038	3937	3903
15°	3991	3820	3710
20°	3927	3654	3470
25°	3861	3464	3238
30°	3770	3270	2939
35°	3681	3059	2678
40°	3591	2839	2375
45°	3486	2594	2101
50°	3378	2346	1832
55°	3268	2078	1573
60°	3140	1797	1306
65°	2994	1510	1189
70°	2821	1244	1094
75°	2607	1133	1021
80°	2302	1013	929
85°	1809	800	800

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3486 cd/sqm

TEST NUMBER: P930846

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.8	4.6
10°-20°	474.3	12.5
20°-30°	665.8	17.6
30°-40°	725.8	19.1
40°-50°	667.1	17.6
50°-60°	523.9	13.8
60°-70°	341.0	9.0
70°-80°	175.5	4.6
80°-90°	44.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1312.9	34.6
0°-40°	2038.7	53.8
0°-60°	3229.7	85.2
0°-90°	3791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3791.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1835	1813	1828	1823	175
15°	1753	1735	1678	1646	1630	494
25°	1591	1538	1428	1360	1334	732
35°	1371	1286	1139	1034	998	858
45°	1121	1009	834	716	676	866
55°	852	722	542	442	410	762
65°	576	440	290	234	228	571
75°	307	190	133	122	120	325
85°	72	37	32	32	32	86
90°	0	0	0	0	0	

TEST NUMBER: P930846

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1843.3	1843.3	1843.3	1843.3	1843.3
2.5°	1851.6	1843.3	1824.9	1841.7	1838.3
5°	1843.3	1835.0	1813.3	1828.2	1823.3
7.5°	1828.2	1818.3	1795.0	1801.6	1793.2
10°	1808.3	1796.6	1763.3	1758.2	1748.2
12.5°	1783.3	1768.3	1723.2	1713.3	1694.8
15°	1753.2	1734.9	1678.2	1646.5	1629.9
17.5°	1718.2	1691.5	1621.4	1584.7	1558.0
20°	1678.2	1644.8	1561.4	1519.8	1483.0
22.5°	1634.9	1596.4	1499.6	1443.0	1418.0
25°	1591.4	1538.0	1427.9	1359.6	1334.4
27.5°	1539.8	1483.0	1361.2	1282.8	1244.4
30°	1484.7	1421.2	1287.8	1202.8	1157.6
32.5°	1431.3	1354.5	1217.8	1117.7	1075.9
35°	1371.3	1286.2	1139.4	1034.3	997.5
37.5°	1312.8	1221.1	1066.0	950.8	909.2
40°	1251.1	1151.1	989.1	870.8	827.4
42.5°	1187.8	1081.0	912.5	789.0	747.4
45°	1121.1	1009.2	834.1	715.6	675.5
47.5°	1057.6	939.3	759.1	640.5	603.9
50°	987.6	869.2	685.7	570.4	535.6
52.5°	919.1	794.0	615.6	505.5	473.8
55°	852.4	722.3	542.1	442.1	410.4
57.5°	784.1	650.6	477.1	383.7	357.0
60°	714.0	580.5	408.6	323.7	296.9
62.5°	645.6	512.2	350.3	270.3	257.0
65°	575.5	440.4	290.3	233.6	228.5
67.5°	508.8	373.7	233.6	205.2	200.2
70°	438.8	308.6	193.5	176.8	170.1
72.5°	372.1	248.5	161.8	148.5	145.1
75°	306.9	190.1	133.4	121.8	120.2
77.5°	241.9	135.0	105.2	98.4	95.0
80°	181.8	96.8	80.0	73.4	73.4
82.5°	126.8	65.1	55.0	51.6	51.6
85°	71.7	36.7	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930846

CATALOG NUMBER: DFN2DS-SQ2F0-050DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.10	17.62	16.46	17.93	18.25	12.06	13.58	12.42	13.89	14.21
	3H	17.86	19.23	18.24	19.56	19.92	13.32	14.69	13.70	15.02	15.38
	4H	18.53	19.81	18.93	20.16	20.54	13.82	15.11	14.22	15.45	15.83
	6H	19.02	20.20	19.43	20.57	20.96	14.21	15.39	14.62	15.75	16.15
	8H	19.18	20.31	19.61	20.70	21.10	14.33	15.46	14.76	15.85	16.25
	12H	19.29	20.36	19.72	20.75	21.18	14.41	15.49	14.84	15.87	16.30
4H	2H	16.20	17.48	16.60	17.83	18.21	12.75	14.03	13.15	14.38	14.76
	3H	18.13	19.20	18.55	19.60	20.00	14.20	15.26	14.61	15.66	16.06
	4H	18.88	19.84	19.32	20.26	20.69	14.80	15.75	15.23	16.17	16.61
	6H	19.48	20.31	19.93	20.75	21.21	15.28	16.12	15.74	16.56	17.02
	8H	19.69	20.47	20.15	20.91	21.38	15.45	16.22	15.91	16.67	17.13
	12H	19.84	20.54	20.33	21.02	21.49	15.56	16.26	16.04	16.74	17.21
8H	4H	18.91	19.69	19.37	20.13	20.60	15.15	15.93	15.61	16.37	16.84
	6H	19.55	20.19	20.04	20.68	21.16	15.74	16.38	16.23	16.87	17.35
	8H	19.80	20.37	20.31	20.88	21.37	15.96	16.53	16.47	17.04	17.53
	12H	20.00	20.51	20.51	21.00	21.57	16.14	16.65	16.65	17.14	17.70
12H	4H	18.89	19.59	19.37	20.07	20.54	15.19	15.89	15.68	16.37	16.84
	6H	19.53	20.10	20.04	20.61	21.10	15.80	16.38	16.31	16.89	17.37
	8H	19.81	20.32	20.32	20.81	21.38	16.07	16.58	16.58	17.07	17.64

END OF REPORT