

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930489

Luminaire Tested: DFN2DS-PN2F0-060DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS830-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5595.4 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930489

CATALOG NUMBER: DFN2DS-PN2F0-060DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930489

CATALOG NUMBER: DFN2DS-PN2F0-060DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4763	4763	4763
5°	4781	4712	4741
10°	4753	4665	4688
15°	4694	4604	4600
20°	4611	4513	4509
25°	4528	4402	4402
30°	4422	4300	4263
35°	4322	4177	4115
40°	4197	4054	3976
45°	4075	3932	3835
50°	3940	3805	3669
55°	3801	3658	3522
60°	3646	3481	3353
65°	3479	3306	3154
70°	3268	3093	2947
75°	2972	2848	2779
80°	2639	2558	2426
85°	2152	2050	1839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4075 cd/sqm

TEST NUMBER: P930489

CATALOG NUMBER: DFN2DS-PN2F0-060DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.0	3.7
10°-20°	582.4	10.4
20°-30°	855.9	15.3
30°-40°	994.1	17.8
40°-50°	992.8	17.7
50°-60°	865.7	15.5
60°-70°	639.9	11.4
70°-80°	362.1	6.5
80°-90°	95.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1645.3	29.4
0°-40°	2639.3	47.2
0°-60°	4497.9	80.4
0°-90°	5595.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5595.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2199	2199	2199	2199	2199	
5°	2199	2191	2168	2184	2180	209
15°	2094	2081	2053	2062	2051	590
25°	1895	1878	1842	1846	1842	872
35°	1635	1614	1580	1567	1556	1021
45°	1330	1315	1284	1260	1252	1027
55°	1007	994	969	943	933	900
65°	679	666	645	626	615	671
75°	355	351	340	328	332	379
85°	87	85	82	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P930489

CATALOG NUMBER: DFN2DS-PN2F0-060DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2199.2	2199.2	2199.2	2199.2	2199.2
2.5°	2212.0	2201.5	2178.1	2199.2	2195.1
5°	2199.2	2190.9	2167.5	2184.4	2180.4
7.5°	2184.4	2171.9	2148.5	2165.6	2161.3
10°	2161.3	2146.5	2121.1	2138.0	2131.7
12.5°	2129.5	2116.9	2091.5	2102.1	2097.8
15°	2093.5	2081.0	2053.4	2061.9	2051.4
17.5°	2049.1	2036.6	2009.0	2019.5	2009.0
20°	2000.4	1987.9	1958.2	1964.5	1956.3
22.5°	1952.0	1932.9	1905.3	1905.3	1901.1
25°	1894.7	1878.0	1842.0	1846.0	1842.0
27.5°	1831.2	1816.5	1789.0	1782.8	1772.3
30°	1768.0	1750.9	1719.3	1713.0	1704.5
32.5°	1700.2	1687.7	1653.8	1641.0	1632.5
35°	1634.7	1613.6	1579.7	1566.9	1556.4
37.5°	1560.7	1541.6	1507.8	1492.9	1482.3
40°	1484.6	1467.5	1433.7	1414.9	1406.3
42.5°	1410.6	1393.5	1359.9	1338.6	1326.0
45°	1330.3	1315.4	1283.6	1260.5	1251.9
47.5°	1251.9	1237.1	1203.3	1179.9	1167.3
50°	1169.4	1158.8	1129.3	1099.6	1089.0
52.5°	1089.0	1074.3	1046.8	1023.6	1008.8
55°	1006.7	993.9	968.6	943.2	932.7
57.5°	924.2	913.6	886.0	860.7	852.1
60°	841.6	833.3	803.7	780.4	774.0
62.5°	761.2	746.4	725.3	704.2	695.8
65°	678.9	666.2	645.1	626.0	615.4
67.5°	594.3	583.6	564.7	549.9	541.4
70°	516.0	507.5	488.4	473.6	465.3
72.5°	435.7	427.2	416.6	401.9	395.5
75°	355.1	351.2	340.3	327.8	332.1
77.5°	283.4	274.9	270.5	264.3	258.0
80°	211.6	209.3	205.1	198.8	194.5
82.5°	143.8	143.8	141.8	133.3	133.3
85°	86.6	84.6	82.5	76.0	74.0
87.5°	38.2	33.9	29.6	23.4	21.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930489

CATALOG NUMBER: DFN2DS-PN2F0-060DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.71	18.32	17.07	18.63	18.94	16.26	17.87	16.63	18.19	18.50
	3H	18.46	19.91	18.83	20.24	20.60	17.96	19.42	18.34	19.75	20.11
	4H	19.10	20.47	19.50	20.82	21.20	18.61	19.98	19.01	20.32	20.70
	6H	19.57	20.84	19.98	21.20	21.60	19.07	20.34	19.48	20.70	21.09
	8H	19.71	20.93	20.14	21.31	21.71	19.21	20.42	19.64	20.81	21.21
	12H	19.80	20.96	20.23	21.35	21.78	19.29	20.45	19.72	20.83	21.26
4H	2H	17.27	18.64	17.66	18.98	19.36	16.91	18.28	17.31	18.63	19.01
	3H	19.24	20.39	19.65	20.79	21.19	18.83	19.98	19.24	20.38	20.78
	4H	20.02	21.05	20.45	21.47	21.90	19.59	20.63	20.03	21.04	21.48
	6H	20.61	21.52	21.07	21.96	22.42	20.18	21.09	20.64	21.53	21.98
	8H	20.80	21.65	21.26	22.09	22.56	20.37	21.21	20.83	21.65	22.12
	12H	20.94	21.70	21.42	22.17	22.64	20.48	21.24	20.96	21.72	22.19
8H	4H	20.29	21.14	20.75	21.58	22.05	19.92	20.76	20.38	21.21	21.67
	6H	21.01	21.71	21.50	22.20	22.67	20.62	21.33	21.12	21.82	22.29
	8H	21.26	21.90	21.77	22.40	22.89	20.87	21.50	21.38	22.01	22.50
	12H	21.46	22.02	21.97	22.51	23.07	21.05	21.61	21.56	22.10	22.66
12H	4H	20.32	21.08	20.80	21.55	22.02	19.95	20.71	20.43	21.19	21.66
	6H	21.05	21.68	21.56	22.19	22.68	20.68	21.31	21.19	21.82	22.31
	8H	21.36	21.92	21.87	22.41	22.97	20.99	21.54	21.49	22.04	22.60