

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930899

Luminaire Tested: DFN2DS-SQ2F0-080DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-080DS940-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7064.6 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930899

CATALOG NUMBER: DFN2DS-SQ2F0-080DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930899

CATALOG NUMBER: DFN2DS-SQ2F0-080DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6105	6105	6105
5°	6129	6041	6076
10°	6093	5980	6009
15°	6017	5902	5896
20°	5910	5785	5780
25°	5804	5643	5643
30°	5668	5512	5464
35°	5540	5354	5275
40°	5380	5196	5096
45°	5223	5040	4916
50°	5051	4877	4704
55°	4873	4688	4514
60°	4673	4462	4298
65°	4460	4237	4043
70°	4189	3965	3777
75°	3810	3652	3561
80°	3384	3278	3110
85°	2760	2631	2359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5223 cd/sqm

TEST NUMBER: P930899

CATALOG NUMBER: DFN2DS-SQ2F0-080DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	3.7
10°-20°	735.3	10.4
20°-30°	1080.6	15.3
30°-40°	1255.1	17.8
40°-50°	1253.5	17.7
50°-60°	1093.0	15.5
60°-70°	808.0	11.4
70°-80°	457.1	6.5
80°-90°	120.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2077.3	29.4
0°-40°	3332.3	47.2
0°-60°	5678.8	80.4
0°-90°	7064.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7064.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2777	2777	2777	2777	2777	
5°	2777	2766	2737	2758	2753	264
15°	2643	2627	2592	2603	2590	744
25°	2392	2371	2326	2331	2326	1101
35°	2064	2037	1994	1978	1965	1289
45°	1680	1661	1621	1591	1581	1296
55°	1271	1255	1223	1191	1178	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	129
90°	0	0	0	0	0	

TEST NUMBER: P930899

CATALOG NUMBER: DFN2DS-SQ2F0-080DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2776.6	2776.6	2776.6	2776.6	2776.6
2.5°	2792.8	2779.5	2750.0	2776.6	2771.5
5°	2776.6	2766.2	2736.7	2758.0	2752.9
7.5°	2758.0	2742.1	2712.7	2734.2	2728.8
10°	2728.8	2710.1	2678.1	2699.3	2691.4
12.5°	2688.6	2672.7	2640.7	2654.0	2648.6
15°	2643.3	2627.4	2592.5	2603.3	2590.0
17.5°	2587.2	2571.3	2536.4	2549.8	2536.4
20°	2525.7	2509.8	2472.4	2480.4	2469.9
22.5°	2464.5	2440.4	2405.5	2405.5	2400.2
25°	2392.3	2371.0	2325.7	2330.8	2325.7
27.5°	2312.1	2293.4	2258.8	2250.9	2237.6
30°	2232.2	2210.6	2170.8	2162.8	2152.0
32.5°	2146.7	2130.8	2088.0	2071.8	2061.1
35°	2063.9	2037.3	1994.5	1978.4	1965.1
37.5°	1970.4	1946.3	1903.6	1884.9	1871.6
40°	1874.4	1852.9	1810.1	1786.3	1775.5
42.5°	1781.0	1759.4	1716.9	1690.0	1674.2
45°	1679.5	1660.8	1620.6	1591.4	1580.7
47.5°	1580.7	1562.0	1519.2	1489.7	1473.9
50°	1476.4	1463.1	1425.7	1388.3	1375.0
52.5°	1375.0	1356.3	1321.8	1292.3	1273.6
55°	1271.0	1254.9	1222.9	1190.9	1177.5
57.5°	1166.8	1153.5	1118.7	1086.6	1075.8
60°	1062.6	1052.1	1014.6	985.2	977.3
62.5°	961.1	942.5	915.8	889.2	878.4
65°	857.2	841.1	814.4	790.3	777.0
67.5°	750.4	736.8	713.0	694.3	683.5
70°	651.5	640.7	616.7	598.0	587.5
72.5°	550.1	539.4	526.0	507.4	499.4
75°	448.4	443.3	429.8	413.9	419.2
77.5°	357.8	347.0	341.6	333.7	325.8
80°	267.2	264.3	258.9	251.0	245.6
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.4	106.8	104.3	96.1	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930899

CATALOG NUMBER: DFN2DS-SQ2F0-080DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.57	19.18	17.93	19.49	19.81	17.12	18.73	17.49	19.05	19.36
	3H	19.32	20.77	19.70	21.10	21.46	18.83	20.28	19.20	20.61	20.97
	4H	19.96	21.33	20.36	21.68	22.06	19.47	20.84	19.87	21.19	21.56
	6H	20.43	21.70	20.84	22.07	22.46	19.93	21.20	20.34	21.57	21.96
	8H	20.58	21.79	21.00	22.18	22.58	20.07	21.28	20.50	21.67	22.07
	12H	20.67	21.83	21.10	22.21	22.64	20.15	21.31	20.58	21.70	22.13
4H	2H	18.13	19.50	18.53	19.85	20.22	17.78	19.14	18.17	19.49	19.87
	3H	20.10	21.25	20.51	21.65	22.05	19.70	20.84	20.11	21.24	21.64
	4H	20.88	21.92	21.31	22.33	22.77	20.46	21.49	20.89	21.91	22.34
	6H	21.48	22.38	21.93	22.82	23.28	21.04	21.95	21.50	22.39	22.85
	8H	21.67	22.51	22.13	22.96	23.42	21.23	22.07	21.69	22.52	22.98
	12H	21.80	22.56	22.28	23.03	23.50	21.35	22.11	21.83	22.58	23.05
8H	4H	21.15	22.00	21.61	22.44	22.91	20.78	21.63	21.24	22.07	22.53
	6H	21.87	22.57	22.36	23.06	23.53	21.49	22.19	21.98	22.68	23.15
	8H	22.13	22.76	22.64	23.26	23.75	21.74	22.37	22.25	22.87	23.36
	12H	22.33	22.89	22.83	23.38	23.94	21.91	22.47	22.42	22.96	23.52
12H	4H	21.18	21.94	21.66	22.42	22.88	20.82	21.57	21.30	22.05	22.52
	6H	21.91	22.55	22.42	23.05	23.54	21.54	22.18	22.05	22.68	23.17
	8H	22.23	22.79	22.73	23.28	23.84	21.85	22.41	22.36	22.90	23.46