

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930458

Luminaire Tested: DFN2DS-PN2F0-040DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-040DS840-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3403.4 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 42.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930458

CATALOG NUMBER: DFN2DS-PN2F0-040DS840-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P930458

CATALOG NUMBER: DFN2DS-PN2F0-040DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3584	3584	3584
5°	3598	3539	3559
10°	3570	3481	3452
15°	3529	3378	3281
20°	3473	3231	3068
25°	3414	3063	2863
30°	3333	2891	2599
35°	3255	2705	2368
40°	3176	2511	2100
45°	3083	2294	1858
50°	2987	2074	1620
55°	2890	1838	1391
60°	2776	1589	1155
65°	2648	1336	1051
70°	2494	1100	967
75°	2305	1003	903
80°	2036	896	823
85°	1600	706	706

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3083 cd/sqm

TEST NUMBER: P930458

CATALOG NUMBER: DFN2DS-PN2F0-040DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.1	4.6
10°-20°	425.8	12.5
20°-30°	597.8	17.6
30°-40°	651.6	19.1
40°-50°	598.9	17.6
50°-60°	470.3	13.8
60°-70°	306.1	9.0
70°-80°	157.6	4.6
80°-90°	40.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.6	34.6
0°-40°	1830.2	53.8
0°-60°	2899.4	85.2
0°-90°	3403.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3403.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1655	1655	1655	1655	1655	
5°	1655	1647	1628	1641	1637	157
15°	1574	1558	1507	1478	1463	444
25°	1429	1381	1282	1221	1198	657
35°	1231	1155	1023	928	896	771
45°	1006	906	749	642	606	777
55°	765	648	487	397	368	684
65°	517	395	261	210	205	512
75°	276	171	120	109	108	291
85°	64	33	28	28	28	77
90°	0	0	0	0	0	

TEST NUMBER: P930458

CATALOG NUMBER: DFN2DS-PN2F0-040DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1654.9	1654.9	1654.9	1654.9	1654.9
2.5°	1662.4	1654.9	1638.3	1653.5	1650.3
5°	1654.9	1647.3	1627.8	1641.3	1636.9
7.5°	1641.3	1632.4	1611.5	1617.3	1609.9
10°	1623.4	1612.9	1583.0	1578.4	1569.6
12.5°	1601.0	1587.5	1546.9	1538.0	1521.5
15°	1574.0	1557.5	1506.6	1478.2	1463.3
17.5°	1542.5	1518.5	1455.6	1422.7	1398.7
20°	1506.6	1476.6	1401.7	1364.4	1331.3
22.5°	1467.7	1433.2	1346.2	1295.4	1273.1
25°	1428.7	1380.8	1281.9	1220.6	1198.0
27.5°	1382.4	1331.3	1222.0	1151.7	1117.1
30°	1332.9	1275.9	1156.1	1079.8	1039.3
32.5°	1285.0	1216.0	1093.3	1003.4	965.9
35°	1231.1	1154.7	1022.9	928.5	895.5
37.5°	1178.7	1096.2	957.0	853.6	816.2
40°	1123.2	1033.4	888.1	781.8	742.8
42.5°	1066.3	970.5	819.2	708.3	671.0
45°	1006.4	906.0	748.8	642.4	606.5
47.5°	949.5	843.2	681.5	575.1	542.1
50°	886.6	780.3	615.5	512.1	480.8
52.5°	825.1	712.8	552.7	453.8	425.3
55°	765.3	648.4	486.7	396.9	368.5
57.5°	703.9	584.1	428.3	344.4	320.5
60°	640.9	521.1	366.9	290.6	266.7
62.5°	579.7	459.9	314.4	242.6	230.7
65°	516.7	395.3	260.6	209.7	205.1
67.5°	456.9	335.4	209.7	184.2	179.7
70°	393.9	277.1	173.7	158.8	152.7
72.5°	334.0	223.1	145.2	133.3	130.3
75°	275.5	170.7	119.8	109.3	107.9
77.5°	217.2	121.2	94.4	88.4	85.3
80°	163.2	86.9	71.8	66.0	66.0
82.5°	113.8	58.5	49.4	46.3	46.3
85°	64.4	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930458

CATALOG NUMBER: DFN2DS-PN2F0-040DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.67	17.19	16.03	17.51	17.82	11.63	13.15	11.99	13.46	13.78
	3H	17.44	18.80	17.81	19.13	19.49	12.90	14.26	13.27	14.59	14.95
	4H	18.10	19.38	18.50	19.73	20.11	13.40	14.68	13.80	15.03	15.40
	6H	18.59	19.77	19.00	20.14	20.53	13.78	14.96	14.19	15.33	15.72
	8H	18.76	19.88	19.18	20.27	20.67	13.90	15.03	14.33	15.42	15.82
	12H	18.86	19.94	19.29	20.32	20.75	13.98	15.06	14.41	15.44	15.87
4H	2H	15.77	17.05	16.17	17.40	17.78	12.33	13.61	12.72	13.95	14.33
	3H	17.71	18.77	18.12	19.17	19.57	13.77	14.83	14.18	15.23	15.63
	4H	18.46	19.41	18.89	19.83	20.27	14.37	15.32	14.80	15.74	16.18
	6H	19.05	19.88	19.51	20.32	20.78	14.86	15.69	15.31	16.13	16.59
	8H	19.26	20.04	19.73	20.48	20.95	15.02	15.80	15.48	16.24	16.71
	12H	19.42	20.11	19.90	20.59	21.06	15.14	15.83	15.62	16.31	16.78
8H	4H	18.48	19.26	18.94	19.70	20.17	14.72	15.50	15.19	15.94	16.41
	6H	19.12	19.76	19.62	20.25	20.73	15.31	15.95	15.81	16.44	16.92
	8H	19.37	19.95	19.88	20.46	20.94	15.53	16.11	16.04	16.62	17.10
	12H	19.57	20.08	20.08	20.58	21.14	15.71	16.22	16.22	16.71	17.27
12H	4H	18.47	19.16	18.95	19.64	20.11	14.77	15.46	15.25	15.94	16.41
	6H	19.10	19.68	19.61	20.19	20.67	15.37	15.95	15.89	16.46	16.95
	8H	19.38	19.89	19.89	20.39	20.95	15.65	16.15	16.15	16.65	17.21