

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930494

Luminaire Tested: DFN2DS-PN2F0-060DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS840-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5105.1 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930494
CATALOG NUMBER: DFN2DS-PN2F0-060DS840-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P930494

CATALOG NUMBER: DFN2DS-PN2F0-060DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5376	5376	5376
5°	5397	5309	5338
10°	5355	5222	5178
15°	5294	5067	4921
20°	5209	4846	4603
25°	5122	4595	4295
30°	5000	4337	3899
35°	4882	4057	3551
40°	4764	3766	3150
45°	4624	3441	2786
50°	4481	3111	2430
55°	4334	2757	2087
60°	4165	2384	1732
65°	3972	2003	1577
70°	3741	1650	1450
75°	3459	1504	1355
80°	3052	1343	1234
85°	2398	1059	1059

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4624 cd/sqm



TEST NUMBER: P930494
 CATALOG NUMBER: DFN2DS-PN2F0-060DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.6	4.6
10°-20°	638.6	12.5
20°-30°	896.6	17.6
30°-40°	977.4	19.1
40°-50°	898.3	17.6
50°-60°	705.5	13.8
60°-70°	459.2	9.0
70°-80°	236.4	4.6
80°-90°	60.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1767.9	34.6
0°-40°	2745.3	53.8
0°-60°	4349.1	85.2
0°-90°	5105.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5105.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2482	2482	2482	2482	2482	
5°	2482	2471	2442	2462	2455	235
15°	2361	2336	2260	2217	2195	665
25°	2143	2071	1923	1831	1797	986
35°	1847	1732	1534	1393	1343	1156
45°	1510	1359	1123	964	910	1166
55°	1148	973	730	595	553	1026
65°	775	593	391	315	308	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	116
90°	0	0	0	0	0	



TEST NUMBER: P930494

CATALOG NUMBER: DFN2DS-PN2F0-060DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2482.3	2482.3	2482.3	2482.3	2482.3
2.5°	2493.5	2482.3	2457.5	2480.1	2475.6
5°	2482.3	2471.1	2441.7	2462.1	2455.4
7.5°	2462.1	2448.6	2417.2	2426.0	2414.8
10°	2435.0	2419.3	2374.6	2367.7	2354.3
12.5°	2401.5	2381.2	2320.4	2307.1	2282.3
15°	2361.0	2336.1	2259.9	2217.2	2194.8
17.5°	2313.8	2277.8	2183.4	2134.0	2098.1
20°	2259.9	2214.8	2102.6	2046.5	1997.0
22.5°	2201.5	2149.7	2019.4	1943.1	1909.5
25°	2143.1	2071.2	1922.9	1830.9	1797.1
27.5°	2073.6	1997.0	1833.0	1727.4	1675.8
30°	1999.4	1913.8	1734.1	1619.7	1559.0
32.5°	1927.4	1824.0	1640.0	1505.1	1448.8
35°	1846.6	1732.0	1534.4	1392.8	1343.2
37.5°	1768.0	1644.2	1435.5	1280.4	1224.3
40°	1684.8	1550.1	1332.0	1172.6	1114.2
42.5°	1599.5	1455.8	1228.8	1062.5	1006.5
45°	1509.6	1359.0	1123.3	963.6	909.7
47.5°	1424.3	1264.9	1022.2	862.6	813.2
50°	1329.9	1170.5	923.3	768.2	721.2
52.5°	1237.6	1069.2	828.9	680.7	638.0
55°	1147.8	972.7	730.0	595.4	552.7
57.5°	1055.9	876.1	642.5	516.7	480.7
60°	961.5	781.8	550.3	435.9	399.9
62.5°	869.5	689.8	471.7	364.0	346.0
65°	775.1	593.0	390.9	314.6	307.7
67.5°	685.2	503.1	314.6	276.3	269.6
70°	590.8	415.6	260.5	238.1	229.0
72.5°	501.0	334.6	217.8	200.0	195.4
75°	413.3	256.0	179.7	164.0	161.9
77.5°	325.8	181.9	141.5	132.5	128.0
80°	244.7	130.3	107.7	98.9	98.9
82.5°	170.7	87.7	74.1	69.6	69.6
85°	96.5	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930494
 CATALOG NUMBER: DFN2DS-PN2F0-060DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.08	18.60	17.44	18.91	19.23	13.04	14.56	13.40	14.87	15.19
	3H	18.84	20.21	19.22	20.54	20.90	14.30	15.67	14.68	16.00	16.36
	4H	19.51	20.79	19.91	21.14	21.52	14.81	16.09	15.21	16.44	16.81
	6H	20.00	21.18	20.41	21.55	21.94	15.19	16.37	15.60	16.74	17.13
	8H	20.16	21.29	20.59	21.68	22.08	15.31	16.44	15.74	16.83	17.23
	12H	20.27	21.35	20.70	21.73	22.16	15.39	16.47	15.82	16.85	17.28
4H	2H	17.18	18.46	17.58	18.81	19.19	13.73	15.02	14.13	15.36	15.74
	3H	19.12	20.18	19.53	20.58	20.98	15.18	16.24	15.59	16.64	17.04
	4H	19.87	20.82	20.30	21.24	21.68	15.78	16.73	16.21	17.15	17.59
	6H	20.46	21.29	20.91	21.73	22.19	16.27	17.10	16.72	17.54	18.00
	8H	20.67	21.45	21.13	21.89	22.36	16.43	17.20	16.89	17.65	18.12
	12H	20.82	21.52	21.31	22.00	22.47	16.54	17.24	17.03	17.72	18.19
8H	4H	19.89	20.67	20.35	21.11	21.58	16.13	16.91	16.59	17.35	17.82
	6H	20.53	21.17	21.02	21.66	22.14	16.72	17.36	17.21	17.85	18.33
	8H	20.78	21.35	21.29	21.86	22.35	16.94	17.52	17.45	18.03	18.51
	12H	20.98	21.49	21.49	21.98	22.55	17.12	17.63	17.63	18.12	18.68
12H	4H	19.87	20.57	20.36	21.05	21.52	16.17	16.87	16.66	17.35	17.82
	6H	20.51	21.09	21.02	21.59	22.08	16.78	17.36	17.29	17.87	18.36
	8H	20.79	21.30	21.30	21.79	22.36	17.05	17.56	17.56	18.06	18.62