

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930902

Luminaire Tested: DFN2DS-SQ2F0-080DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930902
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-080DS950-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6426.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930902

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930902

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6870	6870	6870
5°	6897	6784	6822
10°	6844	6674	6617
15°	6765	6476	6289
20°	6656	6193	5882
25°	6545	5872	5488
30°	6390	5543	4982
35°	6240	5185	4539
40°	6088	4813	4026
45°	5909	4397	3561
50°	5727	3976	3105
55°	5539	3523	2667
60°	5322	3046	2214
65°	5076	2560	2015
70°	4781	2108	1854
75°	4420	1922	1731
80°	3901	1717	1577
85°	3065	1355	1355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5909 cd/sqm

TEST NUMBER: P930902

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.8	4.6
10°-20°	803.9	12.5
20°-30°	1128.6	17.6
30°-40°	1230.3	19.1
40°-50°	1130.8	17.6
50°-60°	888.0	13.8
60°-70°	578.0	9.0
70°-80°	297.5	4.6
80°-90°	76.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2225.4	34.6
0°-40°	3455.7	53.8
0°-60°	5474.5	85.2
0°-90°	6426.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6426.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3124	3124	3124	3124	3124	
5°	3124	3110	3074	3099	3091	296
15°	2972	2941	2845	2791	2763	837
25°	2698	2607	2420	2305	2262	1241
35°	2324	2180	1931	1753	1691	1455
45°	1900	1711	1414	1213	1145	1467
55°	1445	1224	919	749	696	1291
65°	976	746	492	396	387	967
75°	520	322	226	206	204	550
85°	122	62	54	54	54	146
90°	0	0	0	0	0	



TEST NUMBER: P930902

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3124.5	3124.5	3124.5	3124.5	3124.5
2.5°	3138.6	3124.5	3093.4	3121.8	3116.1
5°	3124.5	3110.5	3073.5	3099.0	3090.6
7.5°	3099.0	3082.2	3042.6	3053.8	3039.6
10°	3065.1	3045.4	2988.9	2980.2	2963.4
12.5°	3022.9	2997.4	2920.8	2904.0	2872.8
15°	2971.8	2940.7	2844.6	2791.0	2762.7
17.5°	2912.4	2867.1	2748.3	2686.3	2640.9
20°	2844.6	2787.9	2646.7	2576.2	2513.7
22.5°	2771.1	2706.0	2542.0	2445.9	2403.6
25°	2697.6	2607.1	2420.4	2304.7	2262.0
27.5°	2610.0	2513.7	2307.3	2174.4	2109.3
30°	2516.7	2409.0	2182.9	2038.8	1962.3
32.5°	2426.1	2296.0	2064.4	1894.5	1823.8
35°	2324.4	2180.1	1931.4	1753.3	1690.8
37.5°	2225.4	2069.7	1806.9	1611.6	1541.1
40°	2120.8	1951.2	1676.7	1476.0	1402.5
42.5°	2013.3	1832.4	1546.8	1337.5	1266.9
45°	1900.2	1710.6	1413.9	1212.9	1145.2
47.5°	1792.9	1592.1	1286.7	1085.7	1023.6
50°	1674.0	1473.3	1162.3	966.9	907.8
52.5°	1557.9	1345.8	1043.4	856.8	803.2
55°	1444.8	1224.3	918.9	749.4	695.7
57.5°	1329.0	1102.8	808.8	650.4	605.1
60°	1210.2	984.0	692.7	548.7	503.4
62.5°	1094.4	868.2	593.7	458.1	435.6
65°	975.6	746.4	492.0	396.0	387.3
67.5°	862.5	633.3	396.0	347.7	339.3
70°	743.7	523.2	327.9	299.7	288.3
72.5°	630.6	421.2	274.2	251.7	246.0
75°	520.2	322.2	226.2	206.4	203.7
77.5°	410.1	228.9	178.2	166.8	161.1
80°	308.1	164.1	135.6	124.5	124.5
82.5°	214.8	110.4	93.3	87.6	87.6
85°	121.5	62.1	53.7	53.7	53.7
87.5°	45.3	22.5	22.5	19.8	19.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930902

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.93	19.45	18.30	19.77	20.08	13.89	15.41	14.26	15.73	16.04
	3H	19.70	21.06	20.07	21.39	21.75	15.16	16.52	15.53	16.85	17.21
	4H	20.36	21.64	20.76	21.99	22.37	15.66	16.94	16.06	17.29	17.67
	6H	20.85	22.03	21.26	22.40	22.79	16.04	17.22	16.45	17.59	17.98
	8H	21.02	22.14	21.44	22.53	22.93	16.16	17.29	16.59	17.68	18.08
	12H	21.12	22.20	21.55	22.58	23.01	16.24	17.32	16.68	17.70	18.13
4H	2H	18.03	19.32	18.43	19.66	20.04	14.59	15.87	14.99	16.22	16.59
	3H	19.97	21.03	20.38	21.43	21.83	16.03	17.09	16.44	17.49	17.89
	4H	20.72	21.67	21.15	22.09	22.53	16.63	17.59	17.06	18.00	18.44
	6H	21.31	22.14	21.77	22.58	23.04	17.12	17.95	17.57	18.39	18.85
	8H	21.52	22.30	21.99	22.74	23.21	17.28	18.06	17.74	18.50	18.97
	12H	21.68	22.37	22.16	22.85	23.32	17.40	18.09	17.88	18.57	19.04
8H	4H	20.74	21.52	21.20	21.96	22.43	16.98	17.76	17.45	18.20	18.67
	6H	21.38	22.02	21.88	22.51	22.99	17.57	18.21	18.07	18.70	19.18
	8H	21.63	22.21	22.14	22.72	23.20	17.79	18.37	18.30	18.88	19.37
	12H	21.83	22.34	22.34	22.84	23.40	17.97	18.48	18.48	18.97	19.54
12H	4H	20.73	21.42	21.21	21.90	22.37	17.03	17.72	17.51	18.20	18.67
	6H	21.36	21.94	21.87	22.45	22.94	17.63	18.21	18.15	18.72	19.21
	8H	21.64	22.15	22.15	22.65	23.21	17.91	18.42	18.42	18.91	19.47