

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930495

Luminaire Tested: DFN2DS-PN2F0-060DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS850-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6587.4 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930495

CATALOG NUMBER: DFN2DS-PN2F0-060DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930495

CATALOG NUMBER: DFN2DS-PN2F0-060DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5608	5608	5608
5°	5629	5548	5581
10°	5596	5492	5519
15°	5526	5420	5415
20°	5428	5314	5308
25°	5331	5182	5182
30°	5206	5062	5018
35°	5089	4917	4845
40°	4942	4772	4681
45°	4797	4629	4515
50°	4639	4480	4320
55°	4475	4306	4146
60°	4292	4099	3948
65°	4096	3892	3713
70°	3847	3641	3469
75°	3499	3353	3271
80°	3107	3011	2856
85°	2532	2413	2167

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4797 cd/sqm

TEST NUMBER: P930495

CATALOG NUMBER: DFN2DS-PN2F0-060DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	3.7
10°-20°	685.6	10.4
20°-30°	1007.6	15.3
30°-40°	1170.3	17.8
40°-50°	1168.8	17.7
50°-60°	1019.2	15.5
60°-70°	753.4	11.4
70°-80°	426.3	6.5
80°-90°	112.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1937.0	29.4
0°-40°	3107.2	47.2
0°-60°	5295.3	80.4
0°-90°	6587.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6587.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	120
90°	0	0	0	0	0	

TEST NUMBER: P930495

CATALOG NUMBER: DFN2DS-PN2F0-060DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930495

CATALOG NUMBER: DFN2DS-PN2F0-060DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.27	18.88	17.64	19.20	19.51	16.83	18.44	17.19	18.75	19.07
	3H	19.02	20.48	19.40	20.80	21.16	18.53	19.99	18.91	20.31	20.67
	4H	19.67	21.04	20.07	21.39	21.76	19.17	20.54	19.57	20.89	21.27
	6H	20.14	21.41	20.55	21.77	22.16	19.64	20.91	20.05	21.27	21.66
	8H	20.28	21.49	20.71	21.88	22.28	19.78	20.99	20.20	21.38	21.78
	12H	20.37	21.53	20.80	21.91	22.34	19.86	21.02	20.29	21.40	21.83
4H	2H	17.83	19.20	18.23	19.55	19.93	17.48	18.85	17.88	19.20	19.57
	3H	19.81	20.95	20.22	21.35	21.75	19.40	20.55	19.81	20.95	21.35
	4H	20.58	21.62	21.02	22.03	22.47	20.16	21.20	20.59	21.61	22.05
	6H	21.18	22.09	21.64	22.53	22.98	20.75	21.65	21.20	22.09	22.55
	8H	21.37	22.22	21.83	22.66	23.13	20.93	21.78	21.39	22.22	22.69
	12H	21.50	22.26	21.98	22.74	23.21	21.05	21.81	21.53	22.29	22.76
8H	4H	20.86	21.70	21.32	22.15	22.61	20.48	21.33	20.94	21.77	22.24
	6H	21.57	22.28	22.07	22.76	23.24	21.19	21.89	21.68	22.38	22.86
	8H	21.83	22.46	22.34	22.97	23.46	21.44	22.07	21.95	22.58	23.06
	12H	22.03	22.59	22.54	23.08	23.64	21.62	22.18	22.13	22.67	23.23
12H	4H	20.88	21.64	21.36	22.12	22.59	20.52	21.28	21.00	21.76	22.22
	6H	21.62	22.25	22.13	22.76	23.24	21.25	21.88	21.76	22.39	22.87
	8H	21.93	22.49	22.44	22.98	23.54	21.55	22.11	22.06	22.60	23.16