

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930426

Luminaire Tested: DFN2DS-PN2F0-020DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-020DS927-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1346.4 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 19.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930426

CATALOG NUMBER: DFN2DS-PN2F0-020DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930426

CATALOG NUMBER: DFN2DS-PN2F0-020DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1418	1418	1418
5°	1423	1400	1408
10°	1412	1377	1366
15°	1396	1336	1298
20°	1374	1278	1214
25°	1351	1212	1133
30°	1319	1144	1028
35°	1288	1070	937
40°	1256	993	831
45°	1219	908	735
50°	1182	820	641
55°	1143	727	550
60°	1099	629	457
65°	1048	528	416
70°	987	435	382
75°	912	397	357
80°	804	354	326
85°	631	278	278

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1219 cd/sqm

TEST NUMBER: P930426

CATALOG NUMBER: DFN2DS-PN2F0-020DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	4.6
10°-20°	168.4	12.5
20°-30°	236.5	17.6
30°-40°	257.8	19.1
40°-50°	236.9	17.6
50°-60°	186.1	13.8
60°-70°	121.1	9.0
70°-80°	62.3	4.6
80°-90°	15.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.3	34.6
0°-40°	724.0	53.8
0°-60°	1147.0	85.2
0°-90°	1346.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1346.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	655	652	644	649	648	62
15°	623	616	596	585	579	175
25°	565	546	507	483	474	260
35°	487	457	405	367	354	305
45°	398	358	296	254	240	307
55°	303	256	192	157	146	271
65°	204	156	103	83	81	203
75°	109	68	47	43	43	115
85°	25	13	11	11	11	31
90°	0	0	0	0	0	

TEST NUMBER: P930426

CATALOG NUMBER: DFN2DS-PN2F0-020DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	654.7	654.7	654.7	654.7	654.7
2.5°	657.6	654.7	648.1	654.1	652.9
5°	654.7	651.7	644.0	649.4	647.5
7.5°	649.4	645.8	637.5	639.9	636.8
10°	642.2	638.0	626.2	624.4	620.9
12.5°	633.4	628.0	612.0	608.5	601.9
15°	622.7	616.1	596.0	584.7	578.9
17.5°	610.2	600.7	575.9	562.8	553.4
20°	596.0	584.1	554.6	539.7	526.7
22.5°	580.6	567.0	532.6	512.5	503.6
25°	565.3	546.2	507.1	482.9	473.9
27.5°	546.9	526.7	483.4	455.6	441.9
30°	527.3	504.7	457.4	427.2	411.1
32.5°	508.3	481.1	432.5	397.0	382.1
35°	487.0	456.8	404.7	367.3	354.3
37.5°	466.3	433.6	378.6	337.7	322.9
40°	444.3	408.8	351.3	309.3	293.8
42.5°	421.8	384.0	324.1	280.2	265.5
45°	398.1	358.4	296.3	254.2	239.9
47.5°	375.6	333.6	269.6	227.5	214.5
50°	350.8	308.7	243.5	202.6	190.2
52.5°	326.4	282.0	218.6	179.5	168.3
55°	302.7	256.5	192.5	157.1	145.7
57.5°	278.5	231.0	169.5	136.3	126.8
60°	253.6	206.2	145.2	115.0	105.5
62.5°	229.3	181.9	124.4	96.0	91.2
65°	204.4	156.4	103.1	83.0	81.2
67.5°	180.7	132.7	83.0	72.9	71.1
70°	155.8	109.6	68.7	62.8	60.4
72.5°	132.1	88.2	57.4	52.7	51.6
75°	109.0	67.5	47.4	43.2	42.7
77.5°	85.9	48.0	37.3	34.9	33.7
80°	64.5	34.4	28.4	26.1	26.1
82.5°	45.0	23.1	19.6	18.4	18.4
85°	25.4	13.0	11.2	11.2	11.2
87.5°	9.5	4.8	4.8	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930426

CATALOG NUMBER: DFN2DS-PN2F0-020DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.45	13.97	12.81	14.28	14.60	8.41	9.93	8.77	10.25	10.56
	3H	14.21	15.58	14.59	15.91	16.27	9.67	11.04	10.05	11.37	11.73
	4H	14.88	16.16	15.28	16.51	16.89	10.18	11.46	10.58	11.81	12.18
	6H	15.37	16.55	15.78	16.92	17.31	10.56	11.74	10.97	12.11	12.50
	8H	15.53	16.66	15.96	17.05	17.45	10.68	11.81	11.11	12.20	12.60
	12H	15.64	16.71	16.07	17.10	17.53	10.76	11.84	11.19	12.22	12.65
4H	2H	12.55	13.83	12.95	14.18	14.56	9.11	10.39	9.50	10.73	11.11
	3H	14.48	15.55	14.89	15.95	16.35	10.55	11.61	10.96	12.01	12.41
	4H	15.23	16.19	15.67	16.61	17.04	11.15	12.10	11.58	12.52	12.96
	6H	15.83	16.66	16.28	17.10	17.56	11.63	12.47	12.09	12.91	13.37
	8H	16.04	16.82	16.50	17.26	17.73	11.80	12.57	12.26	13.02	13.49
	12H	16.19	16.89	16.68	17.37	17.84	11.91	12.61	12.40	13.09	13.56
8H	4H	15.26	16.04	15.72	16.48	16.95	11.50	12.28	11.96	12.72	13.19
	6H	15.90	16.54	16.39	17.03	17.51	12.09	12.73	12.58	13.22	13.70
	8H	16.15	16.72	16.66	17.23	17.72	12.31	12.88	12.82	13.39	13.88
	12H	16.35	16.86	16.86	17.35	17.92	12.49	13.00	13.00	13.49	14.05
12H	4H	15.24	15.94	15.72	16.42	16.89	11.54	12.24	12.03	12.72	13.19
	6H	15.88	16.45	16.39	16.96	17.45	12.15	12.73	12.66	13.24	13.73
	8H	16.16	16.67	16.67	17.16	17.73	12.42	12.93	12.93	13.43	13.99

END OF REPORT