

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931101

Luminaire Tested: DFN2DS-SQ4F0-080DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-080DS830-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7460.7 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 79.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931101

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931101

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2058	2058	2058
5°	2065	2036	2048
10°	2053	2015	2025
15°	2028	1989	1987
20°	1992	1950	1948
25°	1956	1902	1902
30°	1910	1857	1841
35°	1867	1804	1778
40°	1813	1751	1718
45°	1760	1698	1656
50°	1702	1644	1585
55°	1642	1580	1521
60°	1575	1504	1448
65°	1503	1428	1362
70°	1411	1336	1273
75°	1284	1231	1200
80°	1140	1105	1048
85°	930	886	795

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1760 cd/sqm

TEST NUMBER: P931101

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.0	3.7
10°-20°	776.5	10.4
20°-30°	1141.2	15.3
30°-40°	1325.4	17.8
40°-50°	1323.8	17.7
50°-60°	1154.3	15.5
60°-70°	853.3	11.4
70°-80°	482.8	6.5
80°-90°	127.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2193.7	29.4
0°-40°	3519.1	47.2
0°-60°	5997.2	80.4
0°-90°	7460.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7460.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2932	2932	2932	2932	2932	
5°	2932	2921	2890	2913	2907	278
15°	2791	2775	2738	2749	2735	786
25°	2526	2504	2456	2461	2456	1163
35°	2180	2152	2106	2089	2075	1361
45°	1774	1754	1711	1681	1669	1369
55°	1342	1325	1292	1258	1244	1200
65°	905	888	860	835	821	895
75°	474	468	454	437	443	505
85°	116	113	110	102	99	136
90°	0	0	0	0	0	

TEST NUMBER: P931101

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2932.3	2932.3	2932.3	2932.3	2932.3
2.5°	2949.3	2935.3	2904.2	2932.3	2926.9
5°	2932.3	2921.2	2890.2	2912.6	2907.2
7.5°	2912.6	2895.8	2864.7	2887.4	2881.8
10°	2881.8	2862.0	2828.2	2850.6	2842.3
12.5°	2839.3	2822.5	2788.7	2802.7	2797.1
15°	2791.4	2774.7	2737.8	2749.2	2735.2
17.5°	2732.2	2715.4	2678.6	2692.7	2678.6
20°	2667.3	2650.5	2611.0	2619.4	2608.3
22.5°	2602.7	2577.2	2540.4	2540.4	2534.7
25°	2526.3	2503.9	2456.1	2461.4	2456.1
27.5°	2441.7	2422.0	2385.4	2377.0	2363.0
30°	2357.4	2334.6	2292.5	2284.1	2272.7
32.5°	2267.0	2250.2	2205.0	2188.0	2176.7
35°	2179.6	2151.5	2106.3	2089.3	2075.2
37.5°	2080.9	2055.4	2010.3	1990.5	1976.5
40°	1979.5	1956.7	1911.6	1886.4	1875.1
42.5°	1880.8	1858.0	1813.2	1784.7	1768.0
45°	1773.7	1753.9	1711.4	1680.6	1669.3
47.5°	1669.3	1649.5	1604.3	1573.2	1556.5
50°	1559.2	1545.2	1505.6	1466.1	1452.1
52.5°	1452.1	1432.3	1395.9	1364.8	1345.0
55°	1342.3	1325.2	1291.5	1257.7	1243.5
57.5°	1232.2	1218.2	1181.4	1147.5	1136.1
60°	1122.1	1111.1	1071.5	1040.4	1032.1
62.5°	1015.0	995.3	967.2	939.1	927.7
65°	905.3	888.2	860.0	834.6	820.6
67.5°	792.4	778.1	752.9	733.3	721.9
70°	688.0	676.6	651.3	631.5	620.4
72.5°	580.9	569.6	555.5	535.8	527.4
75°	473.5	468.2	453.9	437.1	442.7
77.5°	377.8	366.4	360.8	352.4	344.0
80°	282.1	279.1	273.5	265.1	259.3
82.5°	191.8	191.8	189.1	177.7	177.7
85°	115.5	112.8	110.1	101.5	98.7
87.5°	50.9	45.2	39.5	31.1	28.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931101

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.79	15.40	14.15	15.71	16.03	13.34	14.96	13.71	15.27	15.58
	3H	15.54	16.99	15.92	17.32	17.68	15.05	16.50	15.43	16.83	17.19
	4H	16.19	17.55	16.58	17.90	18.28	15.69	17.06	16.09	17.41	17.78
	6H	16.65	17.92	17.07	18.29	18.68	16.15	17.42	16.56	17.79	18.18
	8H	16.80	18.01	17.22	18.40	18.80	16.29	17.51	16.72	17.89	18.29
	12H	16.89	18.05	17.32	18.43	18.86	16.38	17.54	16.81	17.92	18.35
4H	2H	14.35	15.72	14.75	16.07	16.44	14.00	15.37	14.39	15.71	16.09
	3H	16.32	17.47	16.73	17.87	18.27	15.92	17.06	16.33	17.46	17.86
	4H	17.10	18.14	17.53	18.55	18.99	16.68	17.71	17.11	18.13	18.56
	6H	17.70	18.60	18.15	19.04	19.50	17.27	18.17	17.72	18.61	19.07
	8H	17.89	18.73	18.35	19.18	19.64	17.45	18.30	17.91	18.74	19.20
	12H	18.02	18.78	18.50	19.25	19.72	17.57	18.33	18.05	18.80	19.27
8H	4H	17.37	18.22	17.84	18.66	19.13	17.00	17.85	17.46	18.29	18.75
	6H	18.09	18.79	18.58	19.28	19.76	17.71	18.41	18.20	18.90	19.37
	8H	18.35	18.98	18.86	19.49	19.97	17.96	18.59	18.47	19.09	19.58
	12H	18.55	19.11	19.06	19.60	20.16	18.14	18.69	18.64	19.18	19.74
12H	4H	17.40	18.16	17.88	18.64	19.11	17.04	17.80	17.52	18.27	18.74
	6H	18.13	18.77	18.64	19.27	19.76	17.77	18.40	18.28	18.90	19.39
	8H	18.45	19.01	18.96	19.50	20.06	18.07	18.63	18.58	19.12	19.68