

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931102

Luminaire Tested: DFN2DS-SQ4F0-080DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-080DS830-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6405.6 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 79.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931102

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931102

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2185	2185	2185
5°	2194	2158	2170
10°	2177	2123	2105
15°	2152	2060	2001
20°	2117	1970	1871
25°	2082	1868	1746
30°	2033	1763	1585
35°	1985	1649	1444
40°	1936	1531	1281
45°	1880	1399	1133
50°	1822	1265	988
55°	1762	1121	848
60°	1693	969	704
65°	1615	814	641
70°	1521	671	590
75°	1406	611	551
80°	1241	546	501
85°	975	431	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1880 cd/sqm

TEST NUMBER: P931102

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.9	4.6
10°-20°	801.3	12.5
20°-30°	1125.1	17.6
30°-40°	1226.4	19.1
40°-50°	1127.2	17.6
50°-60°	885.2	13.8
60°-70°	576.2	9.0
70°-80°	296.6	4.6
80°-90°	75.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2218.3	34.6
0°-40°	3444.7	53.8
0°-60°	5457.1	85.2
0°-90°	6405.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6405.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3115	3115	3115	3115	3115	
5°	3115	3101	3064	3089	3081	295
15°	2962	2931	2836	2782	2754	835
25°	2689	2599	2413	2297	2255	1237
35°	2317	2173	1925	1748	1685	1450
45°	1894	1705	1409	1209	1142	1463
55°	1440	1220	916	747	694	1287
65°	972	744	490	395	386	964
75°	519	321	226	206	203	548
85°	121	62	54	54	54	145
90°	0	0	0	0	0	

TEST NUMBER: P931102

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3114.6	3114.6	3114.6	3114.6	3114.6
2.5°	3128.7	3114.6	3083.5	3111.9	3106.2
5°	3114.6	3100.6	3063.8	3089.2	3080.8
7.5°	3089.2	3072.4	3033.0	3044.1	3029.9
10°	3055.4	3035.7	2979.5	2970.8	2954.0
12.5°	3013.3	2987.8	2911.5	2894.8	2863.7
15°	2962.4	2931.3	2835.6	2782.1	2753.9
17.5°	2903.1	2858.0	2739.6	2677.7	2632.5
20°	2835.6	2779.1	2638.3	2568.0	2505.7
22.5°	2762.3	2697.4	2533.9	2438.2	2396.0
25°	2689.0	2598.8	2412.7	2297.3	2254.9
27.5°	2601.7	2505.7	2300.0	2167.5	2102.6
30°	2508.7	2401.3	2175.9	2032.4	1956.1
32.5°	2418.4	2288.7	2057.8	1888.5	1818.0
35°	2317.0	2173.2	1925.3	1747.7	1685.4
37.5°	2218.3	2063.2	1801.2	1606.5	1536.2
40°	2114.0	1945.0	1671.4	1471.3	1398.0
42.5°	2006.9	1826.6	1541.9	1333.2	1262.8
45°	1894.2	1705.2	1409.4	1209.1	1141.5
47.5°	1787.2	1587.1	1282.6	1082.3	1020.4
50°	1668.7	1468.7	1158.6	963.9	904.9
52.5°	1553.0	1341.5	1040.1	854.1	800.6
55°	1440.2	1220.5	916.0	747.0	693.5
57.5°	1324.8	1099.3	806.3	648.4	603.2
60°	1206.3	980.9	690.5	546.9	501.8
62.5°	1090.9	865.4	591.9	456.7	434.3
65°	972.5	744.0	490.4	394.8	386.0
67.5°	859.8	631.3	394.8	346.6	338.3
70°	741.4	521.6	326.9	298.7	287.4
72.5°	628.6	419.8	273.4	250.9	245.2
75°	518.6	321.2	225.5	205.7	203.1
77.5°	408.8	228.2	177.7	166.3	160.6
80°	307.1	163.6	135.2	124.1	124.1
82.5°	214.1	110.0	93.0	87.3	87.3
85°	121.1	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931102

CATALOG NUMBER: DFN2DS-SQ4F0-080DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.95	15.47	14.32	15.79	16.10	9.91	11.43	10.28	11.75	12.06
	3H	15.72	17.08	16.09	17.41	17.77	11.18	12.54	11.55	12.87	13.23
	4H	16.38	17.66	16.78	18.01	18.39	11.68	12.96	12.08	13.31	13.69
	6H	16.87	18.05	17.28	18.42	18.81	12.06	13.24	12.47	13.61	14.00
	8H	17.04	18.16	17.46	18.55	18.95	12.18	13.31	12.61	13.70	14.10
	12H	17.14	18.22	17.57	18.60	19.03	12.27	13.34	12.70	13.73	14.15
4H	2H	14.05	15.34	14.45	15.68	16.06	10.61	11.89	11.01	12.24	12.62
	3H	15.99	17.05	16.40	17.45	17.85	12.05	13.11	12.46	13.51	13.91
	4H	16.74	17.69	17.17	18.11	18.55	12.65	13.61	13.08	14.02	14.46
	6H	17.33	18.16	17.79	18.60	19.06	13.14	13.97	13.60	14.41	14.87
	8H	17.54	18.32	18.01	18.77	19.23	13.30	14.08	13.76	14.52	14.99
	12H	17.70	18.39	18.18	18.87	19.34	13.42	14.11	13.90	14.59	15.06
8H	4H	16.76	17.54	17.23	17.98	18.45	13.00	13.78	13.47	14.23	14.69
	6H	17.40	18.04	17.90	18.53	19.01	13.59	14.23	14.09	14.72	15.20
	8H	17.65	18.23	18.16	18.74	19.22	13.81	14.39	14.33	14.90	15.39
	12H	17.85	18.36	18.36	18.86	19.42	13.99	14.50	14.50	14.99	15.56
12H	4H	16.75	17.44	17.23	17.92	18.39	13.05	13.74	13.53	14.22	14.69
	6H	17.38	17.96	17.89	18.47	18.96	13.65	14.23	14.17	14.74	15.23
	8H	17.66	18.17	18.17	18.67	19.23	13.93	14.44	14.44	14.93	15.49