

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931067

Luminaire Tested: DFN2DS-SQ4F0-060DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-060DS835-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5940.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 57.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931067

CATALOG NUMBER: DFN2DS-SQ4F0-060DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931067

CATALOG NUMBER: DFN2DS-SQ4F0-060DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1638	1638	1638
5°	1644	1621	1630
10°	1635	1604	1612
15°	1614	1583	1582
20°	1586	1552	1551
25°	1557	1514	1514
30°	1521	1479	1466
35°	1487	1436	1415
40°	1444	1394	1367
45°	1401	1352	1319
50°	1355	1309	1262
55°	1307	1258	1211
60°	1254	1197	1153
65°	1197	1137	1085
70°	1124	1064	1013
75°	1022	980	956
80°	908	880	834
85°	740	705	633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1401 cd/sqm

TEST NUMBER: P931067

CATALOG NUMBER: DFN2DS-SQ4F0-060DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	3.7
10°-20°	618.3	10.4
20°-30°	908.6	15.3
30°-40°	1055.3	17.8
40°-50°	1054.0	17.7
50°-60°	919.0	15.5
60°-70°	679.4	11.4
70°-80°	384.4	6.5
80°-90°	101.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.6	29.4
0°-40°	2801.8	47.2
0°-60°	4774.8	80.4
0°-90°	5940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5940.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P931067

CATALOG NUMBER: DFN2DS-SQ4F0-060DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931067

CATALOG NUMBER: DFN2DS-SQ4F0-060DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.00	14.61	13.36	14.92	15.24	12.55	14.16	12.92	14.48	14.79
	3H	14.75	16.20	15.12	16.53	16.89	14.26	15.71	14.63	16.04	16.40
	4H	15.39	16.76	15.79	17.11	17.49	14.90	16.27	15.30	16.62	16.99
	6H	15.86	17.13	16.27	17.50	17.89	15.36	16.63	15.77	16.99	17.39
	8H	16.01	17.22	16.43	17.61	18.01	15.50	16.71	15.93	17.10	17.50
	12H	16.10	17.26	16.53	17.64	18.07	15.58	16.74	16.01	17.13	17.55
4H	2H	13.56	14.93	13.96	15.28	15.65	13.21	14.57	13.60	14.92	15.30
	3H	15.53	16.68	15.94	17.08	17.48	15.13	16.27	15.54	16.67	17.07
	4H	16.31	17.35	16.74	17.76	18.20	15.89	16.92	16.32	17.34	17.77
	6H	16.91	17.81	17.36	18.25	18.71	16.47	17.38	16.93	17.82	18.28
	8H	17.10	17.94	17.56	18.38	18.85	16.66	17.50	17.12	17.95	18.41
	12H	17.23	17.99	17.71	18.46	18.93	16.78	17.54	17.26	18.01	18.48
8H	4H	16.58	17.43	17.04	17.87	18.34	16.21	17.06	16.67	17.50	17.96
	6H	17.30	18.00	17.79	18.49	18.96	16.92	17.62	17.41	18.11	18.58
	8H	17.56	18.19	18.07	18.69	19.18	17.16	17.80	17.67	18.30	18.79
	12H	17.76	18.31	18.26	18.80	19.37	17.34	17.90	17.85	18.39	18.95
12H	4H	16.61	17.37	17.09	17.84	18.31	16.24	17.00	16.72	17.48	17.95
	6H	17.34	17.97	17.85	18.48	18.97	16.97	17.61	17.48	18.11	18.60
	8H	17.66	18.21	18.16	18.70	19.27	17.28	17.84	17.79	18.33	18.89