

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931085

Luminaire Tested: DFN2DS-SQ4F0-070DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-070DS835-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 69.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931085

CATALOG NUMBER: DFN2DS-SQ4F0-070DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931085

CATALOG NUMBER: DFN2DS-SQ4F0-070DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1911	1911	1911
5°	1918	1891	1902
10°	1907	1872	1881
15°	1884	1847	1846
20°	1850	1811	1809
25°	1817	1766	1766
30°	1774	1725	1710
35°	1734	1676	1651
40°	1684	1626	1595
45°	1635	1577	1539
50°	1581	1527	1472
55°	1525	1468	1413
60°	1463	1397	1345
65°	1396	1326	1265
70°	1311	1241	1182
75°	1193	1143	1115
80°	1059	1026	973
85°	864	824	738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1635 cd/sqm

TEST NUMBER: P931085

CATALOG NUMBER: DFN2DS-SQ4F0-070DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	3.7
10°-20°	721.3	10.4
20°-30°	1060.0	15.3
30°-40°	1231.1	17.8
40°-50°	1229.6	17.7
50°-60°	1072.2	15.5
60°-70°	792.6	11.4
70°-80°	448.4	6.5
80°-90°	118.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2037.7	29.4
0°-40°	3268.8	47.2
0°-60°	5570.6	80.4
0°-90°	6930.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	126
90°	0	0	0	0	0	

TEST NUMBER: P931085

CATALOG NUMBER: DFN2DS-SQ4F0-070DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931085

CATALOG NUMBER: DFN2DS-SQ4F0-070DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.53	15.14	13.90	15.46	15.77	13.09	14.70	13.45	15.01	15.33
	3H	15.28	16.74	15.66	17.06	17.42	14.79	16.25	15.17	16.57	16.93
	4H	15.93	17.30	16.33	17.65	18.02	15.43	16.80	15.83	17.15	17.53
	6H	16.40	17.67	16.81	18.03	18.42	15.90	17.17	16.31	17.53	17.92
	8H	16.54	17.75	16.97	18.14	18.54	16.04	17.25	16.46	17.64	18.04
	12H	16.63	17.79	17.06	18.17	18.60	16.12	17.28	16.55	17.66	18.09
4H	2H	14.09	15.46	14.49	15.81	16.19	13.74	15.11	14.14	15.46	15.83
	3H	16.07	17.21	16.48	17.61	18.01	15.66	16.81	16.07	17.21	17.61
	4H	16.85	17.88	17.28	18.29	18.73	16.42	17.46	16.85	17.87	18.31
	6H	17.44	18.35	17.90	18.79	19.24	17.01	17.91	17.46	18.35	18.81
	8H	17.63	18.48	18.09	18.92	19.39	17.19	18.04	17.65	18.48	18.95
	12H	17.76	18.52	18.24	19.00	19.47	17.31	18.07	17.79	18.55	19.02
8H	4H	17.12	17.96	17.58	18.41	18.87	16.74	17.59	17.20	18.03	18.50
	6H	17.83	18.54	18.33	19.02	19.50	17.45	18.15	17.94	18.64	19.12
	8H	18.09	18.72	18.60	19.23	19.72	17.70	18.33	18.21	18.84	19.32
	12H	18.29	18.85	18.80	19.34	19.90	17.88	18.44	18.39	18.93	19.49
12H	4H	17.14	17.90	17.62	18.38	18.85	16.78	17.54	17.26	18.02	18.48
	6H	17.88	18.51	18.39	19.02	19.50	17.51	18.14	18.02	18.65	19.13
	8H	18.19	18.75	18.70	19.24	19.80	17.81	18.37	18.32	18.86	19.42