

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931122

Luminaire Tested: DFN2DS-SQ4F0-090DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-090DS835-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7650.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 90.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931122

CATALOG NUMBER: DFN2DS-SQ4F0-090DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931122

CATALOG NUMBER: DFN2DS-SQ4F0-090DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2610	2610	2610
5°	2620	2577	2592
10°	2600	2535	2514
15°	2570	2460	2389
20°	2529	2353	2235
25°	2486	2231	2085
30°	2428	2105	1893
35°	2370	1970	1724
40°	2313	1828	1529
45°	2245	1670	1353
50°	2175	1510	1180
55°	2104	1338	1013
60°	2022	1157	841
65°	1928	972	766
70°	1816	801	704
75°	1679	730	657
80°	1482	652	599
85°	1164	514	514

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2245 cd/sqm

TEST NUMBER: P931122

CATALOG NUMBER: DFN2DS-SQ4F0-090DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	4.6
10°-20°	957.0	12.5
20°-30°	1343.6	17.6
30°-40°	1464.6	19.1
40°-50°	1346.2	17.6
50°-60°	1057.2	13.8
60°-70°	688.1	9.0
70°-80°	354.2	4.6
80°-90°	90.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2649.2	34.6
0°-40°	4113.9	53.8
0°-60°	6517.2	85.2
0°-90°	7650.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7650.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	173
90°	0	0	0	0	0	



TEST NUMBER: P931122

CATALOG NUMBER: DFN2DS-SQ4F0-090DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931122

CATALOG NUMBER: DFN2DS-SQ4F0-090DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.57	16.09	14.93	16.40	16.72	10.53	12.05	10.89	12.36	12.68
	3H	16.33	17.70	16.71	18.03	18.39	11.79	13.16	12.17	13.49	13.85
	4H	17.00	18.28	17.40	18.63	19.01	12.30	13.58	12.69	13.92	14.30
	6H	17.49	18.67	17.90	19.04	19.43	12.68	13.86	13.09	14.23	14.62
	8H	17.65	18.78	18.08	19.17	19.57	12.80	13.93	13.23	14.32	14.72
	12H	17.76	18.84	18.19	19.22	19.65	12.88	13.96	13.31	14.34	14.77
4H	2H	14.67	15.95	15.07	16.30	16.68	11.22	12.50	11.62	12.85	13.23
	3H	16.61	17.67	17.02	18.07	18.47	12.67	13.73	13.08	14.13	14.53
	4H	17.35	18.31	17.79	18.73	19.17	13.27	14.22	13.70	14.64	15.08
	6H	17.95	18.78	18.40	19.22	19.68	13.75	14.59	14.21	15.03	15.49
	8H	18.16	18.94	18.62	19.38	19.85	13.92	14.69	14.38	15.14	15.61
	12H	18.31	19.01	18.80	19.49	19.96	14.03	14.73	14.52	15.21	15.68
8H	4H	17.38	18.16	17.84	18.60	19.07	13.62	14.40	14.08	14.84	15.31
	6H	18.02	18.66	18.51	19.15	19.63	14.21	14.85	14.70	15.34	15.82
	8H	18.27	18.84	18.78	19.35	19.84	14.43	15.00	14.94	15.51	16.00
	12H	18.47	18.98	18.98	19.47	20.04	14.61	15.12	15.12	15.61	16.17
12H	4H	17.36	18.06	17.85	18.54	19.01	13.66	14.36	14.15	14.84	15.31
	6H	18.00	18.57	18.51	19.08	19.57	14.27	14.85	14.78	15.36	15.85
	8H	18.28	18.79	18.79	19.28	19.85	14.54	15.05	15.05	15.55	16.11