

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930502

Luminaire Tested: DFN2DS-PN2F0-060DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS935-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4386.0 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930502

CATALOG NUMBER: DFN2DS-PN2F0-060DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930502

CATALOG NUMBER: DFN2DS-PN2F0-060DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4619	4619	4619
5°	4637	4561	4586
10°	4601	4487	4448
15°	4548	4353	4228
20°	4475	4164	3954
25°	4400	3948	3690
30°	4296	3726	3350
35°	4195	3486	3051
40°	4093	3236	2707
45°	3973	2956	2394
50°	3850	2673	2088
55°	3724	2368	1793
60°	3578	2048	1488
65°	3413	1721	1355
70°	3214	1417	1246
75°	2972	1292	1164
80°	2623	1154	1060
85°	2060	910	910

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3973 cd/sqm

TEST NUMBER: P930502

CATALOG NUMBER: DFN2DS-PN2F0-060DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	4.6
10°-20°	548.7	12.5
20°-30°	770.3	17.6
30°-40°	839.7	19.1
40°-50°	771.8	17.6
50°-60°	606.1	13.8
60°-70°	394.5	9.0
70°-80°	203.1	4.6
80°-90°	51.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.9	34.6
0°-40°	2358.6	53.8
0°-60°	3736.5	85.2
0°-90°	4386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2133	2133	2133	2133	2133	
5°	2133	2123	2098	2115	2110	202
15°	2028	2007	1942	1905	1886	572
25°	1841	1779	1652	1573	1544	847
35°	1586	1488	1318	1197	1154	993
45°	1297	1168	965	828	782	1002
55°	986	836	627	512	475	881
65°	666	510	336	270	264	660
75°	355	220	154	141	139	376
85°	83	42	37	37	37	99
90°	0	0	0	0	0	

TEST NUMBER: P930502

CATALOG NUMBER: DFN2DS-PN2F0-060DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2132.6	2132.6	2132.6	2132.6	2132.6
2.5°	2142.3	2132.6	2111.3	2130.7	2126.9
5°	2132.6	2123.0	2097.8	2115.3	2109.5
7.5°	2115.3	2103.7	2076.7	2084.3	2074.7
10°	2092.0	2078.5	2040.1	2034.2	2022.6
12.5°	2063.2	2045.8	1993.6	1982.1	1960.8
15°	2028.4	2007.1	1941.5	1904.9	1885.6
17.5°	1987.9	1956.9	1875.8	1833.4	1802.6
20°	1941.5	1902.8	1806.4	1758.3	1715.7
22.5°	1891.4	1846.9	1735.0	1669.4	1640.5
25°	1841.3	1779.4	1652.1	1573.0	1544.0
27.5°	1781.5	1715.7	1574.8	1484.1	1439.7
30°	1717.8	1644.2	1489.9	1391.6	1339.4
32.5°	1655.9	1567.1	1409.0	1293.1	1244.8
35°	1586.5	1488.1	1318.3	1196.6	1154.0
37.5°	1518.9	1412.6	1233.3	1100.0	1051.9
40°	1447.5	1331.8	1144.4	1007.4	957.3
42.5°	1374.2	1250.7	1055.7	912.8	864.7
45°	1297.0	1167.5	965.1	827.8	781.6
47.5°	1223.7	1086.7	878.2	741.1	698.7
50°	1142.6	1005.6	793.3	660.0	619.6
52.5°	1063.3	918.6	712.2	584.8	548.2
55°	986.2	835.7	627.2	511.5	474.8
57.5°	907.1	752.7	552.0	443.9	413.0
60°	826.0	671.7	472.8	374.5	343.6
62.5°	747.0	592.6	405.2	312.7	297.3
65°	665.9	509.5	335.8	270.3	264.4
67.5°	588.7	432.2	270.3	237.4	231.6
70°	507.6	357.1	223.8	204.6	196.8
72.5°	430.4	287.5	187.1	171.8	167.9
75°	355.1	219.9	154.4	140.9	139.1
77.5°	279.9	156.3	121.6	113.9	110.0
80°	210.3	112.0	92.5	85.0	85.0
82.5°	146.6	75.3	63.6	59.8	59.8
85°	82.9	42.4	36.6	36.6	36.6
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930502

CATALOG NUMBER: DFN2DS-PN2F0-060DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.55	18.07	16.92	18.39	18.70	12.51	14.03	12.88	14.35	14.66
	3H	18.32	19.68	18.69	20.01	20.37	13.78	15.14	14.15	15.47	15.83
	4H	18.98	20.26	19.38	20.61	20.99	14.28	15.56	14.68	15.91	16.29
	6H	19.47	20.65	19.88	21.02	21.41	14.66	15.84	15.07	16.21	16.60
	8H	19.64	20.76	20.06	21.15	21.55	14.78	15.91	15.21	16.30	16.70
	12H	19.74	20.82	20.17	21.20	21.63	14.87	15.94	15.30	16.33	16.76
4H	2H	16.65	17.94	17.05	18.28	18.66	13.21	14.49	13.61	14.84	15.21
	3H	18.59	19.65	19.00	20.05	20.45	14.65	15.71	15.06	16.11	16.51
	4H	19.34	20.29	19.77	20.71	21.15	15.25	16.21	15.68	16.62	17.06
	6H	19.93	20.76	20.39	21.20	21.66	15.74	16.57	16.20	17.01	17.47
	8H	20.14	20.92	20.61	21.37	21.83	15.90	16.68	16.36	17.12	17.59
	12H	20.30	20.99	20.78	21.47	21.94	16.02	16.71	16.50	17.19	17.66
8H	4H	19.36	20.14	19.83	20.58	21.05	15.60	16.38	16.07	16.83	17.29
	6H	20.00	20.64	20.50	21.13	21.61	16.19	16.83	16.69	17.32	17.80
	8H	20.25	20.83	20.76	21.34	21.82	16.41	16.99	16.93	17.50	17.99
	12H	20.45	20.96	20.96	21.46	22.02	16.59	17.10	17.10	17.59	18.16
12H	4H	19.35	20.04	19.83	20.52	20.99	15.65	16.34	16.13	16.82	17.29
	6H	19.98	20.56	20.49	21.07	21.56	16.25	16.83	16.77	17.34	17.83
	8H	20.26	20.77	20.77	21.27	21.83	16.53	17.04	17.04	17.53	18.09