

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930503

Luminaire Tested: DFN2DS-PN2F0-060DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS940-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5298.4 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930503

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930503

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4510	4510	4510
5°	4528	4462	4489
10°	4501	4417	4439
15°	4445	4360	4356
20°	4366	4274	4270
25°	4288	4168	4168
30°	4187	4072	4037
35°	4093	3955	3897
40°	3975	3838	3765
45°	3858	3723	3631
50°	3731	3603	3475
55°	3600	3463	3335
60°	3452	3297	3175
65°	3295	3130	2986
70°	3094	2929	2790
75°	2814	2697	2631
80°	2498	2422	2297
85°	2038	1941	1742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3858 cd/sqm

TEST NUMBER: P930503

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	3.7
10°-20°	551.5	10.4
20°-30°	810.5	15.3
30°-40°	941.3	17.8
40°-50°	940.1	17.7
50°-60°	819.8	15.5
60°-70°	606.0	11.4
70°-80°	342.9	6.5
80°-90°	90.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1558.0	29.4
0°-40°	2499.3	47.2
0°-60°	4259.1	80.4
0°-90°	5298.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5298.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2075	2052	2068	2065	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	826
35°	1548	1528	1496	1484	1474	967
45°	1260	1246	1215	1194	1186	972
55°	953	941	917	893	883	852
65°	643	631	611	593	583	636
75°	336	332	322	310	314	359
85°	82	80	78	72	70	96
90°	0	0	0	0	0	

TEST NUMBER: P930503

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2082.5	2082.5	2082.5	2082.5	2082.5
2.5°	2094.6	2084.6	2062.5	2082.5	2078.6
5°	2082.5	2074.6	2052.5	2068.5	2064.6
7.5°	2068.5	2056.6	2034.5	2050.6	2046.6
10°	2046.6	2032.6	2008.5	2024.5	2018.5
12.5°	2016.5	2004.5	1980.5	1990.5	1986.5
15°	1982.4	1970.5	1944.4	1952.5	1942.5
17.5°	1940.4	1928.5	1902.4	1912.3	1902.4
20°	1894.3	1882.4	1854.3	1860.3	1852.4
22.5°	1848.4	1830.3	1804.2	1804.2	1800.1
25°	1794.2	1778.3	1744.2	1748.1	1744.2
27.5°	1734.0	1720.0	1694.1	1688.2	1678.2
30°	1674.2	1658.0	1628.1	1622.1	1614.0
32.5°	1610.0	1598.1	1566.0	1553.9	1545.8
35°	1548.0	1528.0	1495.9	1483.8	1473.8
37.5°	1477.9	1459.8	1427.7	1413.6	1403.7
40°	1405.8	1389.6	1357.6	1339.8	1331.7
42.5°	1335.7	1319.5	1287.7	1267.5	1255.6
45°	1259.7	1245.6	1215.4	1193.6	1185.5
47.5°	1185.5	1171.5	1139.4	1117.3	1105.4
50°	1107.3	1097.3	1069.3	1041.2	1031.2
52.5°	1031.2	1017.2	991.3	969.2	955.2
55°	953.3	941.1	917.2	893.2	883.2
57.5°	875.1	865.2	839.0	815.0	806.9
60°	796.9	789.1	761.1	738.9	733.0
62.5°	720.8	706.8	686.8	666.9	658.8
65°	642.9	630.8	610.8	592.7	582.7
67.5°	562.8	552.6	534.8	520.7	512.6
70°	488.6	480.6	462.5	448.5	440.6
72.5°	412.6	404.5	394.5	380.5	374.6
75°	336.3	332.5	322.3	310.4	314.4
77.5°	268.3	260.3	256.2	250.3	244.3
80°	200.3	198.2	194.2	188.2	184.2
82.5°	136.2	136.2	134.2	126.2	126.2
85°	82.0	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930503

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.52	18.13	16.88	18.44	18.76	16.07	17.68	16.44	18.00	18.31
	3H	18.27	19.72	18.64	20.05	20.41	17.78	19.23	18.15	19.56	19.92
	4H	18.91	20.28	19.31	20.63	21.01	18.42	19.79	18.82	20.13	20.51
	6H	19.38	20.65	19.79	21.02	21.41	18.88	20.15	19.29	20.51	20.90
	8H	19.52	20.74	19.95	21.12	21.52	19.02	20.23	19.45	20.62	21.02
	12H	19.62	20.78	20.04	21.16	21.59	19.10	20.26	19.53	20.64	21.07
4H	2H	17.08	18.45	17.48	18.79	19.17	16.72	18.09	17.12	18.44	18.82
	3H	19.05	20.20	19.46	20.60	21.00	18.65	19.79	19.05	20.19	20.59
	4H	19.83	20.86	20.26	21.28	21.71	19.40	20.44	19.84	20.85	21.29
	6H	20.43	21.33	20.88	21.77	22.23	19.99	20.90	20.45	21.34	21.79
	8H	20.61	21.46	21.08	21.90	22.37	20.18	21.02	20.64	21.47	21.93
	12H	20.75	21.51	21.23	21.98	22.45	20.29	21.05	20.77	21.53	22.00
8H	4H	20.10	20.95	20.56	21.39	21.86	19.73	20.57	20.19	21.02	21.48
	6H	20.82	21.52	21.31	22.01	22.48	20.43	21.14	20.93	21.63	22.10
	8H	21.08	21.71	21.59	22.21	22.70	20.68	21.31	21.19	21.82	22.31
	12H	21.28	21.83	21.78	22.32	22.88	20.86	21.42	21.37	21.91	22.47
12H	4H	20.13	20.89	20.61	21.36	21.83	19.76	20.52	20.24	21.00	21.47
	6H	20.86	21.49	21.37	22.00	22.49	20.49	21.12	21.00	21.63	22.12
	8H	21.18	21.73	21.68	22.22	22.78	20.80	21.35	21.30	21.85	22.41

END OF REPORT