

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931090

Luminaire Tested: DFN2DS-SQ4F0-070DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-070DS850-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6598.5 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 69.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931090

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931090

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2251	2251	2251
5°	2260	2223	2235
10°	2243	2187	2168
15°	2217	2122	2061
20°	2181	2029	1927
25°	2145	1924	1798
30°	2094	1816	1633
35°	2045	1699	1487
40°	1995	1577	1319
45°	1936	1441	1167
50°	1876	1303	1018
55°	1815	1154	874
60°	1744	998	725
65°	1663	839	660
70°	1567	691	607
75°	1448	630	567
80°	1279	563	517
85°	1005	444	444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1936 cd/sqm

TEST NUMBER: P931090

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	4.6
10°-20°	825.5	12.5
20°-30°	1158.9	17.6
30°-40°	1263.3	19.1
40°-50°	1161.1	17.6
50°-60°	911.9	13.8
60°-70°	593.5	9.0
70°-80°	305.5	4.6
80°-90°	78.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2285.1	34.6
0°-40°	3548.4	53.8
0°-60°	5621.4	85.2
0°-90°	6598.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6598.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3208	3208	3208	3208	3208	
5°	3208	3194	3156	3182	3174	304
15°	3052	3020	2921	2866	2837	860
25°	2770	2677	2485	2366	2323	1274
35°	2387	2239	1983	1800	1736	1494
45°	1951	1756	1452	1246	1176	1507
55°	1484	1257	944	770	714	1326
65°	1002	766	505	407	398	993
75°	534	331	232	212	209	565
85°	125	64	55	55	55	150
90°	0	0	0	0	0	

TEST NUMBER: P931090

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3208.4	3208.4	3208.4	3208.4	3208.4
2.5°	3222.9	3208.4	3176.4	3205.7	3199.8
5°	3208.4	3193.9	3156.1	3182.3	3173.6
7.5°	3182.3	3165.0	3124.4	3135.7	3121.3
10°	3147.5	3127.2	3069.2	3060.3	3043.0
12.5°	3104.0	3077.8	2999.3	2982.0	2949.9
15°	3051.6	3019.6	2921.0	2865.9	2836.9
17.5°	2990.6	2944.2	2822.2	2758.3	2711.8
20°	2921.0	2862.8	2717.7	2645.3	2581.2
22.5°	2845.6	2778.7	2610.1	2511.6	2468.2
25°	2770.1	2677.0	2485.4	2366.5	2322.8
27.5°	2680.1	2581.2	2369.3	2232.9	2166.0
30°	2584.3	2473.7	2241.4	2093.6	2015.1
32.5°	2491.3	2357.6	2119.7	1945.4	1872.7
35°	2386.8	2238.6	1983.3	1800.4	1736.3
37.5°	2285.2	2125.3	1855.5	1654.8	1582.5
40°	2177.6	2003.6	1721.7	1515.7	1440.1
42.5°	2067.4	1881.6	1588.3	1373.3	1301.0
45°	1951.3	1756.5	1451.9	1245.5	1175.9
47.5°	1840.9	1634.9	1321.3	1114.9	1051.1
50°	1719.0	1512.9	1193.4	992.9	932.2
52.5°	1599.7	1381.9	1071.4	879.8	824.7
55°	1483.6	1257.2	943.5	769.5	714.4
57.5°	1364.7	1132.4	830.5	667.8	621.4
60°	1242.7	1010.4	711.3	563.5	516.9
62.5°	1123.7	891.5	609.6	470.4	447.3
65°	1001.8	766.4	505.3	406.7	397.7
67.5°	885.6	650.3	406.7	357.0	348.4
70°	763.7	537.2	336.7	307.7	296.0
72.5°	647.5	432.5	281.6	258.5	252.6
75°	534.2	330.8	232.2	211.9	209.2
77.5°	421.1	235.0	183.0	171.2	165.5
80°	316.4	168.5	139.3	127.9	127.9
82.5°	220.6	113.3	95.8	89.9	89.9
85°	124.8	63.8	55.1	55.1	55.1
87.5°	46.5	23.1	23.1	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931090

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.05	15.58	14.42	15.89	16.20	10.01	11.54	10.38	11.85	12.16
	3H	15.82	17.18	16.20	17.51	17.87	11.28	12.64	11.66	12.97	13.33
	4H	16.49	17.77	16.89	18.11	18.49	11.78	13.06	12.18	13.41	13.79
	6H	16.97	18.16	17.39	18.52	18.92	12.16	13.35	12.57	13.71	14.10
	8H	17.14	18.27	17.57	18.66	19.06	12.29	13.41	12.71	13.80	14.20
	12H	17.24	18.32	17.67	18.70	19.13	12.37	13.45	12.80	13.83	14.26
4H	2H	14.16	15.44	14.56	15.79	16.17	10.71	11.99	11.11	12.34	12.72
	3H	16.09	17.15	16.50	17.55	17.96	12.15	13.22	12.56	13.62	14.02
	4H	16.84	17.80	17.27	18.21	18.65	12.75	13.71	13.18	14.12	14.56
	6H	17.43	18.26	17.89	18.71	19.17	13.24	14.07	13.70	14.52	14.98
	8H	17.65	18.42	18.11	18.87	19.34	13.40	14.18	13.87	14.62	15.09
	12H	17.80	18.50	18.28	18.97	19.44	13.52	14.21	14.00	14.69	15.16
8H	4H	16.86	17.64	17.33	18.09	18.55	13.11	13.88	13.57	14.33	14.79
	6H	17.50	18.14	18.00	18.64	19.11	13.69	14.34	14.19	14.83	15.30
	8H	17.75	18.33	18.27	18.84	19.33	13.91	14.49	14.43	15.00	15.49
	12H	17.96	18.47	18.47	18.96	19.52	14.09	14.60	14.60	15.09	15.66
12H	4H	16.85	17.54	17.33	18.02	18.49	13.15	13.84	13.63	14.32	14.79
	6H	17.48	18.06	18.00	18.57	19.06	13.76	14.33	14.27	14.84	15.33
	8H	17.77	18.28	18.28	18.77	19.33	14.03	14.54	14.54	15.03	15.60