

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931108

Luminaire Tested: DFN2DS-SQ4F0-080DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931108
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-080DS850-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7541.2 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 79.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931108

CATALOG NUMBER: DFN2DS-SQ4F0-080DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931108

CATALOG NUMBER: DFN2DS-SQ4F0-080DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2573	2573	2573
5°	2583	2541	2555
10°	2563	2499	2478
15°	2533	2425	2355
20°	2493	2319	2203
25°	2451	2199	2055
30°	2393	2076	1866
35°	2337	1942	1700
40°	2280	1802	1508
45°	2213	1647	1334
50°	2144	1489	1163
55°	2074	1319	999
60°	1993	1141	829
65°	1901	958	755
70°	1791	789	694
75°	1655	720	648
80°	1461	643	590
85°	1148	507	507

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2213 cd/sqm

TEST NUMBER: P931108

CATALOG NUMBER: DFN2DS-SQ4F0-080DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	4.6
10°-20°	943.4	12.5
20°-30°	1324.5	17.6
30°-40°	1443.8	19.1
40°-50°	1327.0	17.6
50°-60°	1042.1	13.8
60°-70°	678.3	9.0
70°-80°	349.2	4.6
80°-90°	89.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2611.6	34.6
0°-40°	4055.4	53.8
0°-60°	6424.5	85.2
0°-90°	7541.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7541.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	171
90°	0	0	0	0	0	

TEST NUMBER: P931108

CATALOG NUMBER: DFN2DS-SQ4F0-080DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931108

CATALOG NUMBER: DFN2DS-SQ4F0-080DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.52	16.04	14.88	16.35	16.67	10.48	12.00	10.84	12.31	12.63
	3H	16.28	17.65	16.66	17.98	18.34	11.74	13.11	12.12	13.44	13.80
	4H	16.95	18.23	17.35	18.58	18.96	12.25	13.53	12.65	13.88	14.25
	6H	17.44	18.62	17.85	18.99	19.38	12.63	13.81	13.04	14.18	14.57
	8H	17.60	18.73	18.03	19.12	19.52	12.75	13.88	13.18	14.27	14.67
	12H	17.71	18.79	18.14	19.17	19.60	12.83	13.91	13.26	14.29	14.72
4H	2H	14.62	15.90	15.02	16.25	16.63	11.17	12.45	11.57	12.80	13.18
	3H	16.56	17.62	16.97	18.02	18.42	12.62	13.68	13.03	14.08	14.48
	4H	17.31	18.26	17.74	18.68	19.12	13.22	14.17	13.65	14.59	15.03
	6H	17.90	18.73	18.35	19.17	19.63	13.70	14.54	14.16	14.98	15.44
	8H	18.11	18.89	18.57	19.33	19.80	13.87	14.64	14.33	15.09	15.56
	12H	18.26	18.96	18.75	19.44	19.91	13.98	14.68	14.47	15.16	15.63
8H	4H	17.33	18.11	17.79	18.55	19.02	13.57	14.35	14.03	14.79	15.26
	6H	17.97	18.61	18.46	19.10	19.58	14.16	14.80	14.65	15.29	15.77
	8H	18.22	18.79	18.73	19.30	19.79	14.38	14.95	14.89	15.46	15.95
	12H	18.42	18.93	18.93	19.42	19.99	14.56	15.07	15.07	15.56	16.12
12H	4H	17.31	18.01	17.80	18.49	18.96	13.61	14.31	14.10	14.79	15.26
	6H	17.95	18.53	18.46	19.03	19.52	14.22	14.80	14.73	15.31	15.80
	8H	18.23	18.74	18.74	19.23	19.80	14.49	15.00	15.00	15.50	16.06