

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930543

Luminaire Tested: DFN2DS-PN3F0-050DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-050DS830-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4662.9 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930543

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930543

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2142	2142	2142
5°	2151	2120	2132
10°	2138	2098	2109
15°	2111	2071	2069
20°	2074	2030	2028
25°	2037	1980	1980
30°	1989	1934	1917
35°	1944	1879	1851
40°	1888	1823	1788
45°	1833	1768	1725
50°	1772	1711	1650
55°	1710	1645	1584
60°	1640	1566	1508
65°	1565	1487	1418
70°	1470	1391	1325
75°	1337	1281	1250
80°	1187	1150	1091
85°	968	923	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1833 cd/sqm

TEST NUMBER: P930543

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.5	3.7
10°-20°	485.3	10.4
20°-30°	713.2	15.3
30°-40°	828.4	17.8
40°-50°	827.4	17.7
50°-60°	721.4	15.5
60°-70°	533.3	11.4
70°-80°	301.7	6.5
80°-90°	79.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.1	29.4
0°-40°	2199.4	47.2
0°-60°	3748.2	80.4
0°-90°	4662.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4662.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1826	1806	1820	1817	174
15°	1745	1734	1711	1718	1709	491
25°	1579	1565	1535	1538	1535	727
35°	1362	1345	1316	1306	1297	851
45°	1108	1096	1070	1050	1043	856
55°	839	828	807	786	777	750
65°	566	555	538	522	513	559
75°	296	293	284	273	277	316
85°	72	70	69	63	62	85
90°	0	0	0	0	0	

TEST NUMBER: P930543

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.7	1832.7	1832.7	1832.7	1832.7
2.5°	1843.3	1834.5	1815.1	1832.7	1829.4
5°	1832.7	1825.8	1806.3	1820.3	1817.0
7.5°	1820.3	1809.9	1790.5	1804.7	1801.1
10°	1801.1	1788.8	1767.7	1781.6	1776.4
12.5°	1774.5	1764.1	1743.0	1751.7	1748.2
15°	1744.6	1734.1	1711.1	1718.3	1709.4
17.5°	1707.6	1697.1	1674.1	1682.9	1674.1
20°	1667.1	1656.6	1631.9	1637.1	1630.2
22.5°	1626.6	1610.7	1587.7	1587.7	1584.2
25°	1579.0	1564.9	1535.0	1538.4	1535.0
27.5°	1526.0	1513.7	1490.9	1485.6	1476.9
30°	1473.3	1459.2	1432.8	1427.5	1420.4
32.5°	1416.9	1406.4	1378.1	1367.5	1360.4
35°	1362.2	1344.7	1316.4	1305.8	1297.0
37.5°	1300.5	1284.7	1256.4	1244.1	1235.3
40°	1237.2	1223.0	1194.7	1179.0	1171.9
42.5°	1175.5	1161.3	1133.2	1115.4	1105.0
45°	1108.5	1096.2	1069.6	1050.4	1043.3
47.5°	1043.3	1030.9	1002.8	983.3	972.8
50°	974.5	965.7	941.1	916.4	907.5
52.5°	907.5	895.2	872.4	853.0	840.6
55°	838.9	828.3	807.1	786.0	777.2
57.5°	770.1	761.3	738.3	717.2	710.1
60°	701.3	694.4	669.8	650.3	645.1
62.5°	634.4	622.1	604.5	586.9	579.8
65°	565.8	555.1	537.5	521.7	512.8
67.5°	495.3	486.4	470.6	458.3	451.1
70°	430.0	423.0	407.0	394.7	387.8
72.5°	363.1	356.0	347.2	334.9	329.6
75°	296.0	292.6	283.6	273.2	276.8
77.5°	236.2	229.0	225.5	220.2	215.1
80°	176.3	174.5	170.9	165.7	162.1
82.5°	119.8	119.8	118.1	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.7	28.3	24.7	19.4	17.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930543

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.93	15.54	14.29	15.85	16.17	13.49	15.10	13.85	15.41	15.72
	3H	15.68	17.13	16.06	17.46	17.82	15.19	16.64	15.57	16.97	17.33
	4H	16.33	17.70	16.72	18.04	18.42	15.83	17.20	16.23	17.55	17.92
	6H	16.80	18.06	17.21	18.43	18.82	16.29	17.56	16.71	17.93	18.32
	8H	16.94	18.15	17.36	18.54	18.94	16.44	17.65	16.86	18.04	18.43
	12H	17.03	18.19	17.46	18.57	19.00	16.52	17.68	16.95	18.06	18.49
4H	2H	14.49	15.86	14.89	16.21	16.58	14.14	15.51	14.54	15.85	16.23
	3H	16.47	17.61	16.87	18.01	18.41	16.06	17.20	16.47	17.60	18.00
	4H	17.24	18.28	17.67	18.69	19.13	16.82	17.85	17.25	18.27	18.70
	6H	17.84	18.74	18.29	19.18	19.64	17.41	18.31	17.86	18.75	19.21
	8H	18.03	18.87	18.49	19.32	19.78	17.59	18.44	18.05	18.88	19.34
	12H	18.16	18.92	18.64	19.40	19.86	17.71	18.47	18.19	18.94	19.41
8H	4H	17.52	18.36	17.98	18.80	19.27	17.14	17.99	17.60	18.43	18.90
	6H	18.23	18.93	18.72	19.42	19.90	17.85	18.55	18.34	19.04	19.51
	8H	18.49	19.12	19.00	19.63	20.11	18.10	18.73	18.61	19.23	19.72
	12H	18.69	19.25	19.20	19.74	20.30	18.28	18.83	18.78	19.32	19.89
12H	4H	17.54	18.30	18.02	18.78	19.25	17.18	17.94	17.66	18.41	18.88
	6H	18.27	18.91	18.78	19.41	19.90	17.91	18.54	18.42	19.05	19.53
	8H	18.59	19.15	19.10	19.64	20.20	18.21	18.77	18.72	19.26	19.82