

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930580

Luminaire Tested: DFN2DS-PN3F0-070DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-070DS830-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5604.9 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 73.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930580

CATALOG NUMBER: DFN2DS-PN3F0-070DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930580

CATALOG NUMBER: DFN2DS-PN3F0-070DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3186	3186	3186
5°	3198	3146	3163
10°	3173	3095	3068
15°	3137	3003	2916
20°	3086	2872	2727
25°	3035	2723	2545
30°	2963	2570	2310
35°	2893	2404	2105
40°	2823	2232	1867
45°	2740	2039	1651
50°	2655	1844	1440
55°	2568	1634	1237
60°	2468	1413	1027
65°	2354	1187	934
70°	2217	978	859
75°	2050	891	803
80°	1810	796	731
85°	1422	628	628

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2740 cd/sqm

TEST NUMBER: P930580

CATALOG NUMBER: DFN2DS-PN3F0-070DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.4	4.6
10°-20°	701.2	12.5
20°-30°	984.4	17.6
30°-40°	1073.1	19.1
40°-50°	986.3	17.6
50°-60°	774.6	13.8
60°-70°	504.2	9.0
70°-80°	259.5	4.6
80°-90°	66.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1941.0	34.6
0°-40°	3014.1	53.8
0°-60°	4775.0	85.2
0°-90°	5604.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5604.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2725	2725	2725	2725	2725	
5°	2725	2713	2681	2703	2696	258
15°	2592	2565	2481	2434	2410	730
25°	2353	2274	2111	2010	1973	1082
35°	2027	1902	1685	1529	1475	1269
45°	1657	1492	1233	1058	999	1280
55°	1260	1068	802	654	607	1126
65°	851	651	429	345	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	127
90°	0	0	0	0	0	

TEST NUMBER: P930580

CATALOG NUMBER: DFN2DS-PN3F0-070DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2725.3	2725.3	2725.3	2725.3	2725.3
2.5°	2737.5	2725.3	2698.1	2722.9	2718.0
5°	2725.3	2713.0	2680.8	2703.1	2695.7
7.5°	2703.1	2688.4	2653.9	2663.5	2651.3
10°	2673.5	2656.3	2607.0	2599.4	2584.8
12.5°	2636.6	2614.3	2547.6	2532.9	2505.7
15°	2592.1	2564.9	2481.1	2434.3	2409.7
17.5°	2540.3	2500.8	2397.2	2342.9	2303.5
20°	2481.1	2431.7	2308.5	2247.0	2192.5
22.5°	2417.1	2360.3	2217.1	2133.3	2096.5
25°	2352.9	2273.9	2111.1	2010.1	1973.0
27.5°	2276.5	2192.5	2012.5	1896.6	1839.8
30°	2195.1	2101.2	1903.9	1778.3	1711.6
32.5°	2116.1	2002.6	1800.5	1652.5	1590.7
35°	2027.4	1901.5	1684.7	1529.2	1474.8
37.5°	1941.1	1805.2	1576.1	1405.7	1344.2
40°	1849.7	1701.9	1462.5	1287.4	1223.3
42.5°	1756.1	1598.3	1349.1	1166.5	1105.1
45°	1657.4	1492.0	1233.3	1058.0	998.8
47.5°	1563.7	1388.7	1122.3	947.0	892.8
50°	1460.1	1285.1	1013.7	843.4	791.8
52.5°	1358.8	1173.8	910.1	747.3	700.5
55°	1260.2	1067.9	801.5	653.7	606.8
57.5°	1159.2	961.9	705.5	567.3	527.8
60°	1055.6	858.3	604.2	478.6	439.1
62.5°	954.5	757.3	517.8	399.6	379.9
65°	850.9	651.0	429.2	345.4	337.8
67.5°	752.3	552.4	345.4	303.2	296.0
70°	648.7	456.3	286.0	261.4	251.4
72.5°	550.0	367.4	239.2	219.6	214.6
75°	453.8	281.0	197.3	180.0	177.7
77.5°	357.7	199.6	155.4	145.4	140.5
80°	268.8	143.1	118.3	108.6	108.6
82.5°	187.4	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930580

CATALOG NUMBER: DFN2DS-PN3F0-070DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.26	16.78	15.63	17.10	17.41	11.22	12.74	11.59	13.06	13.37
	3H	17.03	18.39	17.40	18.72	19.08	12.49	13.85	12.86	14.18	14.54
	4H	17.69	18.97	18.09	19.32	19.70	12.99	14.27	13.39	14.62	15.00
	6H	18.18	19.36	18.59	19.73	20.12	13.37	14.55	13.78	14.92	15.31
	8H	18.35	19.47	18.77	19.86	20.26	13.49	14.62	13.92	15.01	15.41
	12H	18.45	19.53	18.88	19.91	20.34	13.57	14.65	14.00	15.03	15.46
4H	2H	15.36	16.65	15.76	16.99	17.37	11.92	13.20	12.32	13.55	13.92
	3H	17.30	18.36	17.71	18.76	19.16	13.36	14.42	13.77	14.82	15.22
	4H	18.05	19.00	18.48	19.42	19.86	13.96	14.92	14.39	15.33	15.77
	6H	18.64	19.47	19.10	19.91	20.37	14.45	15.28	14.90	15.72	16.18
	8H	18.85	19.63	19.32	20.07	20.54	14.61	15.39	15.07	15.83	16.30
	12H	19.01	19.70	19.49	20.18	20.65	14.73	15.42	15.21	15.90	16.37
8H	4H	18.07	18.85	18.53	19.29	19.76	14.31	15.09	14.78	15.53	16.00
	6H	18.71	19.35	19.21	19.84	20.32	14.90	15.54	15.40	16.03	16.51
	8H	18.96	19.54	19.47	20.05	20.53	15.12	15.70	15.63	16.21	16.69
	12H	19.16	19.67	19.67	20.17	20.73	15.30	15.81	15.81	16.30	16.87
12H	4H	18.06	18.75	18.54	19.23	19.70	14.36	15.05	14.84	15.53	16.00
	6H	18.69	19.27	19.20	19.78	20.27	14.96	15.54	15.48	16.05	16.54
	8H	18.97	19.48	19.48	19.98	20.54	15.24	15.75	15.75	16.24	16.80