

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931073

Luminaire Tested: DFN2DS-SQ4F0-060DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-060DS927-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4704.5 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 57.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931073

CATALOG NUMBER: DFN2DS-SQ4F0-060DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931073

CATALOG NUMBER: DFN2DS-SQ4F0-060DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1297	1297	1297
5°	1302	1284	1291
10°	1295	1271	1277
15°	1279	1254	1253
20°	1256	1229	1228
25°	1233	1199	1199
30°	1204	1171	1161
35°	1177	1138	1121
40°	1143	1104	1083
45°	1110	1071	1045
50°	1073	1036	999
55°	1035	996	959
60°	993	948	913
65°	948	901	859
70°	890	843	803
75°	810	776	757
80°	719	697	661
85°	586	559	502

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1110 cd/sqm

TEST NUMBER: P931073

CATALOG NUMBER: DFN2DS-SQ4F0-060DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.0	3.7
10°-20°	489.7	10.4
20°-30°	719.6	15.3
30°-40°	835.8	17.8
40°-50°	834.7	17.7
50°-60°	727.9	15.5
60°-70°	538.1	11.4
70°-80°	304.4	6.5
80°-90°	80.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.3	29.4
0°-40°	2219.1	47.2
0°-60°	3781.7	80.4
0°-90°	4704.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4704.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1822	1837	1833	176
15°	1760	1750	1726	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1374	1357	1328	1317	1308	858
45°	1118	1106	1079	1060	1053	863
55°	846	836	814	793	784	757
65°	571	560	542	526	517	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	86
90°	0	0	0	0	0	

TEST NUMBER: P931073

CATALOG NUMBER: DFN2DS-SQ4F0-060DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1849.0	1849.0	1849.0	1849.0	1849.0
2.5°	1859.8	1850.9	1831.3	1849.0	1845.6
5°	1849.0	1842.0	1822.4	1836.6	1833.2
7.5°	1836.6	1826.0	1806.4	1820.7	1817.2
10°	1817.2	1804.7	1783.3	1797.5	1792.2
12.5°	1790.4	1779.8	1758.5	1767.3	1763.8
15°	1760.1	1749.6	1726.4	1733.6	1724.7
17.5°	1722.8	1712.3	1689.1	1697.9	1689.1
20°	1681.9	1671.4	1646.4	1651.7	1644.7
22.5°	1641.2	1625.1	1601.9	1601.9	1598.3
25°	1593.0	1578.9	1548.7	1552.1	1548.7
27.5°	1539.6	1527.2	1504.2	1498.9	1490.1
30°	1486.5	1472.1	1445.6	1440.3	1433.0
32.5°	1429.5	1418.9	1390.4	1379.7	1372.5
35°	1374.4	1356.7	1328.2	1317.4	1308.5
37.5°	1312.2	1296.1	1267.7	1255.2	1246.3
40°	1248.2	1233.9	1205.4	1189.6	1182.4
42.5°	1185.9	1171.6	1143.3	1125.4	1114.8
45°	1118.5	1105.9	1079.2	1059.8	1052.6
47.5°	1052.6	1040.1	1011.7	992.1	981.4
50°	983.2	974.3	949.4	924.5	915.6
52.5°	915.6	903.2	880.1	860.6	848.2
55°	846.4	835.6	814.3	793.0	784.2
57.5°	777.0	768.2	745.0	723.7	716.4
60°	707.6	700.6	675.7	656.1	650.8
62.5°	640.0	627.6	609.8	592.1	585.0
65°	570.8	560.1	542.4	526.3	517.4
67.5°	499.7	490.6	474.8	462.4	455.2
70°	433.9	426.7	410.7	398.2	391.2
72.5°	366.3	359.2	350.3	337.9	332.6
75°	298.6	295.3	286.1	275.6	279.2
77.5°	238.2	231.1	227.5	222.2	216.9
80°	177.9	176.0	172.4	167.1	163.5
82.5°	120.9	120.9	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931073

CATALOG NUMBER: DFN2DS-SQ4F0-060DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.19	13.80	12.55	14.11	14.43	11.74	13.35	12.11	13.67	13.98
	3H	13.94	15.39	14.31	15.72	16.08	13.45	14.90	13.82	15.23	15.59
	4H	14.58	15.95	14.98	16.30	16.68	14.09	15.46	14.49	15.81	16.18
	6H	15.05	16.32	15.46	16.69	17.08	14.55	15.82	14.96	16.18	16.58
	8H	15.20	16.41	15.62	16.80	17.19	14.69	15.90	15.12	16.29	16.69
	12H	15.29	16.45	15.72	16.83	17.26	14.77	15.93	15.20	16.32	16.74
4H	2H	12.75	14.12	13.15	14.47	14.84	12.40	13.76	12.79	14.11	14.49
	3H	14.72	15.87	15.13	16.27	16.67	14.32	15.46	14.73	15.86	16.26
	4H	15.50	16.54	15.93	16.95	17.39	15.08	16.11	15.51	16.53	16.96
	6H	16.10	17.00	16.55	17.44	17.90	15.66	16.57	16.12	17.01	17.47
	8H	16.29	17.13	16.75	17.57	18.04	15.85	16.69	16.31	17.14	17.60
	12H	16.42	17.18	16.90	17.65	18.12	15.97	16.73	16.45	17.20	17.67
8H	4H	15.77	16.62	16.23	17.06	17.53	15.40	16.25	15.86	16.69	17.15
	6H	16.49	17.19	16.98	17.68	18.15	16.11	16.81	16.60	17.30	17.77
	8H	16.75	17.38	17.26	17.88	18.37	16.35	16.99	16.86	17.49	17.98
	12H	16.95	17.50	17.45	17.99	18.56	16.53	17.09	17.04	17.58	18.14
12H	4H	15.80	16.56	16.28	17.03	17.50	15.43	16.19	15.91	16.67	17.14
	6H	16.53	17.16	17.04	17.67	18.16	16.16	16.80	16.67	17.30	17.79
	8H	16.85	17.40	17.35	17.89	18.46	16.47	17.03	16.98	17.52	18.08