

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931091

Luminaire Tested: DFN2DS-SQ4F0-070DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-070DS927-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5488.6 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 69.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931091

CATALOG NUMBER: DFN2DS-SQ4F0-070DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931091

CATALOG NUMBER: DFN2DS-SQ4F0-070DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1514	1514	1514
5°	1519	1498	1506
10°	1511	1482	1490
15°	1492	1463	1462
20°	1465	1434	1433
25°	1439	1399	1399
30°	1405	1366	1355
35°	1374	1327	1308
40°	1334	1288	1263
45°	1295	1249	1219
50°	1252	1209	1166
55°	1208	1162	1119
60°	1158	1106	1066
65°	1106	1050	1002
70°	1039	983	936
75°	945	905	883
80°	838	813	771
85°	684	652	584

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1295 cd/sqm

TEST NUMBER: P931091

CATALOG NUMBER: DFN2DS-SQ4F0-070DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.0	3.7
10°-20°	571.3	10.4
20°-30°	839.5	15.3
30°-40°	975.1	17.8
40°-50°	973.8	17.7
50°-60°	849.2	15.5
60°-70°	627.7	11.4
70°-80°	355.2	6.5
80°-90°	93.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1613.8	29.4
0°-40°	2588.9	47.2
0°-60°	4411.9	80.4
0°-90°	5488.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5488.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2157	2157	2157	2157	2157	
5°	2157	2149	2126	2143	2139	205
15°	2054	2041	2014	2022	2012	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1001
45°	1305	1290	1259	1236	1228	1007
55°	988	975	950	925	915	883
65°	666	653	633	614	604	658
75°	348	344	334	322	326	372
85°	85	83	81	75	73	100
90°	0	0	0	0	0	

TEST NUMBER: P931091

CATALOG NUMBER: DFN2DS-SQ4F0-070DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.2	2157.2	2157.2	2157.2	2157.2
2.5°	2169.8	2159.4	2136.5	2157.2	2153.2
5°	2157.2	2149.1	2126.2	2142.7	2138.7
7.5°	2142.7	2130.3	2107.4	2124.2	2120.0
10°	2120.0	2105.5	2080.6	2097.1	2091.0
12.5°	2088.7	2076.5	2051.6	2061.9	2057.7
15°	2053.6	2041.2	2014.1	2022.5	2012.2
17.5°	2009.9	1997.7	1970.6	1981.0	1970.6
20°	1962.2	1949.9	1920.8	1927.0	1918.9
22.5°	1914.7	1896.0	1868.9	1868.9	1864.7
25°	1858.6	1842.0	1806.9	1810.8	1806.9
27.5°	1796.3	1781.8	1754.9	1748.7	1738.4
30°	1734.2	1717.5	1686.5	1680.3	1671.9
32.5°	1667.7	1655.4	1622.2	1609.7	1601.3
35°	1603.5	1582.8	1549.5	1537.0	1526.7
37.5°	1530.9	1512.2	1478.9	1464.4	1454.0
40°	1456.3	1439.5	1406.3	1387.8	1379.4
42.5°	1383.6	1366.9	1333.9	1313.0	1300.6
45°	1304.8	1290.3	1259.0	1236.4	1228.0
47.5°	1228.0	1213.5	1180.2	1157.3	1145.1
50°	1147.1	1136.7	1107.6	1078.6	1068.2
52.5°	1068.2	1053.8	1026.9	1004.0	989.4
55°	987.5	975.0	950.1	925.2	914.8
57.5°	906.5	896.1	869.1	844.2	835.9
60°	825.5	817.3	788.4	765.5	759.3
62.5°	746.7	732.2	711.5	690.9	682.5
65°	666.0	653.4	632.7	614.0	603.7
67.5°	583.0	572.5	553.9	539.4	531.0
70°	506.2	497.9	479.1	464.6	456.4
72.5°	427.4	419.0	408.7	394.2	388.0
75°	348.4	344.4	333.8	321.6	325.7
77.5°	278.0	269.6	265.4	259.2	253.1
80°	207.5	205.4	201.2	195.0	190.8
82.5°	141.1	141.1	139.1	130.8	130.8
85°	85.0	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.9	20.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931091

CATALOG NUMBER: DFN2DS-SQ4F0-070DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.72	14.33	13.09	14.65	14.96	12.28	13.89	12.64	14.20	14.52
	3H	14.47	15.93	14.85	16.25	16.61	13.98	15.44	14.36	15.76	16.12
	4H	15.12	16.49	15.52	16.84	17.21	14.62	15.99	15.02	16.34	16.72
	6H	15.59	16.86	16.00	17.22	17.61	15.09	16.36	15.50	16.72	17.11
	8H	15.73	16.94	16.16	17.33	17.73	15.23	16.44	15.65	16.83	17.23
	12H	15.82	16.98	16.25	17.36	17.79	15.31	16.47	15.74	16.85	17.28
4H	2H	13.28	14.65	13.68	15.00	15.38	12.93	14.30	13.33	14.65	15.02
	3H	15.26	16.40	15.67	16.80	17.20	14.85	16.00	15.26	16.40	16.80
	4H	16.03	17.07	16.47	17.48	17.92	15.61	16.65	16.04	17.06	17.50
	6H	16.63	17.54	17.09	17.98	18.43	16.20	17.10	16.65	17.54	18.00
	8H	16.82	17.67	17.28	18.11	18.58	16.38	17.23	16.84	17.67	18.14
	12H	16.95	17.71	17.43	18.19	18.66	16.50	17.26	16.98	17.74	18.21
8H	4H	16.31	17.15	16.77	17.60	18.06	15.93	16.78	16.39	17.22	17.69
	6H	17.02	17.73	17.52	18.21	18.69	16.64	17.34	17.13	17.83	18.31
	8H	17.28	17.91	17.79	18.42	18.91	16.89	17.52	17.40	18.03	18.51
	12H	17.48	18.04	17.99	18.53	19.09	17.07	17.63	17.58	18.12	18.68
12H	4H	16.33	17.09	16.81	17.57	18.04	15.97	16.73	16.45	17.21	17.67
	6H	17.07	17.70	17.58	18.21	18.69	16.70	17.33	17.21	17.84	18.32
	8H	17.38	17.94	17.89	18.43	18.99	17.00	17.56	17.51	18.05	18.61