

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930528

Luminaire Tested: DFN2DS-PN3F0-040DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-040DS835-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3400.0 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930528

CATALOG NUMBER: DFN2DS-PN3F0-040DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930528

CATALOG NUMBER: DFN2DS-PN3F0-040DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1933	1933	1933
5°	1940	1908	1919
10°	1925	1877	1861
15°	1903	1822	1769
20°	1872	1742	1655
25°	1841	1652	1544
30°	1797	1559	1402
35°	1755	1458	1277
40°	1712	1354	1132
45°	1662	1237	1002
50°	1611	1118	873
55°	1558	991	750
60°	1497	857	623
65°	1428	720	567
70°	1345	593	521
75°	1243	541	487
80°	1097	483	444
85°	862	381	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1662 cd/sqm

TEST NUMBER: P930528

CATALOG NUMBER: DFN2DS-PN3F0-040DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	4.6
10°-20°	425.3	12.5
20°-30°	597.2	17.6
30°-40°	650.9	19.1
40°-50°	598.3	17.6
50°-60°	469.9	13.8
60°-70°	305.8	9.0
70°-80°	157.4	4.6
80°-90°	40.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1177.4	34.6
0°-40°	1828.4	53.8
0°-60°	2896.5	85.2
0°-90°	3400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3400.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	77
90°	0	0	0	0	0	

TEST NUMBER: P930528

CATALOG NUMBER: DFN2DS-PN3F0-040DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930528

CATALOG NUMBER: DFN2DS-PN3F0-040DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.52	15.05	13.89	15.36	15.67	9.48	11.01	9.85	11.32	11.63
	3H	15.29	16.65	15.67	16.98	17.34	10.75	12.11	11.13	12.44	12.80
	4H	15.96	17.24	16.36	17.58	17.96	11.25	12.53	11.65	12.88	13.26
	6H	16.44	17.63	16.86	17.99	18.39	11.63	12.82	12.04	13.18	13.57
	8H	16.61	17.74	17.04	18.13	18.53	11.76	12.88	12.18	13.27	13.67
	12H	16.71	17.79	17.14	18.17	18.60	11.84	12.92	12.27	13.30	13.73
4H	2H	13.63	14.91	14.03	15.26	15.64	10.18	11.46	10.58	11.81	12.19
	3H	15.56	16.62	15.97	17.02	17.42	11.62	12.69	12.03	13.09	13.49
	4H	16.31	17.27	16.74	17.68	18.12	12.22	13.18	12.65	13.59	14.03
	6H	16.90	17.73	17.36	18.18	18.64	12.71	13.54	13.17	13.99	14.44
	8H	17.12	17.89	17.58	18.34	18.81	12.87	13.65	13.34	14.09	14.56
	12H	17.27	17.96	17.75	18.44	18.91	12.99	13.68	13.47	14.16	14.63
8H	4H	16.33	17.11	16.80	17.56	18.02	12.58	13.35	13.04	13.80	14.27
	6H	16.97	17.61	17.47	18.11	18.58	13.16	13.81	13.66	14.30	14.77
	8H	17.22	17.80	17.74	18.31	18.80	13.38	13.96	13.90	14.47	14.96
	12H	17.43	17.94	17.94	18.43	18.99	13.56	14.07	14.07	14.56	15.13
12H	4H	16.32	17.01	16.80	17.49	17.96	12.62	13.31	13.10	13.79	14.26
	6H	16.95	17.53	17.47	18.04	18.53	13.23	13.80	13.74	14.31	14.80
	8H	17.24	17.75	17.75	18.24	18.80	13.50	14.01	14.01	14.50	15.07