

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931128

Luminaire Tested: DFN2DS-SQ4F0-090DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-090DS927-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6058.8 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 90.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931128

CATALOG NUMBER: DFN2DS-SQ4F0-090DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931128

CATALOG NUMBER: DFN2DS-SQ4F0-090DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2067	2067	2067
5°	2075	2041	2052
10°	2059	2008	1991
15°	2035	1948	1892
20°	2003	1863	1770
25°	1969	1767	1651
30°	1923	1668	1499
35°	1877	1560	1366
40°	1832	1448	1211
45°	1778	1323	1071
50°	1723	1196	934
55°	1666	1060	802
60°	1601	917	666
65°	1527	770	606
70°	1439	634	558
75°	1330	578	521
80°	1174	516	474
85°	922	407	407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1778 cd/sqm

TEST NUMBER: P931128

CATALOG NUMBER: DFN2DS-SQ4F0-090DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	4.6
10°-20°	758.0	12.5
20°-30°	1064.1	17.6
30°-40°	1160.0	19.1
40°-50°	1066.2	17.6
50°-60°	837.3	13.8
60°-70°	545.0	9.0
70°-80°	280.5	4.6
80°-90°	71.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2098.2	34.6
0°-40°	3258.2	53.8
0°-60°	5161.6	85.2
0°-90°	6058.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6058.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2946	2946	2946	2946	2946	
5°	2946	2933	2898	2922	2914	279
15°	2802	2773	2682	2631	2605	790
25°	2544	2458	2282	2173	2133	1170
35°	2192	2056	1821	1653	1594	1372
45°	1792	1613	1333	1144	1080	1384
55°	1362	1154	866	707	656	1217
65°	920	704	464	373	365	912
75°	490	304	213	195	192	519
85°	114	58	51	51	51	137
90°	0	0	0	0	0	

TEST NUMBER: P931128

CATALOG NUMBER: DFN2DS-SQ4F0-090DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2946.0	2946.0	2946.0	2946.0	2946.0
2.5°	2959.3	2946.0	2916.5	2943.5	2938.1
5°	2946.0	2932.7	2897.9	2921.9	2914.0
7.5°	2921.9	2906.1	2868.8	2879.2	2865.9
10°	2890.0	2871.3	2818.2	2809.9	2794.1
12.5°	2850.1	2826.1	2753.9	2738.1	2708.6
15°	2802.0	2772.6	2682.1	2631.4	2604.9
17.5°	2746.0	2703.3	2591.3	2532.7	2490.0
20°	2682.1	2628.6	2495.4	2428.9	2370.1
22.5°	2612.8	2551.4	2396.7	2306.1	2266.3
25°	2543.5	2458.1	2282.1	2172.9	2132.8
27.5°	2460.9	2370.1	2175.5	2050.2	1988.8
30°	2372.9	2271.4	2058.1	1922.3	1850.2
32.5°	2287.5	2164.7	1946.3	1786.3	1719.5
35°	2191.6	2055.6	1821.0	1653.1	1594.2
37.5°	2098.2	1951.5	1703.7	1519.5	1453.1
40°	1999.6	1839.7	1580.9	1391.7	1322.4
42.5°	1898.3	1727.7	1458.4	1261.0	1194.5
45°	1791.7	1612.9	1333.1	1143.6	1079.7
47.5°	1690.4	1501.2	1213.2	1023.7	965.1
50°	1578.4	1389.1	1095.8	911.7	855.9
52.5°	1468.9	1268.9	983.8	807.8	757.2
55°	1362.2	1154.3	866.4	706.6	655.9
57.5°	1253.1	1039.8	762.6	613.2	570.6
60°	1141.0	927.7	653.2	517.3	474.6
62.5°	1031.9	818.6	559.8	432.0	410.7
65°	919.8	703.8	463.9	373.3	365.2
67.5°	813.2	597.1	373.3	327.8	319.9
70°	701.2	493.3	309.2	282.6	271.8
72.5°	594.6	397.1	258.5	237.3	232.0
75°	490.5	303.8	213.3	194.6	192.1
77.5°	386.7	215.8	168.0	157.3	151.9
80°	290.5	154.8	127.8	117.4	117.4
82.5°	202.5	104.1	88.0	82.6	82.6
85°	114.5	58.5	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931128

CATALOG NUMBER: DFN2DS-SQ4F0-090DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.76	15.28	14.12	15.59	15.91	9.72	11.24	10.08	11.55	11.87
	3H	15.52	16.89	15.90	17.22	17.58	10.98	12.35	11.36	12.68	13.04
	4H	16.19	17.47	16.59	17.82	18.20	11.48	12.77	11.88	13.11	13.49
	6H	16.68	17.86	17.09	18.23	18.62	11.87	13.05	12.28	13.42	13.81
	8H	16.84	17.97	17.27	18.36	18.76	11.99	13.12	12.42	13.51	13.91
	12H	16.95	18.02	17.38	18.41	18.84	12.07	13.15	12.50	13.53	13.96
4H	2H	13.86	15.14	14.26	15.49	15.87	10.41	11.69	10.81	12.04	12.42
	3H	15.79	16.86	16.21	17.26	17.66	11.86	12.92	12.27	13.32	13.72
	4H	16.54	17.50	16.98	17.92	18.36	12.46	13.41	12.89	13.83	14.27
	6H	17.14	17.97	17.59	18.41	18.87	12.94	13.78	13.40	14.22	14.68
	8H	17.35	18.13	17.81	18.57	19.04	13.11	13.88	13.57	14.33	14.80
	12H	17.50	18.20	17.99	18.68	19.15	13.22	13.92	13.71	14.40	14.87
8H	4H	16.57	17.35	17.03	17.79	18.26	12.81	13.59	13.27	14.03	14.50
	6H	17.21	17.85	17.70	18.34	18.82	13.40	14.04	13.89	14.53	15.01
	8H	17.46	18.03	17.97	18.54	19.03	13.62	14.19	14.13	14.70	15.19
	12H	17.66	18.17	18.17	18.66	19.23	13.80	14.31	14.31	14.80	15.36
12H	4H	16.55	17.25	17.04	17.73	18.20	12.85	13.55	13.34	14.03	14.50
	6H	17.19	17.76	17.70	18.27	18.76	13.46	14.04	13.97	14.55	15.04
	8H	17.47	17.98	17.98	18.47	19.04	13.73	14.24	14.24	14.74	15.30

END OF REPORT