

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930582

Luminaire Tested: DFN2DS-PN3F0-070DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-070DS835-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5950.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 73.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930582
CATALOG NUMBER: DFN2DS-PN3F0-070DS835-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P930582

CATALOG NUMBER: DFN2DS-PN3F0-070DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3382	3382	3382
5°	3395	3340	3358
10°	3369	3285	3257
15°	3330	3188	3096
20°	3277	3049	2895
25°	3222	2891	2702
30°	3145	2728	2453
35°	3071	2552	2234
40°	2996	2369	1982
45°	2909	2164	1753
50°	2819	1957	1529
55°	2727	1734	1313
60°	2620	1500	1090
65°	2499	1260	992
70°	2354	1038	912
75°	2176	946	852
80°	1921	846	776
85°	1509	667	667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2909 cd/sqm



TEST NUMBER: P930582

CATALOG NUMBER: DFN2DS-PN3F0-070DS835-RL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	4.6
10°-20°	744.3	12.5
20°-30°	1045.0	17.6
30°-40°	1139.2	19.1
40°-50°	1047.0	17.6
50°-60°	822.3	13.8
60°-70°	535.2	9.0
70°-80°	275.5	4.6
80°-90°	70.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2060.5	34.6
0°-40°	3199.7	53.8
0°-60°	5068.9	85.2
0°-90°	5950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	135
90°	0	0	0	0	0	



TEST NUMBER: P930582

CATALOG NUMBER: DFN2DS-PN3F0-070DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930582
 CATALOG NUMBER: DFN2DS-PN3F0-070DS835-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	16.99	15.83	17.30	17.62	11.43	12.95	11.79	13.26	13.58
	3H	17.23	18.60	17.61	18.93	19.29	12.69	14.06	13.07	14.39	14.75
	4H	17.90	19.18	18.30	19.53	19.91	13.20	14.48	13.60	14.82	15.20
	6H	18.39	19.57	18.80	19.94	20.33	13.58	14.76	13.99	15.13	15.52
	8H	18.55	19.68	18.98	20.07	20.47	13.70	14.83	14.13	15.22	15.62
	12H	18.66	19.74	19.09	20.12	20.55	13.78	14.86	14.21	15.24	15.67
4H	2H	15.57	16.85	15.97	17.20	17.58	12.12	13.40	12.52	13.75	14.13
	3H	17.51	18.57	17.92	18.97	19.37	13.57	14.63	13.98	15.03	15.43
	4H	18.25	19.21	18.69	19.63	20.07	14.17	15.12	14.60	15.54	15.98
	6H	18.85	19.68	19.30	20.12	20.58	14.66	15.49	15.11	15.93	16.39
	8H	19.06	19.84	19.52	20.28	20.75	14.82	15.59	15.28	16.04	16.51
	12H	19.21	19.91	19.70	20.39	20.86	14.93	15.63	15.42	16.11	16.58
8H	4H	18.28	19.06	18.74	19.50	19.97	14.52	15.30	14.98	15.74	16.21
	6H	18.92	19.56	19.41	20.05	20.53	15.11	15.75	15.60	16.24	16.72
	8H	19.17	19.74	19.68	20.25	20.74	15.33	15.90	15.84	16.41	16.90
	12H	19.37	19.88	19.88	20.37	20.94	15.51	16.02	16.02	16.51	17.07
12H	4H	18.26	18.96	18.75	19.44	19.91	14.56	15.26	15.05	15.74	16.21
	6H	18.90	19.47	19.41	19.98	20.47	15.17	15.75	15.68	16.26	16.75
	8H	19.18	19.69	19.69	20.18	20.75	15.44	15.95	15.95	16.45	17.01