

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930584

Luminaire Tested: DFN2DS-PN3F0-070DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-070DS840-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5955.9 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 73.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930584
CATALOG NUMBER: DFN2DS-PN3F0-070DS840-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P930584

CATALOG NUMBER: DFN2DS-PN3F0-070DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3385	3385	3385
5°	3398	3343	3361
10°	3372	3288	3260
15°	3334	3191	3099
20°	3280	3052	2898
25°	3225	2893	2704
30°	3149	2731	2455
35°	3074	2555	2236
40°	3000	2372	1984
45°	2912	2167	1755
50°	2822	1959	1530
55°	2729	1736	1314
60°	2622	1501	1091
65°	2501	1262	993
70°	2356	1039	913
75°	2178	947	853
80°	1923	846	777
85°	1510	667	667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2912 cd/sqm



TEST NUMBER: P930584

CATALOG NUMBER: DFN2DS-PN3F0-070DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.4	4.6
10°-20°	745.1	12.5
20°-30°	1046.1	17.6
30°-40°	1140.3	19.1
40°-50°	1048.1	17.6
50°-60°	823.1	13.8
60°-70°	535.7	9.0
70°-80°	275.8	4.6
80°-90°	70.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2062.6	34.6
0°-40°	3202.9	53.8
0°-60°	5074.0	85.2
0°-90°	5955.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5955.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2896	2896	2896	2896	2896	
5°	2896	2883	2849	2872	2865	275
15°	2754	2726	2636	2587	2561	776
25°	2500	2416	2243	2136	2097	1150
35°	2154	2021	1790	1625	1567	1348
45°	1761	1586	1310	1124	1061	1360
55°	1339	1135	852	695	645	1197
65°	904	692	456	367	359	896
75°	482	299	210	191	189	510
85°	113	58	50	50	50	135
90°	0	0	0	0	0	



TEST NUMBER: P930584

CATALOG NUMBER: DFN2DS-PN3F0-070DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2896.0	2896.0	2896.0	2896.0	2896.0
2.5°	2909.0	2896.0	2867.1	2893.5	2888.2
5°	2896.0	2882.9	2848.7	2872.4	2864.6
7.5°	2872.4	2856.8	2820.1	2830.3	2817.3
10°	2840.9	2822.6	2770.3	2762.3	2746.6
12.5°	2801.7	2778.1	2707.2	2691.6	2662.7
15°	2754.5	2725.5	2636.5	2586.8	2560.7
17.5°	2699.4	2657.5	2547.3	2489.7	2447.7
20°	2636.5	2584.0	2453.1	2387.7	2329.8
22.5°	2568.5	2508.1	2356.0	2267.0	2227.8
25°	2500.3	2416.3	2243.3	2136.0	2096.6
27.5°	2419.1	2329.8	2138.5	2015.4	1955.1
30°	2332.6	2232.8	2023.1	1889.7	1818.8
32.5°	2248.6	2128.0	1913.3	1756.0	1690.3
35°	2154.4	2020.6	1790.2	1625.0	1567.2
37.5°	2062.7	1918.3	1674.8	1493.7	1428.4
40°	1965.6	1808.5	1554.1	1368.1	1299.9
42.5°	1866.1	1698.4	1433.6	1239.5	1174.3
45°	1761.3	1585.5	1310.5	1124.2	1061.4
47.5°	1661.7	1475.7	1192.6	1006.3	948.7
50°	1551.5	1365.6	1077.2	896.2	841.4
52.5°	1443.9	1247.3	967.1	794.1	744.3
55°	1339.1	1134.7	851.7	694.6	644.8
57.5°	1231.8	1022.1	749.6	602.8	560.9
60°	1121.7	912.0	642.0	508.6	466.6
62.5°	1014.3	804.7	550.2	424.6	403.7
65°	904.2	691.8	456.1	367.1	359.0
67.5°	799.4	587.0	367.1	322.2	314.5
70°	689.3	484.9	303.9	277.8	267.2
72.5°	584.5	390.4	254.2	233.3	228.0
75°	482.2	298.6	209.6	191.3	188.8
77.5°	380.1	212.1	165.2	154.6	149.3
80°	285.6	152.1	125.7	115.4	115.4
82.5°	199.1	102.3	86.5	81.2	81.2
85°	112.6	57.6	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930584
 CATALOG NUMBER: DFN2DS-PN3F0-070DS840-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	16.99	15.84	17.31	17.62	11.43	12.95	11.80	13.27	13.58
	3H	17.24	18.60	17.61	18.93	19.29	12.70	14.06	13.07	14.39	14.75
	4H	17.90	19.18	18.30	19.53	19.91	13.20	14.48	13.60	14.83	15.21
	6H	18.39	19.57	18.80	19.94	20.33	13.58	14.76	13.99	15.13	15.52
	8H	18.56	19.68	18.98	20.07	20.47	13.70	14.83	14.13	15.22	15.62
	12H	18.66	19.74	19.09	20.12	20.55	13.79	14.86	14.22	15.25	15.67
4H	2H	15.58	16.86	15.98	17.20	17.58	12.13	13.41	12.53	13.76	14.14
	3H	17.51	18.57	17.92	18.97	19.37	13.57	14.63	13.98	15.03	15.43
	4H	18.26	19.21	18.69	19.63	20.07	14.17	15.13	14.60	15.54	15.98
	6H	18.85	19.68	19.31	20.12	20.58	14.66	15.49	15.12	15.93	16.39
	8H	19.06	19.84	19.53	20.29	20.75	14.82	15.60	15.28	16.04	16.51
	12H	19.22	19.91	19.70	20.39	20.86	14.94	15.63	15.42	16.11	16.58
8H	4H	18.28	19.06	18.75	19.50	19.97	14.52	15.30	14.99	15.75	16.21
	6H	18.92	19.56	19.42	20.05	20.53	15.11	15.75	15.61	16.24	16.72
	8H	19.17	19.75	19.68	20.26	20.74	15.33	15.91	15.85	16.42	16.91
	12H	19.37	19.88	19.88	20.38	20.94	15.51	16.02	16.02	16.51	17.08
12H	4H	18.27	18.96	18.75	19.44	19.91	14.57	15.26	15.05	15.74	16.21
	6H	18.90	19.48	19.41	19.99	20.48	15.17	15.75	15.69	16.26	16.75
	8H	19.19	19.69	19.69	20.19	20.75	15.45	15.96	15.96	16.45	17.01