

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930567

Luminaire Tested: DFN2DS-PN3F0-060DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930567
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-060DS850-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6587.4 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 61.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930567

CATALOG NUMBER: DFN2DS-PN3F0-060DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930567

CATALOG NUMBER: DFN2DS-PN3F0-060DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3027	3027	3027
5°	3038	2994	3012
10°	3020	2964	2979
15°	2983	2926	2923
20°	2930	2868	2865
25°	2877	2797	2797
30°	2810	2732	2709
35°	2747	2654	2615
40°	2667	2576	2526
45°	2589	2498	2437
50°	2504	2418	2332
55°	2416	2324	2238
60°	2316	2212	2131
65°	2211	2101	2004
70°	2076	1965	1872
75°	1888	1810	1766
80°	1677	1625	1542
85°	1367	1302	1170

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2589 cd/sqm

TEST NUMBER: P930567

CATALOG NUMBER: DFN2DS-PN3F0-060DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	3.7
10°-20°	685.6	10.4
20°-30°	1007.6	15.3
30°-40°	1170.3	17.8
40°-50°	1168.8	17.7
50°-60°	1019.2	15.5
60°-70°	753.4	11.4
70°-80°	426.3	6.5
80°-90°	112.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1937.0	29.4
0°-40°	3107.2	47.2
0°-60°	5295.3	80.4
0°-90°	6587.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6587.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	120
90°	0	0	0	0	0	

TEST NUMBER: P930567

CATALOG NUMBER: DFN2DS-PN3F0-060DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930567

CATALOG NUMBER: DFN2DS-PN3F0-060DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.13	16.74	15.50	17.06	17.37	14.69	16.30	15.05	16.61	16.93
	3H	16.88	18.33	17.26	18.66	19.02	16.39	17.84	16.77	18.17	18.53
	4H	17.53	18.90	17.92	19.24	19.62	17.03	18.40	17.43	18.75	19.12
	6H	18.00	19.26	18.41	19.63	20.02	17.49	18.76	17.91	19.13	19.52
	8H	18.14	19.35	18.56	19.74	20.14	17.64	18.85	18.06	19.24	19.63
	12H	18.23	19.39	18.66	19.77	20.20	17.72	18.88	18.15	19.26	19.69
4H	2H	15.69	17.06	16.09	17.41	17.78	15.34	16.71	15.74	17.05	17.43
	3H	17.67	18.81	18.08	19.21	19.61	17.26	18.41	17.67	18.80	19.20
	4H	18.44	19.48	18.87	19.89	20.33	18.02	19.05	18.45	19.47	19.90
	6H	19.04	19.94	19.49	20.38	20.84	18.61	19.51	19.06	19.95	20.41
	8H	19.23	20.07	19.69	20.52	20.98	18.79	19.64	19.25	20.08	20.54
	12H	19.36	20.12	19.84	20.60	21.07	18.91	19.67	19.39	20.14	20.61
8H	4H	18.72	19.56	19.18	20.00	20.47	18.34	19.19	18.80	19.63	20.10
	6H	19.43	20.13	19.92	20.62	21.10	19.05	19.75	19.54	20.24	20.72
	8H	19.69	20.32	20.20	20.83	21.31	19.30	19.93	19.81	20.43	20.92
	12H	19.89	20.45	20.40	20.94	21.50	19.48	20.03	19.98	20.52	21.09
12H	4H	18.74	19.50	19.22	19.98	20.45	18.38	19.14	18.86	19.61	20.08
	6H	19.47	20.11	19.98	20.61	21.10	19.11	19.74	19.62	20.25	20.73
	8H	19.79	20.35	20.30	20.84	21.40	19.41	19.97	19.92	20.46	21.02